

- > Up to 35 PPM
- > Color MFP
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP





- > Color MFP
- > Up to 35 PPM
- > Medium/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP

Specifications

Copying Process	Indirect Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	LED Head Printing
Copy/Print Resolution	600 x 600 dpi (600 x 1200 - PS3 only)
Copy/Print Speed	25/25, 30/30, 35/35 PPM Color/B&W
Warm-Up Time	Approx. 27 Seconds
First Copy Out Time	8.1/6.4 Seconds Color/B&W
Max Duty Cycle	100K/150K/175K Copies
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to LD (16 lb Bond - 140 lb Index) Bypass: 3.9" x 5.8" to LD (16 lb Bond - 100 lb Cover) ST-R to 12" x 47" Banner (17 lb-100 lb) PFP: ST-R to LD (16 lb Bond - 140 lb Index) LCF: LT (17 lb - 28 lb Bond)
Memory (Max)	Main Memory: 2 GB HD: 160 GB (Security SED Drive)
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet "Smart" Bypass (16 lb Bond - 100 lb Cover)
Control Panel	Color 9" LCD Touch Panel
Paper Supply	Up to 3,200-Sheet Input Capacity Standard 2 x 550-Sheet Cassettes 100-Sheet Bypass 1 x 550-Sheet PFP (3rd Cassette) 1 x 550-Sheet Cassette (4th Cassette) for PFP Optional 1 x 2,000-Sheet LCF
Duplex	Standard Automatic Duplex Unit (16 lb Bond - 140 lb Index) Approx. 23" x 25.3" x 31" (W x D x H)
Dimensions	Approx. 166.4 lbs.
Weight	CMY: 28K, BK: 32K
CMYK Toner Yield	120 V, 15 Amps
Power Supply	Maximum 1.5 kW
Power Consumption	

Print Specifications

PDL Support	PCL6 and PostScript 3, XPS
Operating Systems	Netware 6.5, Windows XP, Vista, 7, Windows Server 2003, 2008, 2008R2, Citrix MetaFrame, Macintosh, Linux, UNIX, AS400, SAP
Protocol Support	IPX/SPX, TCP/IP, AppleTalk, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100
Drivers	Server 2003/2008/2008R2/2012, Windows XP, Vista, 7/8, Macintosh 10.2/10.3, 10.4, 10.5, 10.6, 10.7, AS400 LPR & Port 9100, SAP R/3, Unix Filter
Connectivity	10/100/1000BaseTX Ethernet, (802.11b/g/n optional)
Device Management	TopAccess
Certification	Windows (Vista, 7, 2008, 2008R2, 2012) (WHQL) Novell, HPOS (Dazel), Citrix

Scan Specifications

Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	73 SPM LT-Size @300 dpi, 50 SPM LT-Size @600 when copying, 73 SPM LT-Size @ 300 dpi (color scanning)
File Format	TIFF, PDF, Secure PDF, JPEG, XPS

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH / MR / MMR /JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Memory Transmission	100 Jobs, 2,000 Destinations Max. 400 Destinations /Job
Scan Speed	.7 Seconds Per Page, Maximum 73 SPM

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

Security (Standard)

Data Encryption	256 Bit AES (SED Hard Drive)
Authentication	LDAP, SMTP, Windows Server Domain, Local

Accessories (Options)

Additional Paper Options	
Platen	KA1640PC
RADF: 100 Sheets	MR3025
Paper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger	KD1032N
Cassette Module: 550-Sheet Pedestal, Statement-R to Ledger	MY1039
Large Capacity Feeder (LCF): 2,000-Sheet Drawer, Letter	KD1031

Finishing Options

Saddle-Stitch Finisher:	MJ1108
Tray 1 Stack Capacity: 3,000 Sheets + 250 Sheet Stationary Tray (LT)	
Staple Capacity: 50 Sheets	
60 Pages (15 Sheets) SS Booklets	
Multi-Position Hole Punch Unit for Saddle-Stitch Finisher	MJ6104
Multi-Position Console Finisher:	MJ1107
Tray 1 Stack Capacity: 2,000 Sheets (LT)	
Staple Capacity: 50 Sheets	
Multi-Position Hole Punch Unit for Console Finisher	MJ6104
Inner Finisher	MJ1036N
2 Tray: 500 Sheets (LT)	
Staple Capacity: 50 Sheets	
Multi-Position Hole Punch Unit for Inner Finisher	MJ6007

Connectivity/Security Options

Bridge Kit Required with MJ1108 and MJ1107	KN2550
Fax Board	GD1320NX
2nd Line Fax	GD1260F
Wireless LAN Adapter	GN1060
Wireless Antenna	GN3010
Meta Scan Enabler for e-CONNECT	GS1010
IP Sec Enabler	GP1080
Advanced Scanning (ReRite)	GB1280V8
SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540

Miscellaneous Options

Accessible Arm Handle	KK2550
-----------------------	--------



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.