E-STUDIO 3005ACG

- > Color Multifunction Printer
- > Up to 50 PPM
- > Medium/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Solutions Ready





CONNECT. INTEGRATE. SIMPLIFY.

Technology for every office, delivering advanced functionality, ease of use and peace of mind.

Every industry has unique workflow needs. Toshiba has developed customizable MFPs to make your job easier. Intuitive and smartly integrated, our products simplify complex tasks and give you control while providing the reliability Toshiba is known for.

Toshiba's latest series delivers on our promise of Together Information – our commitment to collaborate with clients in order to provide tailored, cost-effective solutions that meet your print, document management and content needs while helping you meet your green objectives.

- > 30 & 50 PPM
- > High-resolution color

Toshiba's latest e-BRIDGE Next controller delivers exceptional color quality.

Don't restrict yourself to black and white when you can print with impactful color. Not just any color, either. It's Toshiba's new, multi-beam laser color with higher resolution for top-notch image quality.

- > 1,200 dpi x 1,200 dpi (PostScript 3) for exceptional laser quality
- > The Toshiba e-BRIDGE Color Profile Tool allows for the creation of profiles to adjust color for varying media types, lighting or even to match Pantone colors, unique spot colors or output from another device
- > 256 gradations for smooth transitions in photographs and illustrations



SMALL FOOTPRINT, BIG BUSINESS.

Even with a relatively small footprint, the e-STUDIO3005ACG/5005ACG is packed with industry-leading technology and innovations designed to help workgroups connect, integrate and simplify.

Dual-Scan Document Feeder holds an amazing 300 originals and boasts an impressive 240 images per minute (IPM) by scanning both sides of the page in a single pass.

Multi-Station Print Enabler allows you to retrieve your print job from a series of networked MFPs via simple authentication.

Print Around eliminates printing bottlenecks by allowing other print jobs to go around one job that's held-up due to requiring a specific paper size or type or, in some cases, even colored toner.

Limitless Job Reservation will queue up multiple copy or print jobs so users can send jobs whenever.

Embedded Optical Character Recognition (OCR) simplifies the creation of searchable PDFs or editable document formats such as Microsoft Word®

Exclusive AquaAce Media water and tear resistant media up to 12" x 47" banner size.

Saddle/Fold Capabilities offer saddle-stitch finishing and the option to fold without stapling.

12" x 18" Cassette provides the ability to print stunning 11" x 17" color bleeds on 12" x 18" paper.

Scan-to and Print-from USB lets you print straight from your USB drive or scan documents to it.

Notifications Feature takes the hassle out of checking for depleted supplies or maintenance needs.

Paper Volume Indicators on the front panel make it easy to see the paper sizes, types and levels in each cassette.

Help Button provides instant, thorough explanations straight from the manual to help as needed.

Service Module Design significantly reduces the cost and time spent servicing the MFP.









TOSHIBA TECHNOLOGY NEVER LOOKED BETTER.

Keeping medium to large workgroups in mind, the e-STUDIO3005ACG/5005ACG is easily integrated, customizable and solutions ready, with an open platform.

Flexible integration with third-party solutions applications, an embedded web browser brings the workflow to one location, at your fingertips.

Toshiba's exclusive e-BRIDGE Print & Capture application enables mobile device users to take advantage of the broad feature set when they're in the office and on the go.

A universal driver along with PCL 6, PS3, and XPS support provide fast and easy connectivity to Windows, Macintosh and more.

The universal print driver works for all users. Tandem print comes standard, and you can choose from a variety of time-saving, function-adding plug-ins that enable productivity from the driver. For instance:

- > Job Point—quickly split up large jobs with up to 10 Toshiba MFPs
- Job Replicator—use multi-part form replacement (3 prints)
- Job Separator—perform batch printing easily using any Windows app
- Job Build—conveniently print different document types all together as a single job

Tight Security

Along with all of the new and innovative Toshiba technologies. we keep the security of your business top of mind.

- > A 320GB Self-Encrypting Drive (SED) with Automatic Drive Invalidation (ADI) & Data Overwrite capability provides top level security
- > FIPS 140-2 Validated SED meets and exceeds government requirements
- > IPsec is available to securely encrypt data sent to and from the MFP

Environmental Protection

Innovation that is truly innovative makes certain that our environment is part of the equation, which is precisely what we do here at Toshiba.

- > RoHS compliance, the use of recycled plastics, and Low-Power (0.6W) Super Sleep Mode work to help the environment
- > EPEAT Gold Registered in the global registry for greener electronics, designed to help purchasers



STUDIO:500540

FEATURES, BENEFITS, AND THE WOW FACTOR.

1 Document Feeder Options

MR4000 Dual-Scan Document Feeder (DSDF)

MR3031 Reversing Automatic Document Feeder (RADF)

KA5005PC Platen Cover

2 Accessory Tray & Options

GR1250 Accessory Tray
GR9000 Bluetooth Keyboard
GR1260 10-Key Numeric Keypad

3 Finishing Options

MJ1042 50-Sheet Inner Finisher
MJ1109 50-Sheet Console Finisher
MJ1110 50-Sheet Saddle-Stitch Finisher

MJ5015 Job Separator

4 Additional Paper Options

KD1058 Paper Feed Pedestal

KD1059LT 2,000-Sheet Large Capacity Feeder MY1048 Additional Drawer Module for PFP

MY1049 Envelope Cassette

Additional Option Highlights

- > Embedded OCR Enabler
- Multi-Station Print Enabler
- > Wireless LAN/Bluetooth
- > IPsec Security Enabler
- > Single & Dual-Line Facsimile
- > Hidden Card Reader Pocket
- > Expansive Third-Party Solutions List



The Toshiba e-STUDIO3005ACG/5005ACG can increase the efficiency of your workgroups, improve the professionalism of your presentations, and streamline the workflow of your organization. And, that's just for starters.

Double the Scan Speed

A 300-sheet high-speed, high-capacity Dual-Scan Document Feeder (DSDF) produces up to 120 IPM simplex and 240 IPM duplex. A conventional RADF is available for less scan-intensive businesses.

Envelopes—the Perfect Fit

A special envelope cassette is available to hold up to 60 envelopes, making sure each one is fed and printed in the same place, every time.

Volumes and Volumes

A high monthly copy volume is up to 210,000 for monochrome and 105,000 for color printing. Toner yields are 33,600 CMY and 38,400 K (at 5%) respectively.

Multi-Station Print Enabler

Toshiba's internally developed Multi-Station Print Enabler allows users to send print jobs from their desktop and retrieve them at any convenient MFP by simply swiping their badge and authenticating at that device.

Advanced e-BRIDGE Next Technology

Built on Linux®, this latest generation e-BRIDGE Next architecture features an Embedded Web Browser, a fast dual-core processor, 4GB RAM and a 320GB FIPS 140-2 Validated SED enabling the MFP to easily drive Toshiba's internally developed solutions or even third-party applications.



E-STUDIO 3005ACG/5005ACG

Main Specifications

Copy System Indirect Electrostatic Photographic Method/OPC/Laser Printing/

Heat Roller Fusing

Display 9" Color WVGA Touch Screen Tilting Display 30/50 PPM (LT)

Copy Speed First Copy Out Color: 7.8/5.9 Monochrome: 5.9/4.4 Warm-Up Time Approx. 20 Seconds

Copy Resolution 600 x 600 dpi 3.9" x 5.8" to 12" x 18", 12" x 47" Banner, Envelope Stack Feed Bypass Multiple Copying Up to 999 Copies

Standard 1,200 Sheets/Max. 3,200 Sheets Paper Capacity Optional 300-Sheet DSDF or 100-Sheet RADF **Original Feed**

DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color), Scan Speed & Weights

Simplex: 9.3-110 lb Bond, Duplex: 9.3-110 lb Bond RADF Scan: Up to 73 IPM (Monochrome or Color), Simplex: 9.3-41.8 lb Bond.

Duplex: 13.3-41.8 lb Bond

Max. Original Size

Paper Weights

Duplex

Paper Feed Sizes Drawer 1: 550 Sheets-ST-R to LD

Drawer 2: 550 Sheets-ST-R to LD Drawer 2: 550 Sheets-ST-R to 12" x 18" Stack Feed Bypass: 100 Sheets-3.9" x 5.8" to 12" x 18", 12" x 47" Banner

Opt. 550-Sheet Paper Feed Pedestal-ST-R to 12" x 18" Opt. 550-Sheet Drawer for PFP-ST-R to 12" x 18"

Opt. Envelope Cassette for PFP-Approx. 60 Envelopes/550 Sheets-ST-R to LG Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-LT Only

Standard: 550 Sheets x 2-16 lb Bond-140 lb Index Stack Feed Bypass: 100 Sheets-14 lb Bond-100 lb Cover Opt. 550-Sheet Paper Feed Pedestal-16 lb Bond-140 lb Index

Opt. 550 Sheets Drawer for PFP-16 lb Bond-140 lb Index
Opt. Envelope Cassette for PFP-16 lb Bond-140 lb Index
Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-17 lb-28 lb Bond Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)

Reproduction Ratio 25% to 400%

Max. 90K/105K Month (Color: 100%) **Max Duty Cycle** Max. 180K/210K Month (Monochrome: 100%)

Weight Approx.166 lb

Approx. Dimensions 23" (W) x 25.2" (D) x 31" (H) **CMYK Toner Yield** CMY: 33.6K, K: 38.4K @ 5% 120 Volts, 50/60 Hz, 12 Amps **Power Source** Maximum 1.5kW (120V) **Power Consumption** CPU Intel Atom™ 1.33 GHz (Dual-Core)

Memory 4GR

Hard Disk Drive 320GB Self-Encrypting Drive FIPS 140-2 Validated

e-BRIDGE Next Print Specifications

PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG PDL 30/50 Pages Per Minute (LT) **Print Speed**

Print Resolution 600 x 600 dpi (5 bit), 1,200 x 1,200 dpi (Color/2 bit) or 3,600 x 1,200 dpi

(BW/with Smoothing) PS3 Only)
Windows® Vista, Windows Server® 2008/R2, Windows® 7, 8, 8.1, 10,

Operating Systems Windows Server® 2012/R2, Macintosh® (Mac OS X 10.6, 10.7, 10.8, 10.9,

10.10, 10,11), Unix®, Linux®

TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, EtherTalk® for Macintosh Environments **Network Protocols**

Printing Protocols SMB, LPR/LPD, IPP (Ver.1.1) w/Authentication, AppleTalk PAP or EtherTalkTM, **Print Drivers**

Port 9100 (bi-directional), NetWare P-SERVER LPD w/ iPrint, WS Print, FTP Windows® Vista SP2 (32-bit, 64-bit), Windows Server® 2008 SP2 (32-bit, 64-bit), Windows Server® 2008 R2 SP1 (64-bit), Windows® 7 SP1 (32-bit, 64-bit), Windows Server® 2008 R2 SP1 (64-bit), Windows® 7 SP1 (32-bit, 64-bit), Windows® 10 SP1 Windows® 8/8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows®

10 (32-bit, 64-bit), Mac OS® X 10.6.8, 10.7.4, 10.8, 10.9, 10.10 RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-speed) Optional

802.11b/g/n, Wireless LAN, Optional Bluetooth AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android Wireless Device

(Available via Apple App Store or Google Play)
TopAccess, EFMS 6.2 (e-BRIDGE Fleet Management Software)
Up to 10,000 users or 1,000 Departments Supports User Authentication Device Management

Account Control

(on Device), Login Name/Password (via Windows domain) or Login Name/ Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Accessibility Features Timeout and Audible Beep Message Alerts

Interface













Security Features

User Authentication, On-Board Data Scramble Function, SCFP, Disable e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408 EAL3+)*, IEEE2600.1, IEEE802.1X, Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log

Access Control for Job Log, Security Stamp
*Compliant with IEEE2600.1 in High Security Mode.

Energy Star (V2.0), EPEAT Gold, Blue Angel Mark (RAL UZ-171, MFD), **Environmental Stds.**

Canadian ECP, Californian Proposition 65, Nordic Swan, RoHS WHQL (Windows 7, 8, 8.1, 10, 2008 R2, 2012, 2012 R2), Novell, Citrix, SAP Certification

Scan Specifications

Scan Speed DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color)

RADF Scan: Up to 73 IPM (Monochrome or Color) Standard: Full Color, Auto Color, Monochrome, Grayscale Scan Modes 600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi Scan Resolution **File Formats**

Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, Slim PDF, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX

(Opt.), PPTX (Opt.) Color/Grayscale: JPEG (High, Middle, Low) Image Compression

Facsimile Specifications

Compatibility Super G3 **Data Compression** MH/MR/MMR/JBIG Approx. 3 Seconds Per Page Transmission Speed

Up to 33.6 Kbps Fax Modem Speed

Memory Transmission 100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job 0.7 Seconds Per Page, Maximum 73 IPM Scan Speed

e-Filing Specifications

Operation Method Color Touch Screen Control Panel or Client PC **Number of Boxes** 1 Public Box, 200 Private User Boxes

Capacity of Boxes 100 Folders Per Box, 400 Documents Per Folder/Box,

200 Pages Per Document

Accessories (Options)

Platen & Document Feeder Options

MR4000 RADF MR3031 Platen Cover KA5005PC

Additional Paper Options

Paper Feed Pedestal KD1058 Drawer Module MY1048 Envelope Cassette Option MY1049 Large Capacity Feeder KD1059LT

Finishing Options Inner Finisher

MJ1042 50-Sheet Staple Finisher MJ1109 Saddle-Stitch Finisher M.I1110 Hole Punch Unit for MJ1042 MJ6011 Hole Punch Unit for MJ1109/MJ1110 MJ6105 Bridge Kit KN5005 Job Separator MJ5015

Connectivity/Security Options

FAX Unit/2nd Line for FAX Unit GD1370 Wireless LAN/Bluetooth GN4020 Hardcopy Security Printing GP1190A Bluetooth Keyboard GR9000 Accessory Tray Panel 10-Key Option GR1250 GR1260 Card Reader Holder GR1290 Meta Scan Enabler GS1010 IPsec Enabler GP1080 Unicode Font Enabler GS1007 Embedded OCR Enabler GS1080 Single License Five Licenses GS1085 Multi-Station Print Enabler GS1090 Single License Five Licenses GS1095 Advanced Scanning (ReRite) GB1280V8 SharePoint Connector GB1440 GB1450 Exchange Connector Google Docs Connector GB1540

Miscellaneous Options

STAND5005 Stand Accessible Arm KK2550 Work Tray KK5005 Harness Kit for Coin Controller GQ1280

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. This is a Class 1 laser product complying with IEC60825-1.

Corporate Office

Midwest

West Coast

South

9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000

East Coast 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000

2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385

9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000 Web Site www.business.toshiba.com