



# A new standard has officially been set.

Multiple functions, innumerable benefits and millions of colors have never been more accessible. The e-STUDIO2555c/3055c/3555c is easily integrated, customizable and solutions ready, with an open platform. You'll also appreciate cloud and mobile printing and scanning along with a host of other benefits.

# **Easy integration**

Includes flexible customization, new EFMS device management and system software upgraded by patch. cloning and F/W updates.



# Open platform

Take advantage of flexible integration into solution applications, output management interface, and an embedded Web browser that can be registered in a template.



# Cloud, internet, and mobile printing/scanning

Enjoy mobile convenience with e-BRIDGE support for new cloud computing and mobile applications as well as Internet browsing and printing from the Internet.



## Universal print driver

One driver works for all users, tandem print comes standard, and additional optional plug-ins can be put directly into the driver.



# Impressive image quality

Low temperature color toner increases range of colors. Other benefits include high gloss output. e-BRIDGE Color Profiler and spot-on color matching.



# AquaAce specialty paper support

Achieve brilliant color that's water, weather and fade resistant. It's like laminated paper without the lamination, in legal and letter sizes. Banner printing can be done using paper up to 12" x 47".



# Compact and lightweight

It has one of the smallest footprints of any comparable MFP. It's 37% lighter than before and substantially quieter.



### Low power consumption

New energy saving technologies have been incorporated, resulting in reduced power consumption.



# Improved serviceability

The replacement of process units is easier and can be performed without a screwdriver. Automatic detection and initialization of a new unit has been added.



# **High security**

A unique Self Encrypting Drive (SED) includes Toshiba's proprietary Wipe Technology along with a suite of security functions that create a level of data protection that's unequalled.





# There's more to Toshiba color than ever before.

Now you can copy, print, scan and fax with an MFP that's smaller, guieter, sleeker, and faster than ever. The new e-STUDIO2555c/3055c/3555c from Toshiba is designed to replace black and white printing with affordable full color, while still offering high quality black and white.

# Color options to match your needs.

For all those times you want to print in color but settle for black and white, there's the e-STUDIO2555c/3055c/3555c. It's designed to make color more efficient and accessible. Whether you want to spruce up a presentation with color produced up to a remarkable 25/30/35 pages per minute or print crisp, clear black and white, you'll be impressed with all that the e-STUDIO2555c/3055c/3555c has to offer. Unique features like the e-BRIDGE Universal Print Driver, the only driver needed for multiple users, allowing you to switch between PS and PCL. It includes plug-ins so you can add features.

# More compact with more impact.

Even though it's chock-full of extraordinary features, the e-STUDIO2555c/3055c/3555c has one of the smallest footprints of any MFP in its class. So, it can be used wherever space is limited. It's lighter, too, which makes it



# Your data has never been more secure.

Toshiba knows that security is a high priority for businesses today. That's why we've put leading innovation to work and developed security measures that are unsurpassed.

# Wipe Technology – it's like the data was never there.

It makes perfect sense. The best way to keep your data secure is to use a method no one else has replicated. That's just what we've done at Toshiba with our proprietary Wipe Technology. The e-STUDIO2555c/3055c/3555c offers Toshiba's proprietary Self-Encrypting Drive equipped with our Wipe Technology as well as a suite of impressive security functions to keep data protected. If the HDD is taken from the MFP and installed into another device, all of the data is automatically erased.

In addition, the HDD data is quickly invalidated at the end of life so you do not have to worry about that either. There is also an encryption key that's securely stored on the HDD.

# Security taken to the next level.

Additional security features include a secure PDF encryption feature with up to 128-bit AES, IP/MAC address filtering, Role Based Access Control, an SNMPv3 protocol for enhanced security administration and an optional IPSec protocol, to name a few. In all, the features permit a security mode that complies with the extremely high security level–IEEE2600.1.

- > Self Encrypting Drive
- > IPSec Enabler (optional)
- > Common Criteria EAL 3+
- > IP Filtering
- > Network Port Control
- > Secure PDF
- > Private Print









Benefits include a 3,200-sheet capacity (including an optional 2,000-sheet LCF), direct USB printing, and tiltable display.



Manage, capture and deliver documents with simple one-touch control using the large, 9" color control panel. It's designed to be easy to read and use.



# Environmentally friendly as well as user friendly.

At Toshiba, we work hard to make certain our products minimize environmental impact. Many of our leading innovations include new ways to save energy and save the environment.

# Saving energy and saving you money.

An added benefit to our new energysaving technologies is that they save you money, too. Take, for instance, our new low temperature fusing toner. Color reproduction is improved while energy consumption is reduced. Energy consumption is reduced even further, thanks to a dramatic reduction in the power usage during sleep mode. Other ways in which Toshiba puts environmental responsibility into action include a recycling program, reduction of CO<sub>2</sub> emissions, and the recycling of plastics. Reduction or elimination of hazardous materials such as lead and mercury enable the series to comply with environmental standards around the world. Everything together qualifies the series to be EPEAT registered.





Print professional-looking, full-color newsletters and brochures using an optional saddle-stitch or staple finisher.



# Doing more for our planet.

From our zero-waste-tolandfill toner recycling to greener manufacturing, Toshiba is a recognized environmental leader. At Toshiba we're investing in programs that help both our business and yours to better reduce, reuse and recycle.



e-STUDIO3555c with Saddle-Stitch Finisher.



e-STUDIO3555c with Paper Feed Pedestal.



e-STUDIO3555c with Inner Finisher and LCF.



# E-STUDIO 2555c/3055c/3555c





- > Color MFP
- > Up to 35 PPM
- Medium/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP

# **Specifications**

Copying Process Indirect Electrostatic Photographic Transfer System

with Internal Transfer Belt

Copying Type LED Head Printing

 Copy/Print Resolution
 600 x 600 dpi (600 x 1200 - PS3 only)

 Copy/Print Speed
 25/25, 30/30, 35/35 PPM Color/B&W

Warm-Up Time Approx. 27 Seconds
First Copy Out Time 8.1/6.4 Seconds Color/B&W
Max Duty Cycle 100K/150K/175K Copies
Multiple Copying Up to 999 Copies

Acceptable Paper Size Cassette 1: LD to ST-R (16 lb. Bond- 140 lb. Index)

and Weight Cassette 2 (and opt. KD1032, MY1039): ST-R to 12 x 18 (16

lb. Bond- 140 lb. Index)

Bypass: 3.9" x 5.8" to LD (14 lb Bond - 100 lb Cover)

12" x 47" (24 lb Bond - 90 lb Index) PFP: ST-R to LD (16 lb Bond - 140 lb Index)

LCF: LT (17 lb - 28 lb Bond) Memory (Max) Main Memory: 2 GB

HD: 320 GB SED

Reduction/Enlargement 25% to 400%

Bypass (14 lb Bond - 100 lb Cover)

Control Panel

Paper Supply

Color 9" LCD Touch Panel

Up to 3,200-Sheet Input Capacity

Standard 2 x 550-Sheet Cassettes

100-Sheet Bypass

Optional 1 x 550-Sheet PFP (3rd Cassette)

Optional 1 x 550-Sheet Cassette (4th Cassette) for PFP Optional 1 x 2,000-Sheet LCF

Duplex Standard Automatic Duplex Unit (16 lb Bond - 140 lb Index)

Dimensions Approx. 23" x 25.3" x 31" (W x D x H)

Weight Approx. 166.4 lbs.
CMYK Toner Yield CMY: 28K, BK: 32K
Power Supply 120 V, 15 Amps
Power Consumption Maximum 1.5 kW

# e-BRIDGE Print Specifications

PDL Support PCL6, PostScript 3, XPS

Operating Systems Windows Server 2003, 2008, 2012, Vista SP2, 7, 8,

NetWare 6.5, Citrix, Macintosh 10.4-10.9,

Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO
Protocol Support Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1)

w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/ iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP

Drivers Windows Server 2003, 2008, 2012, Vista SP2, 7, 8,

Macintosh OS 10.4-10.9

Connectivity 10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB

Wireless Device AirPrint, e-BRIDGE Print & Capture Application on iOS and

Android (Available via Apple App Store or Google Play)

Device Management Top Access,

eFMS 6.0 (e-BRIDGE Fleet Management Software)

Windows 7, 8, 8.1,2008R2, 2012, 2012 R2,

WHQL, Novell, Citrix

## Scan Specifications

Certification

Scan Resolution
100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed
73 SPM LT-Size @300 dpi, 50 SPM LT-Size @600 when copying, 73 SPM LT-Size @ 300 dpi (color scanning)

File Format TIFF, PDF, Secure PDF, JPEG, XPS

# **Facsimile Specifications**

Compatibility Super G3

Data Compression
Transmission Speed

MH / MR / MMR / JBIG
Approx. 3 Seconds Per Page

Fax Modem Speed 33.6 Kbps

Memory Transmission 100 Jobs, 2,000 Destinations Max.

400 Destinations /Job

Scan Speed .7 Seconds Per Page, Maximum 73 SPM

## E-Filing Specifications

Operation Method Color Touch Screen Control Panel or Client PC Number of Boxes 1 Public Box, 200 Private User Boxes

Capacity of Boxes 100 Folders Per Box, 400 Documents Per Folder

200 Pages Per Document

Security (Standard)

Data Encryption 256 Bit AES (SED Hard Drive)

Authentication LDAP, SMTP, Windows Server Domain, Local

# **Accessories (Options)**

# **Additional Paper Options**

Platen
RADF: 100 Sheets
Apper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger
Cassette Module: 550-Sheet Pedestal, Statement-R to Ledger
Large Capacity Feeder (LCF): 2,000-Sheet Drawer, Letter

KA1640PC
MR3025
KD1032N
KD1032N
KD1032N
KD1031

### **Finishing Options**

Saddle-Stitch Finisher: MJ1108

Tray 1 Stack Capacity: 3,000 Sheets + 250 Sheet Stationary Tray (LT)

Staple Capacity: 50 Sheets 60 Pages (15 Sheets) SS Booklets

Multi-Position Hole Punch Unit for Saddle-Stitch Finisher MJ6104
Multi-Position Console Finisher: MJ1107

Tray 1 Stack Capacity: 2,000 Sheets (LT)

Staple Capacity: 50 Sheets

Multi-Position Hole Punch Unit for Console Finisher MJ6104 Inner Finisher MJ1036N

2 Tray: 500 Sheets (LT) Staple Capacity: 50 Sheets

Multi-Position Hole Punch Unit for Inner Finisher

Connectivity/Security Options

Bridge Kit Required with MJ1108 and MJ1107 KN2550 Fax Board GD1320NX 2nd Line Fax GD1260F Wireless LAN Adapter GN1060 Wireless Antenna GN3010 Meta Scan Enabler for e-CONNECT GS1010 IP Sec Enabler GP1080 Advanced Scanning (ReRite) GB1280V8 SharePoint Connector GB1440 **Exchange Connector** GB1450 Google Docs Connector GB1540

# Miscellaneous Options

Accessible Arm Handle



Web Site

















KK2550

MJ6007

Corporate Office 974

9740 Irvine Blvd., Irvine, CA 92618-1631

Tel: 949-462-6000

East Coast 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700

Tel: 9/3-316-2/00

Midwest 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000

Tel: 773-380-6000

South 2037 Bakers Mill Rd., Dacula, GA 30019

Tel: 678-546-9385

West Coast 9740 Irvine Blvd., Irvine, CA 92618

Tel: 949-462-6000

www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

© 2014 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv.Code: 22229 2555c 3055c 3555c Brochure 6/14

Inv.Code: 22229 2555c 3055c 3555c Brochure 6/