

TOSHIBA
Leading Innovation >>>

- > Color MFP
- > Up to 42 PPM
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP



e-STUDIO™ 287CSL/347CSL/407CS





- > Color MFP
- > Up to 42 PPM
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP

Specifications

Copying Process	Direct Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	LED Head Printing
Copy/Print Resolution	600/600 x 600/1200 dpi
Copy/Print Speed	30/30, 35/37, 42/42, PPM Color/B&W
Warm-Up Time	Approx. 60 Seconds
First Copy Out Time	13 Seconds
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to LG (17lb Bond - 120lb Index) Bypass: 3" x 5" to LG, Banner 8.5" x 52" (17lb Bond - 138lb Index)
Memory (Max)	Main Memory: 2GB HD: 320GB FIPS 140-2 Validated SED
Document Feeder	100-Sheet
Reduction/Enlargement	25% to 400% (RADF: 25% to 200%)
Bypass	100-Sheet "Smart" Bypass (17lb Bond - 138lb Index)
Control Panel	Color 9" LCD Touch Panel
Paper Supply	Up to 2,630-Sheet Input Capacity Standard 1 x 530-Sheet Cassettes 100-Sheet Bypass Optional 3 x 530-Sheet Cassette Optional 2,000-Sheet LCF
Duplex	Std. Automatic Duplex Unit (17lb Bond - 120lb Index)
Dimensions	287CSL/347CSL: Approx. 20.6" x 23.8" x 26.4" (W x D x H) 407CS: Approx. 20.6" x 23.8" x 31.9" (W x D x H)
Weight	Approx. 112.43lb
CMYK Toner Yield	CMY: 11.5K, BK: 15K
Power Supply	120 V, 8 Amps
Power Consumption	Maximum 1.5 kW
Max Duty Cycle	85K/100K/125K Copies

e-BRIDGE Print Specifications

PDL Support	PCL6, PostScript 3, XPS
Operating Systems	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO
Protocol Support	Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP
Drivers	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB
Wireless Device	AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)
Device Management	Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software)
Certification	Windows 7, 8, 8.1, 2008R2, 2012, 2012 R2, WHQL, Novell, Citrix

Scan Specifications

Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	40 SPM Color/40 SPM B&W (@ 300 dpi)
File Format	TIFF, PDF, Secure PDF, JPEG, XPS

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Scan Speed	Maximum 40 SPM

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder, 200 Pages Per Document

Security

Data Encryption & Disk Overwrite Authentication	256 Bit AES (SED Hard Drive) LDAP, SMTP, Windows Server Domain, Local
---	--

Accessories (Options)

Additional Paper Options, Spacers, Caster Base

Spacer: (For Adjusting Machine Height Replacing a Stand)	GR1160
Caster Base: (Caster Base for PFU, LCF or Spacer)	GR1170
Cassettes: 530-Sheet Pedestal, 8.5SQ to 14LG	MY1045
Large Capacity Feeder (LCF): 2,000-Sheet Drawer, LT, 13LG, 13.5LG, 14LG, A4	KD1040

Finishing Options

Inner Finisher (e-STUDIO407cs Only): 1 Tray: 500 Sheets	MJ1038
Damper Kit (Required for MJ1038)	KK1002
Offline Stapler	MJ1039

Connectivity/Security Options

Fax Board	GD1340
Wireless Module	GN1060
Wireless Antenna	GN3010
Meta Scan Enabler for e-CONNECT	GS1010
IPsec Enabler	GP1080
Advanced Scanning (Re-Rite)	GB1280V8
SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support vary by client/network operating system.