

- > Up to 50 PPM
- > Color MFP
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP





- ▶ Color MFP
- ▶ Up to 50 PPM
- ▶ Medium/Large Workgroup
- ▶ Copy, Print, Scan, Fax
- ▶ Secure MFP

**Specifications**

|                                  |   |
|----------------------------------|---|
| Copying Process                  | Indirect Electrostatic Photographic Transfer System with Internal Transfer Belt   |
| Copying Type                     | LED Head Printing   |
| Copy/Print Resolution            | 600 x 1200 dpi (PS Driver)  |
| Copy/Print Speed                 | 45/45, 50/50 PPM Color/B&W  |
| Warm-Up Time                     | Approx. 27 Seconds  |
| First Copy Out Time              | 6.1/4.7 Seconds Color/B&W   |
| Max Duty Cycle                   | 200K/225K Copies  |
| Multiple Copying                 | Up to 999 Copies  |
| Acceptable Paper Size and Weight | Cassette 1: LD to ST-R (16 lb. Bond- 140 lb. Index)<br>Cassette 2 (and opt. KD1032, MY1039): ST-R to 12 x 18 (16 lb. Bond- 140 lb. Index)<br>Bypass: 3.9" x 5.8" to LD (14 lb Bond - 100 lb Cover)<br>12" x 47" (24 lb Bond - 90 lb Index)<br>PFP: ST-R to LD (16 lb Bond - 140 lb Index)<br>LCF: LT (17 lb - 28 lb Bond) |
| Memory (Max)                     | Main Memory: 2 GB<br>HD: 320 GB SED   |
| Reduction/Enlargement            | 25% to 400%   |
| Bypass                           | 100-Sheet "Smart" Bypass (14 lb Bond - 100 lb Cover)  |
| Control Panel                    | Color 9" LCD Touch Panel  |
| Paper Supply                     | Up to 3,200-Sheet Input Capacity<br>Standard 2 x 550-Sheet Cassettes<br>100-Sheet Bypass<br>1 x 550-Sheet PFP (3rd Cassette),<br>1 x 550-Sheet Cassette (4th Cassette) for PFP<br>Optional 1 x 2,000-Sheet LCF  |
| Duplex                           | Standard Automatic Duplex Unit (16 lb Bond - 140 lb Index)  |
| Dimensions                       | Approx. 23" x 25.3" x 31" (W x D x H)   |
| Weight                           | Approx. 166.4 lbs.  |
| CMYK Toner Yield                 | CMY: 28K, BK: 32K   |
| Power Supply                     | 120 V, 15 Amps  |
| Power Consumption                | Maximum 1.5 kW  |

**e-BRIDGE Print Specifications**

|                   |   |
|-------------------|---|
| PDL Support       | PCL6, PostScript 3, XPS   |
| Operating Systems | Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO   |
| Protocol Support  | Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/ iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP |
| Drivers           | Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9  |
| Connectivity      | 10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB  |
| Wireless Device   | AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)  |
| Device Management | Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software)   |
| Certification     | Windows 7, 8, 8.1, 2008R2, 2012, 2012 R2, WHQL, Novell, Citrix  |

**Scan Specifications**

|                 |  |
|-----------------|--|
| Scan Resolution | 100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi |
| Scan Speed      | 73 SPM Color/73 SPM B&W (@ 300 dpi)                  |
| File Format     | TIFF, PDF, Secure PDF, JPEG, XPS (with HDD)          |

**Facsimile Specifications**

|                     |  |
|---------------------|--|
| Compatibility       | Super G3   |
| Data Compression    | MH / MR / MMR / JBIG   |
| Transmission Speed  | Approx. 3 Seconds Per Page   |
| Fax Modem Speed     | 33.6 Kbps  |
| Memory Transmission | 100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations /Job |
| Scan Speed          | .7 Seconds Per Page, Maximum 73 SPM                                |

**E-Filing Specifications**

|                   |   |
|-------------------|---|
| Operation Method  | Color Touch Screen Control Panel or Client PC                           |
| Number of Boxes   | 1 Public Box, 200 Private User Boxes                                    |
| Capacity of Boxes | 100 Folders Per Box, 400 Documents Per Folder<br>200 Pages Per Document |

**Security (Standard)**

|                 |  |
|-----------------|--|
| Data Encryption | 256 Bit AES (SED Hard Drive)             |
| Authentication  | LDAP, SMTP, Windows Server Domain, Local |

**Accessories (Options)**

|  |          |
|--|----------|
| <b>Additional Paper Options</b>                                |          |
| Platen:  | KA1640PC |
| RADF: 100 Sheets   | MR3025   |
| Paper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger | KD1032N  |
| Cassette Module :550-Sheet Pedestal, Statement-R to Ledger     | MY1039   |
| Large Capacity Feeder (LCF): 2,000-Sheet Drawer, Letter        | KD1031   |

**Finishing Options**

|  |        |
|--|--------|
| Saddle-Stitch Finisher:  | MJ1108 |
| Tray 1 Stack Capacity: 3,000 Sheets + 250 Sheet Stationary Tray (Lt) |        |
| Staple Capacity: 50 Sheets   |        |
| 60 Pages (15 Sheets) SS Booklets                                     |        |
| Multi-Position Hole Punch Unit for Saddle-Stitch Finisher            | MJ6104 |
| Multi-Position Console Finisher:                                     | MJ1107 |
| Tray 1 Stack Capacity: 2,000 Sheets (Lt)                             |        |
| Staple Capacity: 50 Sheets   |        |
| Multi-Position Hole Punch Unit for Console Finisher                  | MJ6104 |

**Connectivity/Security Options**

|  |          |
|--|----------|
| Bridge Kit Required with MJ1108 and MJ1107 | KN2550   |
| Fax Board                                  | GD1320NX |
| 2nd Line Fax                               | GD1260F  |
| Wireless LAN Adapter                       | GN1060   |
| Wireless Antenna                           | GN3010   |
| Meta Scan Enabler for e-CONNECT            | GS1010   |
| IP Sec Enabler                             | GP1080   |
| Advanced Scanning (ReRite)                 | GB1280V8 |
| SharePoint Connector                       | GB1440   |
| Exchange Connector                         | GB1450   |
| Google Docs Connector                      | GB1540   |

**Miscellaneous Options**

|                       |        |
|-----------------------|--------|
| Accessible Arm Handle | KK2550 |
|-----------------------|--------|



|                         |   |
|-------------------------|---|
| <b>Corporate Office</b> | 9740 Irvine Blvd., Irvine, CA 92618-1631<br>Tel: 949-462-6000             |
| East Coast              | 959 Route 46 East, 5th Floor, Parsippany, NJ 07054<br>Tel: 973-316-2700   |
| Midwest                 | 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631<br>Tel: 773-380-6000 |
| South                   | 2037 Bakers Mill Rd., Dacula, GA 30019<br>Tel: 678-546-9385               |
| West Coast              | 9740 Irvine Blvd., Irvine, CA 92618<br>Tel: 949-462-6000                  |
| Web Site                | www.business.toshiba.com  |

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.