

- > Up to 55 PPM
- > Black & White MFP
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP





- > Black & White MFP
- > Up to 55 PPM
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP

Specifications

Copying Process	Indirect Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	LED Head Printing
Copy/Print Resolution	600 x 600 dpi (1200 x 1200 dpi - PS3 only)
Copy/Print Speed	49/55 PPM B&W
Warm-Up Time	Approx. 60 Seconds
First Copy Out Time	8 Seconds
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to LG (17 lb Bond - 120 lb Index) Bypass: 3" x 5" to LG (17 lb Bond - 138 lb Index)
Memory (Max)	Main Memory: 2 GB HD: 160GB (Security SED Drive)
Document Feeder	100-Sheet
Reduction/Enlargement	25% to 400%
Control Panel	Color 9" LCD Touch Panel
Paper Supply	Up to 3,160-Sheet Input Capacity Standard 1 x 530-Sheet Cassettes 100-Sheet Bypass Optional 3 x 530-Sheet Cassette Optional 2000-Sheet LCF
Duplex	Std. Automatic Duplex Unit (17 lb Bond - 120 lb Index)
Dimensions	Approx. 20.55" x 22.2" x 32" (W x D x H)
Weight	Approx. 115 lbs
Toner Yield	36K
Power Supply	120 V, 15 Amps
Power Consumption	Maximum 1.5 kW
Max Duty Cycle	200/225K Copies

Print Specifications

PDL Support	PCL6 and PostScript 3, XPS
Operating Systems	Netware 6.5, Windows XP, Vista, 7, 8 Windows Server 2003, 2008, 2008R2, 2012, Citrix, Macintosh, Linux, UNIX, AS400, SAP IPX/SPX, TCP/IP, AppleTalk
Protocol Support	NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100,
Drivers	Server 2003/2008/2008R2/2012, Windows XP, Vista, 7, 8, Macintosh 10.4, 10.5, 10.6, 10.7, 10.8 AS400, LPR & Port 9100, SAP R/3, Unix Filter 10/100/1000BaseTX Ethernet, (802.11b/g/n optional)
Connectivity	TopAccess
Device Management	Windows (XP, Vista, 7, 8, 2003, 2008, 2008R2)
Certification	Novell HPOS (Dazel), Citrix

Scan Specifications

Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	55 SPM B&W, 40 SPM Color (@ 300 dpi)
File Format	TIFF, PDF, Secure PDF, JPEG, XPS (with HDD)

Facsimile Specifications (Option GD 1340)

Compatibility	Super G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Memory Transmission	1 GB
Scan Speed	.7 Seconds Per Page, Maximum 42 SPM

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

Security

Data Encryption	256 Bit AES (SED Hard Drive)
Disk Overwrite	1-5 Time Overwrite (meets DOD standard)
Authentication	LDAP, SMTP, Windows Server Domain, Local

Accessories (Options)

Additional Paper Options, Spacers, Caster Base	
Spacer (For adjusting machine height replacing a stand)	GR1160
Caster Base (Caster base for PFU, LCF or Spacer)	GR1170
Cassettes: 530-Sheet Pedestal, ST-R to LG	MY1046
Large Capacity Feeder (LCF): 2,000-Sheet Drawer, LT	KD1040
Stand (Use in place of LCF)	STAND407CS

Finishing Options

Inner Finisher:	MJ1038
1 Tray: 500 Sheets	
Damper Kits	KK1003
Offline Stapler	MJ1039

Connectivity/Security Options

Fax Board	GD1340
Wireless Module	GN1060
Wireless Antenna	GN3010
Meta Scan Enabler for e-CONNECT	GS1010
IP SEC Enabler	GP1080
Advanced Scanning (ReRite)	GB1280V8
SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.