

**TOSHIBA**

Leading Innovation >>>

- > Black & White MFP
- > Up to 50 PPM
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered



**e-STUDIO™ 357/457/507**





- > **Black & White MFP**
- > **Up to 50 PPM**
- > **Small/Medium Workgroup**
- > **Copy, Print, Scan, Fax**
- > **Secure MFP**
- > **EPEAT Registered**

**Specifications**

Copying Process/Type	IEPM (Dry Process)/Laser Technology
Original Reading Method	CCD Line Sensor
Copy/Print Resolution	2400 x 600 dpi (with Smoothing)
Copy/Print Speed	35/45/50 PPM
Warm-Up Time	Approx. 20 Seconds
First Copy Time	3.7 Seconds
Duty Cycle	125K/150K/150K
Multiple Copying	Up to 999 Copies
Standard Paper Supply	2 x 550-Sheet, 100-Sheet Stack Feed Bypass
Maximum Paper Supply	Up to 3,200 Sheets
Acceptable Paper Size	Cassette: Statement-R to Ledger (17-28 lb), Bypass: Statement-R to Ledger (17-110 lb), LCF: Letter (17-28 lb)
Memory	2GB RAM, 320 GB FIPS 140-2 SED
Reduction/Enlargement	25% to 400%
Bypass Tray	100-Sheet Stack Feed Bypass
Control Panel	9" Wide VGA Color Touch-Screen
Dimensions	Approx. 23" x 23" x 30" (W x D x H)
Weight	Approx. 132 lb
Power Supply	115 Volts, 15 Amps
Power Consumption	Maximum 1.5kW
PM Cycle	125K/150K/150K
Black Toner Yield	36.6K Impressions @ 6%

**e-BRIDGE Print Specifications**

PDL Support	PCL6, PostScript 3, XPS
Operating Systems	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO
Protocol Support	Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/ iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP
Drivers	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB
Wireless Device	AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)
Device Management	Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software)
Certification	Windows 7, 8, 8.1, 2008R2, 2012, 2012 R2, WHQL, Novell, Citrix

**Scan Specifications**

Scan Speed	57 SPM LT-Size @ 300 dpi, 45 SPM LT-Size @ 600 dpi (When Copying), 43 SPM LT-Size @ 300 dpi (Color Scanning)
Scan Resolution	Up to 600 dpi
File Format	TIFF, PDF, Slim PDF, JPEG, XPS, MS Word, MS Excel, Searchable PDF w/Adv. Scanning Option

**Facsimile Specifications**

Compatibility	Super G3, G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	Transmission and Reception 1GB (HDD), Backup Permanent (HDD)
Memory Transmission	100 Jobs, 2,000 Destinations Max, 400 Destinations/Job
Scan Speed	0.7 Seconds Per Page, 50 Scans Per Minute
Other Fax Functions	Internet Fax, Network Fax

**e-Filing Specifications**

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folder Per Box, 400 Documents Per Folder, 1000 Pages Per Documents

**Security (Standard)**

Data Encryption	256 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) Standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

**Accessories (Options)**

<b>Input Options</b>	
100-Sheet RADF	MR3028
Platen Cover	KA1640PC
<b>Additional Paper Options</b>	
550-Sheet Paper Feed Pedestal	KD1025
2,000-Sheet Large Capacity Feeder	KD1026
550-Sheet Paper Feed Unit	MY1033
<b>Finishing Options</b>	
Job Separator	MJ5006
Work Tray	KK4550
Bridge Kit for Finisher	KN2520N
50-Sheet Inner Finisher	MJ1032N
Saddle-Stitch Finisher (High Capacity)	MJ1108
Saddle-Stitch Finisher (Low Capacity)	MJ1033
50-Sheet Staple Console Finisher	MJ1107
2/3-Hole Punch Unit for MJ1032N	MJ6007
2/3-Hole Punch Unit for MJ1107 and MJ1108	MJ6104
2/3-Hole Punch Unit for MJ1033	MJ6008

**Connectivity/Security Options**

Fax Kit	GD1350
2nd Line Fax	GD1260F
IPsec Enabler	GP1080
Wireless LAN Adapter	GN1060
Antenna	GN3010
Meta Scan Enabler	GS1010
Advanced Scanning	GB1280T
Harness Kit for Coin Controller	QQ1180



<b>Corporate Office</b>	9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000
<b>East Coast</b>	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
<b>Midwest</b>	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
<b>South</b>	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
<b>West Coast</b>	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
<b>Web Site</b>	www.business.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.