

TOSHIBA
Leading Innovation >>>

- > Color MFP
- > Up to 65 PPM Color
- > Up to 75 PPM B&W
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered*



e-STUDIO™ 5560c/6560c/6570c



* e-STUDIO6560c/6570c only.



- > Color MFP
- > Up to 65 PPM Color
- > Up to 75 PPM B&W
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered*

Specifications

Copying Process	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	4-Beam Color Laser (8 bit)
Copy/Print Resolution	600 x 600 dpi/1200 x 1200 dpi
Copy/Print Speed	e-STUDIO5560c – 55 PPM Color / 55 PPM B&W e-STUDIO6560c – 65 PPM Color / 65 PPM B&W e-STUDIO6570c – 65 PPM Color / 75 PPM B&W
Warm-Up Time	Approx. 180 Seconds
First Copy Out Time	e-STUDIO5560c – 6.5 Seconds Color / 5.3 Seconds B&W e-STUDIO6560c – 6.5 Seconds Color / 5.3 Seconds B&W e-STUDIO6570c – 6.5 Seconds Color / 4.6 Seconds B&W
Duty Cycle	225K / 250K / 275K Copies
Multiple Copying	Up to 9999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to 12" x 18" (17 lb Bond - 140 lb Index) Bypass: ST-R to 13" x 19" (17 lb Bond - 110 lb Cover) ST-R to 12" x 47" Banner (17 lb Bond - 110 lb Cover) LCF: LT (17 lb Bond - 140 lb Index)
Memory	Page + Main Memory: 2GB HD: 320GB FIPS 140-2 SED
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet Bypass (17 lb Bond - 110 lb Cover)
Control Panel	10.4" Color Super SVGA Tiltable LCD Touch Panel
Paper Supply	Up to 6,000-Sheet Input Capacity (Tandem Version + LCF) 4 Drawer Version: 4 x 540-Sheet Cassettes (2,160 Sheets) Tandem Version: 2 x 540-Sheet Cassettes + 2,320-Sheet LCF 100-Sheet Bypass Optional 1 x 2,500-Sheet LCF
Duplex	Standard Automatic Duplex Unit (17 lb Bond - 140 lb Index)
Dimensions	Approx. 38.6" x 27.5" x 60" (W x D x H) Weight Approx. 573 lb
CMYK Toner Yield	CMY: 29.5K, K: 77.4K
Power Supply	120 V, 20 Amps
Power Consumption	Maximum 2.2 kW

Print Specifications

PDL Support	PCL6 & PostScript 3
Operating Systems	Netware 6.x, Windows XP, Windows Server 2003, 2008, Vista, Citrix MetaFrame, Macintosh, Linux, UNIX
Protocol Support	IPX/SPX, TCP/IP, V4/V6 Dual Stack, Ethertalk, AppleTalk PAP, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100
Drivers	Windows 2000, Server 2003/2008/2012, Windows 7, 8, Vista, XP, Macintosh OS 10.4/10.5/10.6/10.7/10.8/10.9 UNIX, AS400 via iData & Port 9100, SAP R/3
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g/n Wireless LAN, USB
Device Management	TopAccess
Certification	Windows (XP, Vista, 7, 2003, 2008) (WHQL) Novell

Scan Specifications

Scan Resolution	Up to 600 dpi
Scan Speed	Up to 77 SPM Color / 77 SPM B&W
File Format	TIFF, PDF, JPEG, XPS

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH / MR / MMR /JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	500 MB Transmission, 200 MB Reception (HDD)
Memory Transmission	100 Jobs, 1,000 Destinations Max. 400 Destinations /Job
Scan Speed	.7 Seconds Per Page, Maximum 50 SPM

* e-STUDIO6560c/6570c only.

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

Security (Standard)

Data Encryption	256 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

Accessories (Options)

Additional Paper Options		
Large Capacity Feeder (LCF): 2,500-Sheet Drawer, Letter		MP2501
Finishing Options		
Multi-Position Finisher Stationary Tray: 250-Sheets		MJ1103
Finishing Tray: 3,000-Sheets		
Staple Capacity: 50 Sheets		
Saddle-Stitch Finisher Stationary Tray: 250-Sheets		MJ1104
Finishing Tray: 3,000-Sheets		
Staple Capacity: 50 Sheets		
Saddle Tray Stitcher: Up to 50 Sets		
Side Exit Tray		KA6570
Hole Punch Unit (for MJ1103/MJ1104) 2- or 3-Hole Punch Capability		MJ6102
Connectivity/Security Options		
EFI Controller		GA1310EX
Fax Board		GD1270NXF
2nd Line Fax		GD1260F
Wireless LAN Adapter		GN1060
Wireless Antenna		GN3010
IP SEC Enabler		GP1080
Meta Scan Enabler for e-CONNECT		GS1010
Advanced Scanning		GB1280T
Harness Kit for Coin Controller		GQ1200



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.