

Lexmark MS810 Series Monochrome Laser Printer

Built for Superior Performance.

Talk about a top performer. With blazing print speeds and multiple finishing styles, the Lexmark MS810 Series satisfies the needs of the busiest corporate offices. *Want 2-sided printing capability? Get the MS810dn. Need productivity solutions? Get the MS810de.*



Up to 55
ppm



Multiple
Media
Support



Finishing
Function



Solutions



Set the Pace for Increased Productivity.

Stay a step ahead by getting more work done faster. These super-efficient systems can meet your most demanding expectations.

Faster Processing - Improve your print speeds by taking advantage of up to 2.5 GB of upgradable memory, an 800 MHz dual-core processor and Gigabit Ethernet.

Reliable High Performance - Easily print up to 20,000 pages per month, plus enjoy fewer maintenance hassles, thanks to our state-of-the-art paper handling.

Keep Jobs Moving - With a maximum input capacity of up to 4,400 sheets and a high yield toner cartridge, you won't have to add paper or change cartridges as often.

Spend Less Time Waiting - Print up to 55 pages per minute, and produce your first page in as little as 4.8 seconds.

Look Professional. Work Smarter.

Produce documents that are presentation ready with optional automatic finishing that's based on your preferences. Our easy-to-use control panel makes everything simple.

Easy-to-use Displays - The bright 2.4-inch color display lets you stay on top of your work. Need more control and productivity solutions? Get the solutions-capable MS810de with the 4.3-inch color touch screen.

Finishing That Adds Polish - Produce projects like a pro with optional automated collating, stapling, and other finishing options.

Print on a Wide Range of Media - With built-in 2-sided printing⁷ and the ability to print on diverse materials, you can do more for your business and use less paper.

Innovative Toner Optimizes Performance - Get greater system performance with Lexmark's Unison™ Toner, which delivers consistent quality from first print to last.

Intelligent Workflow. Secure Design.

Our advanced system simplifies your work processes and increases productivity. Innovative security capabilities provide maximum protection for your critical business data.

Print Anytime and Anywhere⁶ - With this system, you can print from desktops as well as mobile devices that can run applications.


Enjoy Enterprise-level Security - Now you can authenticate, authorize and audit employee usage. Plus, you can protect sensitive data using standard network security protocols, data encryption and disk wiping capabilities.

Identify Potential Risks - Track more than 100 variables and events, including user activity, with Audit Logging. It's designed to work with your intrusion detection system in real time.

Optional Productivity Solutions - Want to empower your business with workflow solutions that can print on demand, automate tasks and more? Get the solutions-capable MS810de.

LEXMARK
TM

Lexmark MS810 Series Monochrome Laser Printer



Standard
 Optional

Product specifications	Lexmark MS810n	Lexmark MS810dn	Lexmark MS810de
Printing			
Display	2.4-inch color LCD display	2.4-inch color LCD display	Lexmark e-Task 4.3-inch (10.9 cm) color touch screen
Print Speed: Up to ¹		Black: 55 ppm	
Time to First Page: As fast as		Black: 4.8 seconds	
Print Resolution		Black: 1200 Image Quality, 1200 x 1200 dpi, 2400 Image Quality, 600 x 600 dpi	
Memory / Processor		Standard: 512 MB / Maximum: 2560 MB / Processor: Dual Core, 800 MHz	
Hard Disk		Option available	
Recommended Monthly Page Volume ²		3000 - 20000 pages	
Maximum Monthly Duty Cycle: Up to ³		250000 pages per month	
Supplies⁵			
Laser Cartridge Yields		6,000 ¹ -page Cartridge, 25,000 ¹ -page High Yield Cartridge	
Cartridge(s) Shipping with Product		10,000 ¹ -page Starter Return Program Toner Cartridge	
Paper Handling			
Included Paper Handling	550-Sheet Input, 100-Sheet Multipurpose Feeder, 550-Sheet Output Bin	550-Sheet Input, 100-Sheet Multipurpose Feeder, 550-Sheet Output Bin, Integrated Duplex	550-Sheet Input, 100-Sheet Multipurpose Feeder, 550-Sheet Output Bin, Integrated Duplex
Optional Paper Handling	250-Sheet Tray, 550-Sheet Tray, 2100-Sheet Tray, 250-Sheet Lockable Tray, 550-Sheet Lockable Tray, 4-Bin Mailbox, Staple Finisher, 1500-Sheet High Capacity Output Expander, 500-Sheet Output Expander		
Paper Input Capacity: Up to	Standard: 650 pages 20 lb or 75 gsm bond / Maximum: 4400 pages 20 lb or 75 gsm bond		
Paper Output Capacity: Up to	Standard: 550 pages 20 lb or 75 gsm bond / Maximum: 2550 pages 20 lb or 75 gsm bond		
Media Types Supported	Card Stock, Dual Web Labels, Envelopes, Integrated Labels, Paper Labels, Plain Paper, Transparencies, Refer to the Card Stock & Label Guide		
Media Sizes Supported	10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, Executive, Folio, JIS-B5, Legal, Letter, Statement, Universal, Oficio, A6		
General			
Standard Ports	One Internal Card Slot, USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified Port (Type A)	One Internal Card Slot, USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified Port (Type A)	One Internal Card Slot, USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified Port (Type A), Rear USB 2.0 Specification Hi-Speed Certified Port (Type A)
Optional Network Ports / Optional Local Ports	Internal MarkNet N8350 802.11b/g/n Wireless / Internal RS-232C serial, Internal 1284-B Bidirectional Parallel		
Noise Level, Operating	Printing: 57 dBA	Printing: 57 dBA	Printing: 58 dBA
Product Warranty	1-Year Exchange Service, Next Business Day		
Size (in. - H x W x D) / Weight (lb.)	16.5 x 16.7 x 20.1 in. / 52.2 lb.	16.5 x 16.7 x 20.1 in. / 52.2 lb.	16.5 x 16.7 x 20.1 in. / 52.3 lb.

¹ Average standard page yield value declared in accordance with ISO/IEC 19752. ² "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³ "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴ Print and copy speeds measured in accordance with ISO/IEC 24734, excludes first set of test documents. For more information see: www.lexmark.com/ISOspeeds. ⁵ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁶ For more information on Lexmark Mobile Solutions see: http://www1.lexmark.com/en_US/solutions/business-solutions/mobile-print/index.shtml ⁷ Duplex (2-sided printing) models are ENERGY STAR compliant.



Lexmark and Lexmark with the diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. All other trademarks are the property of their respective owners. ENERGY STAR® is a U.S. registered mark. Information in this document is subject to change without notice. Unison is a trademark of Lexmark International, Inc.

