

**TOSHIBA**  
Leading Innovation >>>

- > Color MFP
- > 30 PPM Color
- > Medium Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Features

**e-STUDIO™ 3040CG**





- > Color MFP
- > 30 PPM
- > Medium Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Features

**Specifications**

Copying Process	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	4-Beam Color Laser (8 bit)
Copy/Print Resolution	600 x 600 dpi (2,400 x 600 dpi B&W)
Copy/Print Speed	30 PPM Color / B&W
Warm-Up Time	Approx. 99 Seconds
First Copy Out Time	8.4 Seconds Color / 6.5 Seconds B&W
Duty Cycle	60K
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to LD (17 lb Bond - 140 lb Index) Bypass: ST-R to 12" x 47" (17 lb Bond - 100 lb Cover) PFP: ST-R to LD (17 lb Bond - 140 lb Index) LCF: LT (17 lb - 28 lb Bond)
Memory (Max)	Main Memory: 1 GB Page Memory: 512 MB HD: 80 + GB
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet "Smart" Bypass (17 lb Bond - 100 lb Cover)
Control Panel	Color 8.5" WVGA Tiltable LCD Touch Panel
Paper Supply	Up to 3,700-Sheet Input Capacity Standard 2 x 550-Sheet Cassettes 100-Sheet Bypass Optional 1 x 550-Sheet PFP, 1 x 550-Sheet Cassette 1 x 2,500-Sheet LCF
Duplex	Standard Trayless Automatic Duplex Unit (17 lb Bond - 140 lb Index)
Dimensions	Approx. 30" x 28" x 29" (W x D x H)
Weight	Approx. 267 lb
Minimum Footprint Req.	39.53" x 28.31" (W x D)
CMYK Toner Yield	CMY: 26.8K, BK: 34.2K
Power Supply	115 V, 15 Amps
Power Consumption	Maximum 1.5 kW

**Print Specifications**

PDL Support	PCL6 and PostScript 3
Operating Systems	Netware 6.x, Windows XP, Windows Server 2003, 2008, Citrix MetaFrame, Macintosh, Linux, UNIX
Protocol Support	IPX/SPX, TCP/IP, EthernTalk, AppleTalk, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
Drivers	Windows 2000, Server 2003/2008-Windows 7, XP Macintosh 10.1/10.2/10.3, 10.4, 10.5 UNIX, AS400 via iData & Port 9100, SAP R/3
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g Wireless LAN, USB, Bluetooth (HCRP)
Device Management	TopAccess
Certification	Windows (XP, Vista, 7, 2003, 2008) (WHQL) Novell

**Scan Specifications**

Scan Resolution	100 dpi, 150 dpi, 200dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	57 SPM Color / 57 SPM B&W (@ 300 dpi)
File Format	TIFF, PDF, Secure PDF, Slim PDF, JPEG, XPS

**Facsimile Specifications**

Compatibility	Super G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Memory Transmission	100 Jobs, 1,000 Destinations Max. 400 Destinations / Job
Scan Speed	.7 Seconds Per Page, Maximum 55 SPM

**E-Filing Specifications**

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

**Security (Standard)**

Data Encryption	128 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

**Accessories (Options)**

**Additional Paper Options**

RADF: 100 Sheets  
Paper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger  
Cassette Module :550-Sheet Pedestal, Statement-R to Ledger  
Large Capacity Feeder (LCF): 2,500-Sheet Drawer, Letter

**Finishing Options**

Multi Position Finisher: Stationary Tray: 250-Sheets (Lt)  
Tray 1 Stack Capacity: 2,500 Sheets (Lt)  
Staple Capacity: 50 Sheets  
Saddle-Stitch Finisher: Stationary Tray: 250-Sheets (lt)  
Tray 1 Stack Capacity: 3,000 Sheets (Lt)  
Staple Capacity: 50 Sheets  
60 Pages (15 Sheets) SS Booklets  
Hanging Finisher  
1 Tray: 1,000 Sheets (Lt)  
Staple Capacity: 50 Sheets  
Multi-Position Hole Punch Unit (for MJ1101, MJ1106)

**Connectivity/Security Options**

Bridge Kit Required with MJ1101, MJ1106, MJ1031  
EFI Controller (not available at launch)  
Fax Board  
2nd Line Fax  
Wireless LAN Adapter  
Bluetooth Adapter  
Wireless Antenna  
Meta Scan Enabler for e-CONNECT  
IP SEC Enabler  
Advanced Scanning

**Miscellaneous Options**

SmartCard Reader, HID iClass  
SmartCard Reader, HID Prox  
SmartCard Reader, Inditag  
SmartCard Reader, LEGIC  
SmartCard Reader, Multi ISO/Mifare  
SmartCard Reader, Multi 125  
Harness Kit for Coin Controller



<b>Corporate Office</b>	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
<b>East Coast</b>	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
<b>Midwest</b>	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
<b>South</b>	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
<b>West Coast</b>	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
<b>Web Site</b>	www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.