

- > Color MFP
- > 55 PPM Color
- > 55 PPM B&W
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Features

e-STUDIO™ 5540cG





- Color MFP
- 55 PPM Color
- 55 PPM B&W
- Med/Large Workgroup
- Copy, Print, Scan, Fax
- Secure MFP
- Eco Features

Specifications

Copying Process	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	4-Beam Color Laser (8 bit)
Copy/Print Resolution	600 x 600 dpi/1200 x 1200 dpi
Copy/Print Speed	55 PPM Color / 55 PPM B&W
Warm-Up Time	Approx. 180 Seconds
First Copy Out Time	6.5 Seconds Color / 5.3 Seconds B&W
Duty Cycle	225K
Multiple Copying	Up to 9999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to 12" x 18" (17 lb Bond - 140 lb Index) Bypass: ST-R to 13" x 19" (17 lb Bond - 110 lb Cover) ST-R to 12" x 47" Banner (17 lb Bond - 110 lb Cover) LCF: LT (17 lb Bond - 140 lb Index)
Memory (Min/Max)	Page + Main Memory: 2 GB, PowerPC 1.5 GHz Processor HD: 80+ GB
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet Bypass (17 lb Bond - 110 lb Cover)
Control Panel	10.4 Color Super SVGA Tilttable LCD Touch Panel
Paper Supply	Up to 6,000-Sheet Input Capacity (Tandem Version + LCF) 4 Drawer Version: 4 x 540-Sheet Cassettes (2,160 Sheets) Tandem Version: 2 x 540-Sheet Cassettes + 2,320-Sheet LCF 100-Sheet Bypass Optional 1 x 2,500-Sheet LCF
Duplex	Standard Automatic Duplex Unit (17 lb Bond - 140 lb Index)
Dimensions	Approx. 38.582" x 27.480" x 60.629" (W x D x H) Weight Approx. 573 lb
CMYK Toner Yield	CMY: 29.5K, K: 77.4K
Power Supply	120 V, 20 Amps
Power Consumption	Maximum 2.2 kW

Print Specifications

PDL Support	PCL6 & PostScript 3
Operating Systems	Netware 6.x, Windows XP, Windows Server 2003, 2008, Vista, Citrix MetaFrame, Macintosh, Linux, UNIX
Protocol Support	IPX/SPX, TCP/IP, V4/V6 Dual Stack, EtherTalk, AppleTalk PAP, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
Drivers	Windows 2000, Server 2003/2008-Windows 7, Vista, XP Macintosh OS 10.1/10.2/10.3, 10.4, 10.5 (OS 10.4 PPD)
Connectivity	UNIX, AS400 via iData & Port 9100, SAP R/3 10/100/1000BaseTX Ethernet, 802.11b/g Wireless LAN, USB, Bluetooth (HCRP)
Device Management	TopAccess
Certification	Windows (XP, Vista, 7, 2003, 2008) (WHQL) Novell

Scan Specifications

Scan Resolution	Up to 600 dpi
Scan Speed	Up to 77 SPM Color / 77 SPM B&W
File Format	TIFF, PDF, JPEG, XPS

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	500 MB Transmission, 200 MB Reception (HDD)
Memory Transmission	100 Jobs, 1,000 Destinations Max. 400 Destinations / Job
Scan Speed	.7 Seconds Per Page, Maximum 50 SPM

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

Security (Standard)

Data Encryption	128 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

Accessories (Options)

Additional Paper Options

Large Capacity Feeder (LCF): 2,500-Sheet Drawer, Letter

Finishing Options

Multi-Position Finisher Stationary Tray: 250-Sheets
Finishing Tray: 3,000-Sheets
Staple Capacity: 50 Sheets
Saddle-Stitch Finisher Stationary Tray: 250-Sheets
Finishing Tray: 3,000-Sheets
Staple Capacity: 50 Sheets
Saddle Tray Stitcher: Up to 50 Sets
Side Exit Tray
Hole Punch Unit (for MJ1103/MJ1104) 2- or 3-Hole Punch Capability

Connectivity/Security Options

EFI Controller (not available at launch)
Fax Board
2nd Line Fax
Wireless LAN Adapter
Bluetooth Adapter
Wireless Antenna
IP SEC Enabler
Meta Scan Enabler for e-CONNECT
Advanced Scanning

Miscellaneous Options

SmartCard Reader, HID iClass
SmartCard Reader, HID Prox
SmartCard Reader, Inditag
SmartCard Reader, LEGIC
SmartCard Reader, Multi ISO/Mifare
SmartCard Reader, Multi 125
Harness Kit for Coin Controller



Corporate Office

9740 Irvine Blvd., Irvine, CA 92618
Tel: 949-462-6000

East Coast

959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700

Midwest

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
Tel: 773-380-6000

South

2037 Bakers Mill Rd., Dacula, GA 30019
Tel: 678-546-9385

West Coast

9740 Irvine Blvd., Irvine, CA 92618
Tel: 949-462-6000

Web Site

www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.