

**TOSHIBA**  
Leading Innovation >>>

- > Black & White MFP
- > Up to 120 PPM
- > Departmental Workgroup
- > Copy, Print, Scan
- > Secure MFP
- > Eco Features



**e-STUDIO™ 907/1057/1207**





- > Black & White MFP
- > Up to 120 PPM
- > Departmental Workgroup
- > Copy, Print, Scan
- > Secure MFP
- > Eco Features

Main Specifications			
e-STUDIO907/1057/1207	Base Models Include LCD, 250-Sheet DSPF, 3,000-Sheet Paper Capacity (Two Tandem 2,000-Sheet Trays/Two 500-Sheet Trays), 1-TB Hard Disk Drive, PCL6/Adobe® Postscript® 3™ Network Printing, Color Network Scanning, And Retractable Keyboard		
Type	Console, Monochrome Multi-Function Digital Document System		
Display	10.1" (Diagonally Measured) Color Dot Matrix High-Resolution Touch Panel Tilting Display 1024 x 600 Dots (W-SVGA)		
Functions	Copy, Print, Network Print, Network Scan, And Document Filing		
Copy System	Dry Electrostatic Transfer/Dual Component Developer/Magnetic Brush Development/OPC/White LED Exposure/Heat Roller Fusing		
Max Original Size	11" x 17"		
Copy Size	Min. 5.5" x 8.5", Max. 11" x 17" + 12" x 18"		
Copy Speed	90/105/120 PPM (8.5" x 11")		
Multiple Copy	Max. 9999 Copies		
First Copy Time (In Seconds) <sup>2</sup>	e-STUDIO907	e-STUDIO1057	e-STUDIO1207
	Platen Glass	4.0	3.2
	DSPF	6.3	5.5
Warm Up Time	210 Seconds		
Magnification	25% to 400% in 1% Increments (with Document Feeder 25%-200%)		
Original Feed	250-Sheet DSPF		
Scan Speed	DSPF Scan: Up to 200 (Monochrome or Color)		
Original Sizes	5.5" x 8.5", 8.5" x 11", 8.5" x 11" R, 8.5" x 14", 11" x 17"		
Paper Capacity	Std. 3,000 Sheets/Max. 13,500 Sheets		
Paper Feed Sizes	Standard: Tandem Tray 1 - 1200 Sheets (Letter Size), Tandem Tray 2 - 800 Sheets (Letter Size), Trays 3/4 - 500 Sheets Ea. (Letter/Legal/Ledger/Statement/12" x 18"), Optional: Multi-Bypass Tray (for Machine) - 100 Sheets (Letter/Legal/ Ledger/Statement/ 12" x 18"), Multi-Bypass (for LCT) - 500 Sheets (Letter/Legal/ Ledger/ Statement/12" x 18"), LCT (2-Drawer) - 2,500-Sheets Each Drawer (Letter/Legal/Ledger/12" x 18"), Letter LCC - 3,500 Sheets (Letter), Ledger LCC (e-Studio907 Only): 3,000 Sheets (Letter/Legal/Ledger)		
Paper Weights And Types	Tandem Trays - 16-28 lb Bond, Trays 3/4 - 16 lb Bond to 100 lb Bristol, Multi-Bypass Tray (for Machine) - 15 lb Bond to 110 lb Cover, Multi-Bypass Tray (for LCT) - 15 lb Bond to 100 lb Bristol, LCT (2-Drawer) - 15 lb Bond to 110 lb Cover, Letter LCC/Ledger LCC - 16 lb Bond to 100 Bristol. Supported Paper Types Include Thin, Plain, Recycled, Color, Letter Head, Pre-Printed And Pre-Punched, Embossed and Glossy		
Duplexing	Standard Automatic Duplex Copying and Printing		
Cpu	Up to 1.8 GHz Multi-Processor Controller		
Interface	RJ-45 Ethernet (10/100/1,000 Base-T), USB 2.0 (2 Host Ports, Front and Rear), USB 2.0 (1 Device Port)		
Memory	Standard 5 GB		
Hard Disk Drive	1 TB		
Copy Resolution	Scan: 1200 x 1200 dpi / 600 x 600 dpi		
Exposure Control	Modes: Text, Text/Printed-Photo, Printed-Photo, Text Photo, Photo, Map, Pale-Color. Settings: Auto or 9 Step Manual		
HalfTone	256 Gradations/2 Levels (Monochrome)		
Copy Features	Electronic Sort, Auto Paper Selection (APS), Auto Magnification Selection (AMS), Image Preview/Edit, Auto Tray, Paper Type Selection Switching, Rotate Copy, Reserve Copy, Tandem Copy, Book Copy, Margin Shift, Edge/Center Erase, Book Divide, Dual Page, Cover/Insert Page, OHP Insert, Job Build, Card Shot, Blank Page Skip, Mirror/B/W Reverse, Proof, Pamphlet, Watermark, Custom Image, Job Programs		
Account Control	Up to 1,000 Users, Supports User-Number Authentication (On Device), Login Name/ Password or Login Name/Password (Via LDAP Server) for Copy, Print, Scan, Fax and Document Management		
Accessibility Features	Tilt Front Panel, Adjustment of Key Touch, Document Feeder Free Stop, Job Programs, Remote Front Panel, Universal Grip for Paper Trays, and Disable Screen Timeout		
Environmental Standards	International Energy Star Program Ver. 1.2, Law on Promoting Green Purchasing, European ROHS (Restriction of Hazardous Substances)		
Power Source	AC 208-240 VAC, 60 Hz, 15 Amps		
Power Consumption	Maximum: 3.5 kW or Less		
Weight	Approx. 650 lb		
Approx. Dimensions	42.75" (W) x 31.25" (D) x 48.75" (H)		
Network Printing System (Standard)			
PdL	PCL® 6 Compatible, True Adobe®, Postscript®		
Resolution	1200 x 1200 dpi		
Print Speed	90/105/120 Pages Per Minute (8.5" x 11")		
Print Drivers	Windows Server® 2003-2008, Windows XP, Windows XP x64, Windows Server 2003-2008 x64, Windows Vista®, Windows Vista® x64, Windows 7, Windows 7 x64, Mac OS X (Including 10.4.11, 10.5-10.5.8, 10.6.5-10.6.8, 10.7-10.7.2), All Mac PPD		
Features	Auto Configuration, Continuous Printing, Electronic Sorting, N-Up Printing, Duplex Printing, Transparency Inserts, Margin Shift, Image Rotation, Different Cover Page, Poster Print, Job Bypass Print, Job Retention, Confidential Print, Proof Print, User Authentication, Image Stamp and Watermarks. Additional Features: Multiple Pamphlet Print, Network Tandem Print, Carbon Copy Print Mode, Different Cover Page/Last Page/Other Page, form Overlay, Tab Paper Settings, Tab Printing, Chapter Inserts and Page Interleave		
Direct Printing	File Types: TIFF, JPEG, PCL, PRN, TXT, PDF, Encrypted PDF, Compressed PDF/A, and Postscript. Methods: FTP, Web Page, E-Mail, Network Folder & USB		
Resident Fonts	80 Outline Fonts (PCL), 136 Fonts (PS)		
Interface	RJ-45 Ethernet 10/100/1,000 Base-T, USB 2.0		
Operating Systems	Windows Server 2003-2008, Windows XP, Windows Vista, Windows 7, Mac OS 9-9.2.2, Mac OS X 10.2.8, 10.3.9, 10.4.11, 10.5-10.5.8, 10.6-10.6.5, Novell® Netware® 3x, 4x, 5x, Sun® OS 4.1x, Solaris® 2x, Unix®, Linux® and Citrix® (Metaframe, Presentation Server 4, 4.5) and Windows Terminal Services		
Network Protocols	TCP/IP (IPv4, IPv6, IPsec) SSL (HTTP, IPP, FTP), SNMPv3, SMTP, POP3, LDAP, 802.1x for Windows and Unix. LXD and LPR for Unix. IPX/SPX® for Novell Environments and EtherTalk®, AppleTalk® for Macintosh® Environments		
Printing Protocols	LPR, IPP, IPPS, PAP, Raw TCP (Port 9100), FTP and Novell Pserver/Rprinter		
Network Security	IP/Mac Address Filtering, Protocol Filtering, Port Management, User Authentication and Document Administration		
Security Standards	IEEE-2600TM-2008, DoD (NSTISSP) #11, DoD Directive 8500.2, DoD (DISA)		
Network Scanning System (Standard)			
Scan Modes	Standard: Color, Monochrome, Grayscale		
Max. Original Size	11" x 17"		
Optical Resolution	600 dpi		
Output Modes	600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi		
Image Formats	Monochrome: TIFF, PDF, Encrypted PDF, XPS, PDF/A Color/Grayscale: Color TIFF, JPEG, PDF, Encrypted PDF, PDF/A, Compressed PDF		
Network Protocols	TCP/IP & SSL (Includes HTTP, SMTP, LDAP, FTP, POP3), SMB, ESMTS & 802.1x		
Network Security	E-Mail Server User Authentication for LDAP and Active Directory		

100-Sheet Stapler/Finisher (MX-FN21: Option)	
Type	4,000-Sheet Console Stapler Finisher (100-Sheet Stapling)
Output Trays	Upper Tray: Moving Offset Tray (Up to 1,500 Letter Size Sheets) Middle Tray: 250 Sheets (Letter Size, Non-Stapled) Lower Tray: Moving Offset Tray (Up to 2,500 Letter Size Sheets)
Stapling Capacity	Up to 100 Sheets (Letter/Statement)
Stapling Media	Plain Paper, Letter/Legal/Ledger Size or Mixed
Stapling Positions	1 Front, 1 Rear, or 2 Point Stitching
Hole Punching	Optional Three-Hole Punch Unit MX-PN13B
Power Source	120 VAC, 60 Hz, 15 Amps
Power Consumption	200W/350W with MX-MF10
Weight	Approx.: 134.5 lb
Dimensions	Approx.: 30.75" (W) x 30" (D) X 41" (H) (with Tray Extended)
100-Sheet Stapler/Saddle Stitch Finisher (MX-FN22: Option)	
Type	4,000-Sheet Console Stapler Finisher (100-Sheet Stapling)
Output Trays	Upper Tray: Moving Offset Tray (Up to 1,500 Letter Size Sheets) Middle Tray: 250 Sheets (Letter Size, Non-Stapled) Lower Tray: Moving Offset Tray (Up to 2,500 Letter Size Sheets)
Stapling Capacity	Up to 100 Sheets (Letter/Statement)
Stapling Media	Plain Paper, Letter/Legal/Ledger Size or Mixed
Stapling Positions	1 Front, 1 Rear, or 2 Point Stitching
Saddle Stitch	Center Stitch/Center Fold (2 Staples) Letter/Legal/Ledger Paper Sizes
Saddle Stitch Max. Sets	Up to 5 Sets (16-20 Sheets Per Set)/10 Sets (11-15 Sheets Per Set)/15 Sets (6-10 Sheets Per Set)/25 Sets (1-5 Sheets Per Set)
Hole Punching	Optional Three-Hole Punch Unit MX-PN13B
Power Source	120 Vac, 60 Hz, 15 Amps
Power Consumption	200W/350W with MX-MF10
Weight	Approx.: 134.5 lb
Dimensions	Approx.: 30.75" (W) x 30" (D) x 41" (H) (with Tray Extended)
Inserter (MX-CF11 Option)	
Type	Standing, 2 Trays
Paper Capacity	Upper Tray: 200 Sheets, Lower Tray: 200 Sheets (20 lb Bond)
Paper Weight	16 lb Bond to 100 lb Bristol (Paper Feeding)
Paper Size	Up to 12" x 18"
Power Consumption	70 W or Less
Power Source	24 Volts (Supplied by Main Unit)
Dimensions	21.5" (W) x 30" (D) x 50.5" (H)
Weight	Approx. 51 lb
Multi-Folding Unit (MX-FD10 Option)	
Type	Floor Standing
Dimensions	13.5" (W) x 30.5" (D) x 41.5" (H)
Weight	Approx. 146 lb
Power Source	Powered by MX-FN21/FN22 Finisher
Power Consumption	Maximum: Standby: 23 W or Less, in Operation: 150 W or Less
Folding Mode	Z-Fold, C-Fold, Accordion-Fold, Double-Fold and Half-Fold
Optional Equipment	
MX-MFX1	Bypass Tray for Main Unit
MX-LC12	A4LCC
MX-LCX3N	A3LCC
MX-RB16	Relay Unit for LCT
MX-LC13	A3LCT
MX-MF11	Bypass Tray for A3LCT
MX-RB18	Curl Correction Unit
MX-CF11	Inserter
MX-RB13	Relay Unit
MX-FD10	Paper Folding Unit
MX-FN21	100 Staple FN
MX-FN22	100 Staple Saddle Stich FN
MX-PN13B	Punch Unit for FN21/22
MX-RB17	Connection Kit for LCT
MX-SL10N	Status Indicator
MX-ST10	Stacker
MX-CA10	Paper Cart for Stacker
MX-FN24	50 Staple FN
MX-FN25	50 Staple Saddle Stich FN
MX-PNX4B	Punch Unit for FN24/25
MX-TM10	Trimmer Unit for MX-FN22
MX-EB11	Enhanced Compression Kit
MX-EB15	Mirroring Kit
Supplies	
T1207U	Toner Cartridge (Yield 120K @ 5%)
6LS00016000	Developer D1207
Staple2000	Staple Cartridge (for MX-FN24/FN25)
Staple3100	Staple Cartridge (for MX-FN25 - Saddle)
Staple2400	Staple Cartridge (for MX-FN22 - Saddle)
Staple2600	Staple Cartridge (for MX-FN21/FN22)



Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631	949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054	973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631	773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019	678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618	949-462-6000
Website	www.business.toshiba.com	