

- > Up to 30 PPM
- > Black & White MFP
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly





- > Black & White MFP
- > Up to 30 PPM
- > Sml/Med Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly

Specifications

Copying Process/Type	IEPM (Dry Process)/Laser Technology
Original Reading Method	CCD Line Sensor
Copy/Print Resolution	2400 x 600 dpi (with Smoothing)
Copy/Print Speed	20 / 25 / 30 ppm
Warm-Up Time	Appx. 20 Seconds
First Copy Time	4.7 Seconds
Duty Cycle	80K / 100K / 120K
Multiple Copying	Up to 999 Copies
Standard Paper Supply	2 x 550-Sheet, 100-Sheet Stack Feed Bypass
Maximum Paper Supply	Up to 3,200 Sheets
Acceptable Paper Size	Cassette: Statement-R to Ledger (17-28 lbs.); Bypass: Statement-R to Ledger (17-110 lbs.); LCF: Letter (17-28 lbs.)
Special Paper	Bypass: Envelope, Tab Sheet
Memory	1GB RAM, 60 GB HDD
Reduction/Enlargement	25% to 400%
Bypass Tray	100-Sheet Stack Feed Bypass
Control Panel	9" Wide VGA Color Touch-Screen
Dimensions	Appx. 23" x 23" x 30" (W x D x H)
Weight	Appx. 132 lbs.
Power Supply	115 Volts; 15 Amps
Power Consumption	Maximum 1.5kW
PM Cycle	80K / 100K / 120K
Black Toner Yield	36.6K Impressions @ 6%
Drum Type/Yield	Organic Photoconductor; 80K / 100K / 120K
Developer Yield	80K / 100K / 120K

Print (Standard)

Print Speed	20 / 25 / 30 ppm
PDL Support	PCL6, PostScript3, XPS
Operating Systems	Windows 2000/XP/2003/Vista/2008/7; Mac X OS10.2.4/10.3/10.4/10.5; UNIX, Linux, CUPS
Protocol Support	IPX/SPX, TCP/IP (IPv4/IPv6), EtherTalk, AppleTalk PAP, LPR/LPD, IPP w/Authentication, SMB, Netware
Drivers	Windows 2000/XP/2003/Vista/2008/7; Mac X OS 10.2.4/10.3/10.4/10.5 (OS 10.4 PPD); UNIX, Linux, AS/400, SAP R/3
Connectivity	Ethernet 10/100/1000BaseT, USB 2.0, 802.11b/g Wireless LAN
Device Management	TopAccess
Certification	WHQL, Novell, HPOS (Dazel), Vista Premium

Scan (Standard)

Scan Speed	57 spm LT-Size @ 300 dpi, 45 spm LT-Size @ 600 dpi when copying, 43 spm LT-Size @ 300 dpi (Color Scanning)
Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
File Format	TIFF, PDF, Slim PDF, JPEG, XPS MS Word, MS Excel, Searchable PDF w/Adv. Scanning option

E-Filing (Standard)

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box; 200 Private User Boxes
Capacity of Boxes	100 Folder per Box; 400 Documents per Folder; 1000 Pages per Documents

Security (Standard)

Data Encryption	256 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

Facsimile Option

Compatibility	Super G3, G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Appx. 3 Seconds per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	Transmission and Reception 1GB (HDD); Backup Permanent (HDD)
Memory Transmission	100 Jobs, 2,000 Destinations Max; 400 Destinations/Job
Scan Speed	0.7 Seconds per Page; 50 Scans per Minute
Other Fax Functions	Internet Fax; Network Fax

Accessories (Options)

Input Options	
100-Sheet RADF	MR3021
Platen Cover	KA1640PC

Additional Paper Options

550-Sheet Paper Feed Pedestal	KD1025
2,000-Sheet Large Capacity Feeder	KD1026
550-Sheet Paper Feed Unit	MY1033

Finishing Options

Job Separator	MJ5004
Work Tray	KK4550
Bridge Kit for Finisher	KN2520
50-Sheet Inner Finisher	MJ1032
Saddle-Stitch Finisher (low capacity)	MJ1033
2 or 3 Hole Punch Unit for MJ1032	MJ6007
2 or 3 Hole Punch Unit for MJ1033	MJ6008

Connectivity/Security Options

Fax Kit	GD1250NXF
2nd Line Fax	GD1260F
IPSec Enabler	GP1080
Wireless LAN Adapter	GN1060
Antenna	GN3010
Meta Scan Enabler	GS1010
Advanced Scanning	GB1280T

Miscellaneous Options

SmartCard Reader, HID iClass	ART11236
SmartCard Reader, HID Prox	ART11230
SmartCard Reader, Inditag	ART12161
SmartCard Reader, LEGIC	ART11248
SmartCard Reader, Multi ISO/Mifare	ART11443
SmartCard Reader, Multi 125	ART11242
Card Reader Bracket	6BC02231846
Accessible Arm Handle	KK2550
Harness Kit for Coin Controller	GQ1180



Corporate Office	2 Musick, Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-3136-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	142 Technology, Suite 150, Irvine, CA 92618 Tel: 949-462-6262
Web Site	www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.