

Product Configuration



Input Options

1	100-Sheet RADF (Reversing Automatic Document Feeder)	MR3021
2	Platen Cover	KA1640PC

Paper Options

3	550-Sheet Paper Feed Pedestal	KD1025
4	2,000-Sheet Large Capacity Feeder	KD1026
5	550-Sheet Paper Feed Unit (use with 3)	MY1033

Finishing Options

6	Offset Tray	MJ5005
7	Job Separator	MJ5004
8	Bridge Kit (required with 10)	KN2520
9	50-Sheet Inner Finisher	MJ1032
10	Saddle-Stitch Finisher	MJ1033
11	2 or 3 Hole Punch Unit (use with 9)	MJ6007
12	2 or 3 Hole Punch Unit (use with 10)	MJ6008

Other Options

13	Work Tray	KK4550
14	Stand	STAND355/455

Advanced Printing Features

SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540

Advanced Scanning Features

Advanced Scanning (OCR Conversion Software)	GB1280T
---	---------

Connectivity Options

Fax Kit	GD1250NXF
2nd Line Fax	GD1260F
IPSec Enabler	GP1080
Wireless LAN Adapter	GN1060
Antenna	GN3010
Meta Scan Enabler	GS1010

Miscellaneous Options

SmartCard Reader, HID iClass	ART11236
SmartCard Reader, HID Prox	ART11230
SmartCard Reader, Inditag	ART12161
SmartCard Reader, LEGIC	ART11248
SmartCard Reader, Multi ISO/Mifare	ART11443
SmartCard Reader, Multi 125	ART11242
SmartCard Authentication - Demo Only (10 Pack)	KP2004-CDEMO
Bracket for Card Reader	6BC02231846
Accessible Arm Handle	KK2550
Harness Kit for Coin Controller	GQ1180

Supplies

Staples (for 9)	STAPLE2400
Staples - Saddlestitch (for 10)	STAPLE600
Toner	T4590
Developer	6LH58317000