

**e-STUDIO™ 2330c/2830c**

**The Color of Business.**  
**THE COLOR OF SUCCESS.**



**TOSHIBA**  
Leading Innovation >>>

# e-STUDIO™ 2330c/2830c

## SPECIFICATIONS

The Toshiba e-studio2330c/2830c are powerful, multifunction color copiers that combine the performance of a multifunction system with the quality of a professional graphics solution. Outstanding speed, performance, and professional-quality color as well as detailed text and graphics can be yours – every day, all the time. Thanks to Toshiba's proprietary print technology, the e-studio2330c/2830c devices are the ideal, most cost-effective graphic/business solution for the busiest offices.

The Color of  
**SUCCESS.**



Full-color output is produced at 23/28 PPM, with 28/35 PPM for black and white.



For the ultimate in flexibility — Print and scan, print and fax, even copy and scan — all at the same time.



Toshiba's easily replaceable unit (ERU) technology maximizes your MFP's uptime resulting in a lower cost of ownership.

### SPECIFICATIONS

<b>Copying Process</b>	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
<b>Copying Type</b>	4-Beam Color Laser (8-bit)
<b>Copy/Print Resolution</b>	600 x 600 dpi (2,400 x 600 dpi B&W)
<b>Copy/Print Speed</b>	e-STUDIO2330c – 23 PPM Color / 28 PPM B&W e-STUDIO2830c – 28 PPM Color / 35 PPM B&W
<b>Warm-Up Time</b>	Approx. 99 Seconds
<b>First Copy Out Time</b>	e-STUDIO2330c – 8.4 Seconds Color / 6.5 Seconds B&W e-STUDIO2830c – 8.4 Seconds Color / 6.5 Seconds B&W
<b>Duty Cycle</b>	46K, 56K
<b>Multiple Copying</b>	Up to 999 Copies
<b>Acceptable Paper Size and Weight</b>	Cassette: ST-R to LD (17 lb. Bond - 140 lb. Index) Bypass: ST-R to 12" x 47" (17 lb. Bond - 100 lb. Cover) PPF: ST-R to LD (17 lb. Bond - 140 lb. Index) LCF: LT (17 lb. - 28 lb. Bond)
<b>Memory (Max)</b>	Main Memory: 1 GB Page Memory: 512 MB HD: 80+ GB
<b>Reduction/Enlargement</b>	25% to 400%
<b>Bypass</b>	100-Sheet "Smart" Bypass (17 lb. Bond - 100 lb. Cover)
<b>Control Panel</b>	Color 8.5" WVGA Tilttable LCD Touch Panel
<b>Paper Supply</b>	Up to 3,700-Sheet Input Capacity Standard: 2 x 550-Sheet Cassettes 100-Sheet Bypass Optional: 1 x 550-Sheet PPF, 1 x 550-Sheet Cassette 1 x 2,500-Sheet LCF
<b>Duplex</b>	Standard Trayless Automatic Duplex Unit (17 lb. Bond - 140 lb. Index)
<b>Dimensions</b>	Approx. 30" x 28" x 29" (W x D x H)
<b>Weight</b>	Approx. 267 lb.
<b>Minimum Footprint Requirement</b>	39.53" x 28.31" (W x D)
<b>PM Cycle</b>	46K, 56K
<b>Drum Type/Yield</b>	Organic Photoconductor: 46,000/56,000
<b>CMYK Toner Yield</b>	CMY: 24,000/K: 29,000
<b>Black Developer Yield</b>	46,000/56,000
<b>Power Supply</b>	115 V, 15 Amps
<b>Power Consumption</b>	Maximum 1.5 kW

### PRINT SPECIFICATIONS

<b>PDL Support</b>	PCL6 and PostScript 3
<b>Operating Systems</b>	Netware 6.x, Microsoft Windows 2000/XP, Windows Server 2003, Vista, Citrix MetaFrame, Macintosh, Linux, UNIX
<b>Protocol Support</b>	IPX/SPX, TCP/IP, EtherTalk, AppleTalk, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
<b>Drivers</b>	Windows 2000, Server 2003, XP, Vista Macintosh 10.1/10.2/10.3/10.4/10.5 UNIX, AS400 via iData & Port 9100, SAP R/3
<b>Connectivity</b>	10BaseT/100BaseTX Ethernet, 802.11b/g Wireless LAN, USB, Bluetooth (HCRP)
<b>Device Management</b>	TopAccess
<b>Certification</b>	WHQL, Novell

### SCAN

<b>Scan Resolution</b>	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
<b>Scan Speed</b>	Up to 57 SPM
<b>File Format</b>	TIFF, PDF, Secure PDF, Slim PDF, JPEG, XPS
<b>Authentication</b>	LDAP, SMTP, Windows Domain

### FACSIMILE SPECIFICATIONS

<b>Compatibility</b>	Super G3
<b>Data Compression</b>	MH/MR/MMR/JBIG
<b>Transmission Speed</b>	Approx. 3 Seconds Per Page
<b>Fax Modem Speed</b>	33.6 Kbps
<b>Memory Transmission</b>	100 Jobs, 1,000 Destinations Max. 400 Destinations/Job
<b>Scan Speed</b>	.7 Seconds Per Page, 55 SPM

### e-FILING SPECIFICATIONS

<b>Operation Method</b>	Color Touch Screen Control Panel or Client PC
<b>Number of Boxes</b>	1 Public Box, 200 Private User Boxes
<b>Capacity of Boxes</b>	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

### OPTIONS

<b>MR3018</b>	<b>RADF</b>	100 Sheets
<b>KD1023</b>	<b>Paper Feed Pedestal</b>	550-Sheet Pedestal, Statement-R to Ledger
<b>MY1032</b>	<b>Cassette Module</b>	550-Sheet Drawer, Statement-R to Ledger
<b>KD1024</b>	<b>Large Capacity Feeder (LCF)</b>	2,500-Sheet Drawer, Letter
<b>MJ1101</b>	<b>Multi-Position Finisher</b>	Stationary Tray: 250 Sheets (Lt) Tray 1 Stack Capacity: 2,000 Sheets (Lt) Staple Capacity: 50 Sheets
<b>MJ1030</b>	<b>Saddle-Stitch Finisher</b>	Tray 1 Stack Capacity: 1,000 Sheets (Lt) Tray 2 Stack Capacity: 1,000 Sheets (Lt) Staple Capacity: 50 Sheets 60 Pages (15 Sheets) SS Booklets
<b>MJ1031</b>	<b>Hanging Finisher</b>	1 Tray: 1,000 Sheets (Lt) Staple Capacity: 50 Sheets
<b>MJ6101</b>	<b>Multi-Position Hole Punch Unit</b>	(for MJ1101)
<b>MJ6004</b>	<b>Multi-Position Hole Punch Unit</b>	(for MJ1030)
<b>KN4520</b>	<b>Bridge Kit</b>	Required with MJ1101, MJ1030, MJ1031
<b>GA1211</b>	<b>EFI Controller</b>	(not available at launch)
<b>GD1250</b>	<b>Fax Board</b>	
<b>GD1260</b>	<b>2nd Line Fax</b>	
<b>GN1050</b>	<b>Wireless LAN Adapter</b>	
<b>GN2010</b>	<b>Bluetooth Adapter</b>	
<b>GN3010</b>	<b>Wireless Antenna</b>	
<b>GP1070</b>	<b>Data Overwrite Kit</b>	
<b>GS1010</b>	<b>Meta Scan Enabler</b>	
<b>GP1080</b>	<b>IPsec Enabler</b>	
<b>KP2004</b>	<b>HID Card Reader</b>	
<b>KP2005</b>	<b>Mifare Card Reader</b>	
<b>STAND4520</b>	<b>Stand</b>	



Corporate Office: 2 Musick, Irvine, CA 92618-1631 / Tel: 949-462-6000  
 East Coast: 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 / Tel: 973-316-2700 Fax: 973-263-2393  
 Midwest: 8770 W. Bryn Mawr Ave., Suite 700, Chicago IL 60631 / Tel: 773-380-6000 Fax: 773-380-8077  
 South: 4855 Peachtree Industrial Blvd., Suite 210, Norcross, GA 30092 / Tel: 770-209-8540 Fax: 770-209-8556  
 West Coast: 142 Technology, Suite 150, Irvine, CA 92618 / Tel: 949-462-6262 Fax: 949-462-2700  
 Web Site: copiers.toshiba.com

©2008 Toshiba America Business Solutions, Inc., Electronic Imaging Division  
 e-STUDIO2330c/2830c Spec Sheet/Inv. Code ES2330c2830c2

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 6% coverage, letter-sized page. Driver and connectivity feature support varies by client/network operating system.

40M AUGUST 2008 USA NG

**TOSHIBA**  
 Leading Innovation >>>