

- > Up to 25 PPM
- > Color MFP
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered





- > Color MFP
- > Up to 25 PPM
- > Small/Medium Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered

Specifications

Copying Process	Indirect Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	LED Head Printing
Copy/Print Resolution	600 x 600 dpi/600 x 600 dpi, (600 x 1200 dpi, PS only)
Copy/Print Speed	e-STUDIO2050C~20 PPM Color/B&W e-STUDIO2550C~25 PPM Color/B&W
Warm-Up Time	Approx. 35 Seconds
First Copy Out Time	e-STUDIO2050C~10.3 Seconds Color/8.2 Seconds B&W e-STUDIO2550C~10.3 Seconds Color/8.2 Seconds B&W
Duty Cycle	56K/70K/Copies
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to LD (16lb Bond - 90lb Index) Bypass: 3.9" x 5.2" to LD (16lb Bond - 110lb Index) PFP: ST-R to LD (16lb Bond - 90lb Index) LCF: LT (17lb - 28lb Bond), Envelope (Bypass Only)
Memory (Max)	Main Memory: 2GB, SSD: 8GB 320GB FIPS 140-2 SED
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet "Smart" Bypass (16lb Bond - 110lb Index)
Control Panel	Color 9" LCD Touch Panel
Paper Supply	Up to 2,900-Sheet Input Capacity Standard 250-Sheet Cassettes, 100-Sheet Bypass Optional 1 x 550-Sheet PFU (2nd Cassette) 1 x 550-Sheet PFP (3rd Cassette) 1 x 550-Sheet Cassette (4th Cassette) for PFP Optional 1 x 2,000-Sheet LCF
Duplex	Standard Automatic Duplex Unit (16lb Bond - 90lb Index)
Dimensions	Approx. 22.6" x 23.2" x 26.1" (W x D x H)
Weight	Approx. 125.7lb
CMYK Toner Yield	6% Coverage, CMY: 28K, BK: 32K
Power Supply	120 V, 12 Amps
Power Consumption	Maximum 1.5 kW

e-BRIDGE Print Specifications

PDL Support	PCL6, PostScript 3, XPS
Operating Systems	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO
Protocol Support	Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP
Drivers	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB
Wireless Device	AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)
Device Management	Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software)
Certification	Windows 7, 8, 8.1, 2008R2, 2012, 2012 R2, WHQL, Novell, Citrix

Scan Specifications

Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	50 SPM Color/50 SPM B&W (@ 300 dpi)
File Format	TIFF, PDF, Secure PDF, JPEG, (XPS with HDD)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job
Scan Speed	.7 Seconds Per Page, Maximum 50 SPM

e-Filing Specifications (with HDD)

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder, 200 Pages Per Document

Security

Data Encryption	256 Bit AES
Authentication	LDAP, SMTP, Windows Server Domain, Local

Accessories (Options)

Additional Paper Options

Platen Cover	KA1640PC
RADF: 100 Sheets	MR3024
Paper Feed Unit: 550-Sheet Pedestal, Statement-R to Ledger	MY1040
Paper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger	KD1032
Paper Drawer: 550-Sheet Pedestal, Statement-R to Ledger	MY1039
Large Capacity Feeder (LCF): 2,000-Sheet Drawer, Letter	KD1031
Paper Feed Controller	GH1080

Finishing Options

Saddle-Stitch Finisher:	MJ1037
Tray 1 Stack Capacity: 1,000 Sheets (LT)	
Staple Capacity: 50 Sheets	
60 Pages (15 Sheets) SS Booklets	
Multi-Position Hole Punch Unit for Inner Finisher	MJ6008
Inner Finisher	MJ1036
2 Tray: 600 Sheets (LT)	
Staple Capacity: 50 Sheets	
Multi-Position Hole Punch Unit for Inner Finisher	MJ6007

Connectivity/Security Options

Bridge Kit Required with MJ1037	KN2550
Fax Board	GD1320
2nd Line Fax	GD1260F
Wireless Module	GN1060
Wireless Antenna	GN3010
External Interface Enabler	GS1020
Meta Scan Enabler for e-CONNECT	GS1010
Data Overwrite Enabler	GP1070
IPsec Enabler	GP1080
Advanced Scanning (Re-Rite)	GB1280V8
SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540

Miscellaneous Options

Accessible Arm Handle	KK2550
Harness Kit for Coin Controller	GQ1260



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.