

- > **Up to 45 PPM**
- > **Black & White MFP**
- > **Sml/Med Workgroup**
- > **Copy, Print, Scan, Fax**
- > **Secure MFP**
- > **Eco Friendly**

e-STUDIO355SE/455SE





- > Black & White MFP
- > Up to 45 PPM
- > Sml/Med Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly

Specifications

Copying Process/Type	IEPM (Dry Process)/Laser Technology
Original Reading Method	CCD Line Sensor
Copy/Print Resolution	2400 x 600 dpi (with Smoothing)
Copy/Print Speed	35 / 45 ppm
Scanning	Color Scanning
Warm-Up Time	Appx. 20 Seconds
First Copy Time	3.7 Seconds
Duty Cycle	125K / 150K
Multiple Copying	Up to 999 Copies
Standard Paper Supply	2 x 550-Sheet, 100-Sheet Stack Feed Bypass
Maximum Paper Supply	Up to 3,200 Sheets
Acceptable Paper Size	Cassette: Statement-R to Ledger (17-28 lbs.); Bypass: Statement-R to Ledger (17-110 lbs.); LCF: Letter (17-28 lbs.)
Special Paper	Bypass: Envelope, Tab Sheet
Memory	1GB RAM, 60 GB HDD
Reduction/Enlargement	25% to 400%
Bypass Tray	100-Sheet Stack Feed Bypass
Control Panel	8.5" Wide VGA Color Touch-Screen
Dimensions	Appx. 23" x 23" x 30" (W x D x H)
Weight	Appx. 132 lbs.
Power Supply	115 Volts; 15 Amps
Power Consumption	Maximum 1.5kW
PM Cycle	125K / 150K
Black Toner Yield	30K Impressions
Drum Type/Yield	Organic Photoconductor; 125K / 150K
Developer Yield	125K / 150K

Print (Standard)

Print Speed	35 / 45 ppm
PDL Support	PCL6, PostScript3, XPS
Operating Systems	Windows 2000/XP/2003/Vista/2008/7; Mac X OS10.2.4/10.3/10.4/10.5; UNIX, Linux, CUPS
Protocol Support	IPX/SPX, TCP/IP (IPv4/IPv6), EtherTalk, AppleTalk PAP, LPR/LPD, IPP w/Authentication, Port 9100 Bluetooth, SMB, Netware
Drivers	Windows 2000/XP/2003/Vista/2008/7; Mac X OS 10.2.4/10.3/10.4/10.5 (OS 10.4 PPD); UNIX, Linux, AS/400, SAP R/3
Connectivity	Ethernet 10/100BaseT, USB 2.0, 802.11b/g Wireless LAN, Bluetooth (HCRP)
Device Management	TopAccess
Certification	WHQL, Novell, HPOS (Dazel), Vista Premium

Scan (Standard)

Scan Speed	57spm LT-Size@300dpi (B&W)/43spm LT-Size@300dpi (Color)
Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
File Format	TIFF, PDF, Slim PDF, JPEG, XPS, MS Word, MS Excel, Searchable PDF w/ Adv. Scanning option

E-Filing (Standard)

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box; 200 Private User Boxes
Capacity of Boxes	100 Folder per Box; 400 Documents per Folder; 1000 Pages per Documents

Security (Standard)

Data Encryption	128 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

Facsimile Option

Compatibility	Super G3, G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Appx. 3 Seconds per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	Transmission 500MB (HDD); Reception 200MB (HDD); Backup Permanent (HDD)
Memory Transmission	100 Jobs; 1,000 Destinations Max; 400 Destinations/Job
Scan Speed	0.7 Seconds per Page; 50 Scans per Minute
Other Fax Functions	Internet Fax; Network Fax

Accessories (Options)

Input Options	
100-Sheet RADF	MR3022
Platen Cover	KA1640PC
Additional Paper Options	
550-Sheet Paper Feed Pedestal	KD1025
2,000-Sheet Large Capacity Feeder	KD1026
550-Sheet Paper Feed Unit	MY1033
Finishing Options	
Job Separator	MJ5006
Work Tray	KK4550
Bridge Kit for Finisher	KN2520
50-Sheet Staple Hanging Finisher	MJ1031
Saddle-Stitch Finisher	MJ1024
50-Sheet Staple Console Finisher	MJ1101
2 or 3 Hole Punch Unit for MJ1024	MJ6004
2 or 3 Hole Punch Unit for MJ1101	MJ6101
Connectivity/Security Options	
Fax Kit	GD1250
2nd Line Fax	GD1260
IPSec Enabler	GP1080
Wireless LAN Adapter	GN1050
Bluetooth Module	GN2010
Antenna	GN3010
Meta Scan Enabler	GS1010
Advanced Scanning	GB1280T
Miscellaneous Options	
SmartCard Reader, HID iClass	ART11236
SmartCard Reader, HID Prox	ART11230
SmartCard Reader, Inditag	ART12161
SmartCard Reader, LEGIC	ART11248
SmartCard Reader, Multi ISO/Mifare	ART11443
SmartCard Reader, Multi 125	ART11242
SmartCard Authentication - Demo Only (10 Pack)	KP2004-CDEMO
Accessible Arm Handle	KK2550
Harness Kit for Coin Controller	QQ1180



Corporate Office	2 Musick, Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-3136-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	142 Technology, Suite 150, Irvine, CA 92618 Tel: 949-462-6262
Web Site	www.copiers.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.