

Product Configuration



Input Options

1	100-Sheet RADF (Reversing Automatic Document Feeder)	MR3022
2	Platen Cover	KA1640PC

Paper Options

3	550-Sheet Paper Feed Pedestal	KD1025
4	2,000-Sheet Large Capacity Feeder	KD1026
5	550-Sheet Paper Feed Unit (use with 3)	MY1033

Finishing Options

6	Job Separator	MJ5006
7	Bridge Kit (required with 9, 10 & 11)	KN2520
8	50-Sheet Inner Finisher	MJ1032
9	Saddle-Stitch Finisher (low capacity)	MJ1033
10	50-Sheet Staple Console Finisher	MJ1101
11	Saddle-Stitch Finisher (high capacity)	MJ1106N
12	2 or 3 Hole Punch Unit (use with 8)	MJ6007
13	2 or 3 Hole Punch Unit (use with 9)	MJ6008
14	2 or 3 Hole Punch Unit (use with 10 or 11)	MJ6103

Other Options

15	Work Tray	KK4550
16	Stand	STAND355/455

Advanced Scanning Features

SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540
Advanced Scanning (OCR Conversion Software)	GB1280T

Connectivity Options

Fax Kit	GD1250NXF
2nd Line Fax	GD1260F
IPSec Enabler	GP1080
Wireless LAN Adapter	GN1060
Antenna	GN3010
Meta Scan Enabler	GS1010

Miscellaneous Options

SmartCard Reader, HID iClass	ART11236
SmartCard Reader, HID Prox	ART11230
SmartCard Reader, Inditag	ART12161
SmartCard Reader, LEGIC	ART11248
SmartCard Reader, Multi ISO/Mifare	ART11443
SmartCard Reader, Multi 125	ART11242
SmartCard Authentication - Demo Only (10 Pack)	KP2004-CDEMO
Bracket for Card Reader	6BC02231846
Accessible Arm Handle	KK2550
Harness Kit for Coin Controller	GQ1180

Supplies

Staples (for 8 & 10)	STAPLE2400
Staples - Saddlestitch (for 9)	STAPLE600
Toner	T4590
Developer	6LH58317000