

e-STUDIO™ 5530C PRO / 7030C PRO



HIGH-SPEED PRODUCTIVITY. HIGH-QUALITY COLOR.



75/60 BW
70/55 C



Workgroup



Color



EFI Controller



Copy / Print /
Scan / Fax

TOSHIBA
Leading Innovation >>>

e-STUDIO™ 5530c PRO/7030c PRO SPECIFICATIONS



Get high-performance color at the lowest possible operating cost. These lightning-fast, full-color digital multifunction products, (MFPs) are packed with features that make short work of your most demanding color and black and white document needs. Both devices offer a powerful and efficient combination of production color copying along with optional network printing, scanning, and faxing capabilities—all in one flexible footprint.

fast and friendly

The icon-driven display delivers an intuitive user interface. No more poking around to figure out advanced tasks. Plus, a QWERTY keyboard make entering information onscreen a breeze.



think green!

Toshiba is mindful of the environment and strives to conserve natural resources. That's why both devices have attained the coveted Energy Star rating. They use half the electricity of standard models and power down when not in use. Both feature quick start-up, minimal ozone emissions, and are RoHS compliant.

SPECIFICATIONS

Copying Process	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	Color Laser
Copy/Print Resolution	600 x 600 dpi
Copy/Print Speed	e-STUDIO5530c PRO – 55 PPM Color / 60 PPM B&W e-STUDIO7030c PRO – 70 PPM Color / 75 PPM B&W
Warm-Up Time	Less than 90 Seconds / 75 Seconds
First Copy Out Time	e-STUDIO5530c PRO – 7.5 Seconds Color / 5.7 Seconds B&W e-STUDIO7030c PRO – 6.4 Seconds Color / 4.9 Seconds B&W
Duty Cycle	150,000
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to 12" x 18" (14 lb. Bond - 80 lb. Cover) Bypass: ST-R to 12" x 18" (14 lb. Bond - 110 lb. Cover) A4/LCF: Letter (14 - 34 lb. Bond) A3/LCF: ST-R to 12" x 18" (14 lb. Bond - 110 lb. Cover)
Paper Supply	2 x 550 Sheets (Universal) 2 x 1,100 Sheets (LT-only) 100-Sheet Bypass (Universal) Optional: 4,000-Sheet A4/LT LCF Optional: 2,000-Sheet A3/LD LCF*
Duplex	Standard 100-Sheet Duplex Unit (17 lb. Bond - 90 lb. Index)
Memory (Max)	1,536 MB RAM / 320 GB (160 GB x 2) HDD
Reduction/Enlargement	25% to 400%
Dimensions	Approx. 29.5" x 33.5" x 43.1" (W x D x H)
Weight	Approx. 656.9 lb.
PM Cycle	150,000
Drum Type/Yield	Organic Photoconductor: 450,000
CMYK Toner Yield	CMY: 21,600 / K: 43,200
Black Developer Yield	450,000
Power Supply	e-STUDIO5530c PRO – 120 V / 20 Amps / 60 Hz e-STUDIO7030c PRO – 208-240 V / 12 Amps / 60 Hz
Power Consumption	Less than 1,920 W / 2,400 W

PRINT SPECIFICATIONS

PDL Support	RCPS, PCL5c, PDL6, PostScript 3 (optional)
Protocol Support	IPX/SPX, TCP/IP, SMB, AppleTalk
Drivers	Netware 6.x, Microsoft Windows 2000/XP/Server 2003, UNIX, Sun Solaris, HP-UX, IBM AIX, RedHat Linux, SCO OpenServer, Macintosh
Connectivity	10BaseT/100BaseTX, USB 2.0, Gigabit Ethernet (optional)
Device Management	SmartNetMonitor, Command WorkStation (EFI)

SCAN SPECIFICATIONS

Scan Resolution	Up to 600 dpi
Scan Speed	69 SPM Color / 81 SPM B&W
File Format	Single/Multi-Page PDF, Single/Multi-Page TIFF, High Comp PDF
Authentication	LDAP, SMB, FTP

FACSIMILE SPECIFICATIONS

Compatibility	ITU-T (CCITT) G3, Additional G3 (optional)
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	G3: Approx. 2 Seconds
Fax Modem Speed	33.6 Kbps - 2,400 bps
Quick Dial/Speed Dial	Standard - 2,000 Numbers
Group Dial	Standard - 100 Groups (500 Numbers per Group)
Program	Standard - 100 Numbers
Scan Speed	.5 Seconds per Page

OPTIONS

413965	A3/LCF Large Capacity Tray	2,000-Sheet Tray, Ledger-Size
411182	A4/LCF Large Capacity Tray	4,000-Sheet Tray, Letter-Size
412204	A4 Adapter Connection Kit	Use with A4/LCF Large Capacity Tray
411187	A4/LT to Legal-Size Adapter	Letter to Legal-Size, Adapter for A4/LCF (2,500-Sheet)
412190	Copy Tray	Exit Tray
412976	Dual Source Interposer	2 Sources for Covers or Inserts
412213	Cover Interposer	1 Source for Covers or Inserts
413974	50-Sheet Stapling Finisher	50-Sheet Staple Capacity
413976	Booklet Stapling Finisher	50-Sheet Staple Capacity with Saddle
412981	100-Sheet Stapling Finisher	100-Sheet Staple Capacity
413973	Finisher Adapter	Use with 100-Sheet Finisher
412983	100-Sheet Hole Punch Unit	Use with 100-Sheet Finisher
412209	50-Sheet Hole Punch Unit	Use with 50-Sheet Finisher
412203	Tab Sheet Holder	Holds Tab Paper in Drawer
412805	Z-Folding Unit	Folds Ledger-Size Sheets into Letter-Size Documents
412212	Output Jogger Unit	Use with 50-Sheet Finishers
412191	9-Bin Mail Box	200 Sheets Each Tray
412415	Tandem Copy Connector	Connects 5530c PRO-7030c PRO Units
318398	Printer/Scanner Kit	Embedded Printer/Scanner Kit
414000	Genuine Adobe PostScript3	Use with Printer/Scanner Kit
414002	Data Overwrite Security Unit	Data Security Solutions
414496	EFI E7100 Controller	Fiery-Driven Solutions
413968	Fax Option	Provides Walk-up or LAN Fax
413971	G3 Interface Unit	Use with Fax Option to Add More Lines
400516	Memory Unit	32 MB for Fax Option

* Bypass is disabled with addition of A3/LCF



Corporate Office: 2 Musick, Irvine, CA 92618-1631
Tel: 949-462-6000

East Coast: 959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700 Fax: 973-263-2393

Midwest: 8770 W. Bryn Mawr Ave., Suite 700, Chicago IL 60631
Tel: 773-380-6000 Fax: 773-380-8077

West Coast: 142 Technology, Suite 150, Irvine, CA 92618
Tel: 949-462-6262 Fax: 949-462-2700

Web Site: copiers.toshiba.com

AUTHORIZED TOSHIBA DEALER

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 6% coverage, letter-sized page. Driver and connectivity feature support varies by client/network operating system.