

e-STUDIO™ 901/1101/1351



PRODUCTIVITY THAT SPEAKS VOLUMES



TOSHIBA
Leading Innovation >>>

e-STUDIO™ 901/1101/1351

SPECIFICATIONS

The Toshiba e-STUDIO901, e-STUDIO1101 and e-STUDIO1351 are fully featured high-volume black and white digital devices that offer all the optional finishing and paper-handling capability your biggest jobs demand, as well as the optional network printing, scanning, and finishing capabilities to keep your workgroup productive. And with their impressive 90, 110, and 135-PPM output, the e-STUDIO901/1101/1351 keep everything moving briskly along while providing robust duty cycles, impeccable image quality, and a broad array of document finishing options.



Fast!
90/110/135
PPM

**Network
READY**

**Secure
BY DESIGN**

Impeccable image quality with impressive speed for demanding jobs

Optional network printing, scanning, and finishing capabilities

The optional Data Overwrite Security meets the needs of the most security-conscious workgroups

GENERAL SPECIFICATIONS

Warm-up Time	Less than 360 Seconds
Standard Paper Weights	16 lbs. – 40 lbs. Bond 50 lbs. – 80 lbs. Cover 90 lbs. – 110 lbs. Index
Standard Paper Capacity	Tray 1: 1,000 Sheets x 2 Tray 2: 500 Sheets Tray 3: 500 Sheets
Total Paper Capacity	3,000 Sheets
Power Source	208 – 240V, 50/60Hz, 20A (Requires Dedicated Outlet)
Power Consumption	e-STUDIO901/1101: Less than 3,500W with LCT & Finisher e-STUDIO1351: Less than 4,000W with LCT & Finisher
Dimensions (WxDxH)	34.3" x 33.9" x 58.2" (Main Unit Without Finisher)
Weight	672.4 lbs. (Main Unit Without Finisher)

SYSTEM SPECIFICATIONS

First-Copy-Out Time	e-STUDIO901: 3.5 Seconds e-STUDIO1101: 3.2 Seconds e-STUDIO1351: 3.0 Seconds
Copy Size	5.5" x 8.5" to 13" x 18"
HDD Capacity	160 GB x 2 (320 GB)
Reduction/Enlargement	25% – 400% (1% Increments)

SYSTEM ACCESSORIES

Automatic Reversing Document Feeder	
Original Paper Weight	11 lbs. – 34 lbs. Bond (Simplex) 14 lbs. – 28 lbs. Bond (Duplex)
RT5000 LT/LCT Large Capacity Tray	
Paper Sizes Supported	5.5" x 8.5" – 8.5" x 11"
Paper Capacity	Tray 4: 1,000 Sheets Tray 5: 1,000 Sheets Tray 6: 2,550 Sheets
Paper Weights	Tray 4: 16 lbs. Bond – 80 lbs. Cover Tray 5: 16 lbs. Bond – 80 lbs. Cover Tray 6: 16 lbs. Bond – 90 lbs. Index
Dimensions (WxDxH)	21.2" x 28.7" x 38.5"
Weight	194 lbs.
RT5010 DLT/LCT Large Capacity Tray	
Paper Sizes Supported	5.5" x 8.5" – 13" x 18"
Paper Capacity	Tray 4: 1,000 Sheets Tray 5: 2,000 Sheets Tray 6: 1,000 Sheets
Paper Weights	Tray 4: 16 lbs. Bond – 80 lbs. Cover Tray 5: 16 lbs. Bond – 80 lbs. Cover Tray 6: 16 lbs. Bond – 90 lbs. Index
Dimensions (WxDxH)	34.7" x 28.8" x 38.6"
Weight	194 lbs.

SR5000 100-Sheet Finisher

Paper Weight	16 lbs. Bond – 80 lbs. Cover
Proof Tray	500 Sheets (8.5" x 11") 250 Sheets (8.5" x 14" or Larger)
Shift Tray	3,000 Sheets (8.5" x 11" – LEF) 1,500 Sheets (8.5" x 14" – 11" x 17" – SEF) 1,000 Sheets (12" x 18") 100 Sheets (8.5" x 11")
Staple Capacity	31.5" x 28.7" x 38.5"
Dimensions (WxDxH)	165 lbs.
Weight	

BK5000 Saddle Stitch Unit

Paper Sizes Folded	8.5" x 11" – 12" x 18"
Paper Weights Folded	20 lbs – 24 lbs. Bond
Dimensions (WxDxH)	23.6" x 28.7" x 38.5"
Weight	154 lbs.

CI5000 Cover Interposer

Paper Sizes Supported	5.5" x 8.5" – 13" x 18"
Paper Capacity	2 x 200 Sheets
Paper Weight	17 lbs. Bond – 80 lbs. Cover
Dimensions (WxDxH)	27.9" x 28.7" x 50"
Weight	99.2 lbs.

BY5000 Multi Bypass Tray

Paper Capacity	500 Sheets (20 lbs. Bond)
Paper Sizes Supported	5.5" x 8.5" – 12" x 18" (RT5000) 5.5" x 8.5" – 13" x 18" (RT5010)

PU5000 Punch Unit

Punch Type	2 or 3 Holes (User Selectable)
Punch	16 lbs. Bond – 90 lbs. Index
Systems Supported	e-STUDIO901/1101 Only
GBC StreamPunch III	
Punch Type	Customer Replaceable Die Sets (7)
Paper Sizes Supported	8.5" x 11" Long Edge Feed (11" Side Only)
Systems Supported	e-STUDIO901/1101/1351
Dimensions (WxDxH)	12" x 28.5" x 38.5"
Weight	154 lbs.

NETWORK CONNECTIVITY OPTIONS

Printer/Scanner Kit Type 1350	
Windows Drivers	
RPCS	95/98/ME/NT4.0/2000/XP/Server 2003
PCL5e	95/98/ME/NT4.0/2000/XP/Server 2003
PCL 6	95/98/ME/NT4.0/2000/XP/Server 2003
Adobe PostScript3 (Option)	95/98/ME/NT4.0/2000/XP/Server 2003
Utilities Supported	WebImageMonitor, Web SmartDevice Monitor, SmartDeviceMonitor, Printer Utility for Mac, USB Printing Support, PDF Direct Printing, DeskTop Binder Lite
Printer Options	Gigabit Ethernet Type 7300

SCANNER SPECIFICATIONS

Scan Speed	80 SPM (Black & White) 80 SPM (Color 200 dpi/LT)
Optical Resolution	100/150/200/300/ 400/600 dpi
Delivery Scanner Resolution	100/150/200/300/ 400/600 dpi
TWAIN Resolution	100 – 1,200 dpi (Color and Black & White)
File Formats	TIFF/JPEG/PDF and High Compression PDF
Scan-to-Email	
Requirement	SMTP Gateway and TCP/IP
Email Addresses	2,000 Addresses
Max. Address/Send	500 Addresses
Address Support Via LDAP	100 Addresses
Scan-to-Folder	
Protocol Support	SMB/FTP/NCP
Resolution	100/150/200/300/ 400/600 dpi
File Types Supported	Single Page TIFF/JPEG, Single Page PDF, Multi- Page TIFF, Multi-Page PDF, High Compression PDF

SECURITY

Authentication	Windows/LDAP/Basic
Secure Socket Layer Support	
Network Protocol On/Off	
SNMP v3 Support/PDF Encryption	
Driver Encryption Key (PCL/RPCS Driver)	
Data Overwrite Security Unit (DOSS) Type F	

ADDITIONAL OPTIONS

BK5010	Production Booklet Maker
TR5010	Trimmer Unit
CF5010	Cover Feeder Unit
BF5010	Book Folder

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

Corporate Office: 2 Musick, Irvine, CA 92618-1631
 East Coast: 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 / Tel: 973/316-2700
 Midwest: 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 / Tel: 773/380-6000
 South: 2037 Bakers Mill Rd., Dacula, GA 30019 / Tel: 773/380-6000
 West Coast: 142 Technology, Suite 150, Irvine, CA 92618 / Tel: 949/462-6262
 Web Site: www.copiers.toshiba.com

©2010 Toshiba America Business Solutions, Inc., Electronic Imaging Division
 e-STUDIO901/1101/1351 Specification Sheet / Inv. Code ES901110113512
 Revised PDF Aug 2010

AUTHORIZED TOSHIBA DEALER

TOSHIBA
 Leading Innovation >>>