


TOSHIBA
Leading Innovation >>>

- > Up to 135 PPM
- > Black & White MFP
- > Production
- > Copy, Print, Scan
- > SecureMFP
- > Eco Friendly

e-STUDIO™ 905/1105/1355





- > Black & White MFP
- > Up to 135 PPM
- > Production
- > Copy, Print, Scan
- > SecureMFP
- > Eco Friendly

Specifications

Warm-Up Time	Less than 360 Seconds
Speed	90 / 110 / 135 cpm
Paper Weights	Trays 1, 2, 3: 16 lb. Bond – 80 lb. Cover, LT LCT Trays 4, 5: 16 lb. Bond – 80 lb. Cover, Tray 6: 16 lb. Bond – 60 lb. Cover, DLT LCT Trays 4, 6: 16 lb. Bond – 90 lb. Cover, Tray 5: 16 lb. Bond – 100 lb. Cover
Standard Paper Capacity	3,000 Sheets Tray 1: 2 x 1,000 Sheets, Tray 2/3: 1 x 500 Sheets
Power Requirements	208 – 240 Volts, 50/60 Hz, 20 Amps (Dedicated Outlet)
Dimensions	34.3" x 33.9" x 58.2" (WxDxH)
Throughput Size	5.5" x 8.5" to 13" x 19.2"
Reduction/Enlargement	25% to 400% (1% Increments)

Printer Specifications

CPU	Intel Pentium M 1.4 GHz
Memory	512 MB Standard 1.5 GB (Standard + Printer/Scanner Unit)
HDD Capacity	320 GB
Drivers / PDL	RPCS, PCL5e/6, Optional: Adobe® PostScript
Print Resolution	1200 dpi (Max.)
Fonts	PCL: TrueType: 45 Intellifonts, 13 International Fonts, Optional: PS3: 136 Adobe Type 1
Standard Connectivity	100Base-TX/10Base-T Ethernet, USB 2.0
Optional Connectivity	1000Base-T Gigabit Ethernet
Network Protocol	TCP/IP, IPX/SPX, AppleTalk
Operating Systems	Windows 2000, XP, Vista, Windows 7, Server 2003, Server 2008, Mac OS 8.6 – 9.2.X (OS X Classic), Mac OS 10.1.X – OS 10.5.X
Utilities Supported	Web Image Monitor, Web SmartDeviceMonitor, SmartDeviceMonitor, Printer Utility for Mac, PDF Direct Printing (Through DeskTopBinder), DeskTopBinder

Scanner Specifications

Scan Speed	80 spm in Black & White or Color
Optical Resolution	100/150/200/300/400/600 dpi
File Formats	TIFF/JPEG/PDF and High Compression PDF

System Accessories

100-Sheet Automatic Document Feeder (Standard)
Original Paper Weights 11 – 34 lb. Bond (Simplex), 14 – 28 lb. Bond (Duplex)

RT5030 LT Large Capacity Tray (Optional)
Paper Sizes Supported 5.5" x 8.5" to 8.5" x 11"
Paper Capacity Tray 4/5: 1,000 Sheets, Tray 6: 2,550 Sheets
Paper Weights Tray 4/5: 16 lb. Bond - 80 lb. Cover
Tray 6: 16 lb. Bond - 60 lb. Cover
Dimensions 21.2" x 28.7" x 38.6" (WxDxH)

RT5040 DLT Large Capacity Tray (Optional)
Paper Sizes Supported 5.5" x 8.5" to 13" x 18"
Paper Capacity Tray 4: 1,000 Sheets, Tray 5: 2,000 Sheets
Tray 6: 1,000 Sheets
Paper Weights Tray 4/6: 16 lb. Bond - 90 lb. Cover
Tray 5: 16 lb. Bond - 100 lb. Cover
Dimensions 34.6" x 28.8" x 38.6" (WxDxH)

SR5000 Finisher with 100-Sheet Stapler (Optional)
Staple Capacity 100 Sheets (Based on 20 lb. Bond)
Z-Folding 10 Sheets
Dimensions 31.5" x 28.7" x 38.6" (WxDxH)

CI5010 Cover Interposer (Optional)
Paper Sizes Supported 5.5" x 8.5" to 13" x 19.2"
Paper Capacity 2 x 200 Sheets
Paper Weights 17 – 58 lb. Bond/80 lb. Cover
Dimensions 27.9" x 28.7" x 50" (WxDxH)

BY5000 Multi Bypass Tray (Optional)

Paper Capacity 500 Sheets (Based on 8.5" x 11")
16 lb. Bond - 90 lb. Cover, 110 lb. Index

PU5000 or PU5020 (User-Selectable) Punch Unit (Optional)

Punch Type 2 or 3 Holes
Weights Punched 16 lb. Bond – 90 lb. Index

SR5020 Booklet Finisher (Optional)

Staple Capacity 100 Sheets (8.5" x 11"), 50 Sheets (8.5" x 14" or 11" x 17")
Saddle-Stitch Paper Size: 8.5" x 11" – 13" x 19.2" Paper Weight: 18 – 24 lb. Bond, Staple Position: Center 2 Position
Staple Capacity: 20 Sheets (18 – 20 lb. Bond)

FD5000 Multi-Folding (Optional)

Copy Dimensions 18.3" x 28.7" x 38.6" (WxDxH)
Power Consumption 120 Volts, 60Hz
Folding Patterns Z-Fold, Half-Fold/Print Inside, Half-Fold/Print Outside, Letter Fold-In/Print Inside, Letter Fold-In/Print Outside, Letter Fold-Out, Double Parallel/Print Inside, Double Parallel/Print Outside, Gatefold/Print Inside, Gatefold/Print Outside
Paper Sizes Supported 8.5" x 11" – 13" x 19.2"

TR5020 Booklet Trimmer (Optional)

Power Consumption 120 Volts, 60Hz
Trimming Type One Side Edge
Paper Sizes Supported 5.5" x 8.5" – 13" x 19.2"

RT5040 DLT/A3 Tray Kit* (Optional)

Paper Sizes Supported 8.5" x 11", 8.5" x 14", 11" x 17"
Paper Capacity 1,000 Sheets

*This option is put on the Tandem LCT in Tray 1 of base unit and can feed DLT or A3 Paper

SK5010 High Capacity Stacker* (Optional)

Dimensions 35.4" x 38.6" x 28.7" (WxDxH)
Power Consumption 120 Volts, 60Hz
Paper Sizes Supported Proof Tray & Shift Tray: Up to 13" x 19.2"
Paper Weight 14 lb. – 100 lb. Cover
Stack Capacity Proof Tray: 250 Sheets, Shift Tray: 5,000 Sheets
Roll-Away Cart One Included (Second One Optional)

*Decurl Unit must be connected when Large Capacity Stacker is configured

DU5000 Decurl Unit (Optional)

Dimensions 6.7" x 28.7" x 39" (WxDxH)
Power Consumption From Mainframe

Security Options

Data Overwrite Kit
HDD Encryption Unit Type A
Copy Data Security Unit Type F
External HDD Security Kit Type 1357 (For EFI Controller)



Corporate Office 2 Musick, Irvine, CA 92618-1631 | 949-462-6000
East Coast 959 Route 46 E., 5th Flr., Parsippany, NJ 07054 | 973-316-2700
Midwest 8770 W. Bryn Mawr Ave., Ste. 700, Chicago, IL 60631 | 773-380-6000
South 2037 Bakers Mill Rd., Dacula, GA 30019 | 678-546-9385
West Coast 142 Technology, Ste. 150, Irvine, CA 92618 | 949-462-6262
Web Site www.copiers.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. © 2010 Toshiba America Business Solutions, Inc. Electronic Imaging Division | Inv. Code: ES90511051355