

- > Color MFP
- > Up to 30 PPM Color
- > Medium Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Features

e-STUDIO™ 2040c/2540c/3040c





- > Color MFP
- > Up to 30 PPM
- > Medium Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Features

Specifications

Copying Process	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	4-Beam Color Laser (8 bit)
Copy/Print Resolution	600 x 600 dpi (2,400 x 600 dpi B&W)
Copy/Print Speed	e-STUDIO2040c – 20 PPM Color / B&W e-STUDIO2540c – 25 PPM Color / B&W e-STUDIO3040c – 30 PPM Color / B&W
Warm-Up Time	Approx. 99 Seconds
First Copy Out Time	e-STUDIO2040c – 8.4 Seconds Color / 6.5 Seconds B&W e-STUDIO2540c – 8.4 Seconds Color / 6.5 Seconds B&W e-STUDIO3040c – 8.4 Seconds Color / 6.5 Seconds B&W
Duty Cycle	40K / 50K / 60K Copies
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to LD (17 lb Bond - 140 lb Index) Bypass: ST-R to 12" x 47" (17 lb Bond - 100 lb Cover) PPF: ST-R to LD (17 lb Bond - 140 lb Index) LCF: LT (17 lb - 28 lb Bond)
Memory (Max)	Main Memory: 1 GB Page Memory: 512 MB HD: 80 + GB
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet "Smart" Bypass (17 lb Bond - 100 lb Cover)
Control Panel	Color 8.5" WVGA Tilttable LCD Touch Panel
Paper Supply	Up to 3,700-Sheet Input Capacity Standard 2 x 550-Sheet Cassettes 100-Sheet Bypass Optional 1 x 550-Sheet PFP, 1 x 550-Sheet Cassette 1 x 2,500-Sheet LCF
Duplex	Standard Trayless Automatic Duplex Unit (17 lb Bond - 140 lb Index)
Dimensions	Approx. 30" x 28" x 29" (W x D x H)
Weight	Approx. 267 lb
Minimum Footprint Req.	39.53" x 28.31" (W x D)
CMYK Toner Yield	CMY: 26.8K, BK: 34.2K
Power Supply	115 V, 15 Amps
Power Consumption	Maximum 1.5 kW

Print Specifications

PDL Support	PCL6 and PostScript 3
Operating Systems	Netware 6.x, Windows XP, Windows Server 2003, 2008, Citrix MetaFrame, Macintosh, Linux, UNIX
Protocol Support	IPX/SPX, TCP/IP, Ethertalk, AppleTalk, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
Drivers	Windows 2000, Server 2003/2008-Windows 7, XP Macintosh 10.1/10.2/10.3, 10.4, 10.5 UNIX, AS400 via iData & Port 9100, SAP R/3
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g Wireless LAN, USB, Bluetooth (HCRP)
Device Management	TopAccess
Certification	Windows (XP, Vista, 7, 2003, 2008) (WHQL) Novell

Scan Specifications

Scan Resolution	100 dpi, 150 dpi, 200dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	57 SPM Color / 57 SPM B&W (@ 300 dpi)
File Format	TIFF, PDF, Secure PDF, Slim PDF, JPEG, XPS

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Memory Transmission	100 Jobs, 1,000 Destinations Max. 400 Destinations / Job
Scan Speed	.7 Seconds Per Page, Maximum 55 SPM

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

Security (Standard)

Data Encryption	128 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

Accessories (Options)

Additional Paper Options

RADF: 100 Sheets	MR3021
Paper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger	KD1027
Cassette Module :550-Sheet Pedestal, Statement-R to Ledger	MY1035
Large Capacity Feeder (LCF): 2,500-Sheet Drawer, Letter	KD1028

Finishing Options

Multi Position Finisher: Stationary Tray: 250-Sheets (Lt) Tray 1 Stack Capacity: 2,500 Sheets (Lt) Staple Capacity: 50 Sheets	MJ1101
Saddle-Stitch Finisher: Stationary Tray: 250-Sheets (lt) Tray 1 Stack Capacity: 3,000 Sheets (Lt) Staple Capacity: 50 Sheets 60 Pages (15 Sheets) SS Booklets	MJ1106
Hanging Finisher 1 Tray: 1,000 Sheets (Lt) Staple Capacity: 50 Sheets	MJ1031
Multi-Position Hole Punch Unit (for MJ1101, MJ1106)	MJ6103

Connectivity/Security Options

Bridge Kit Required with MJ1101, MJ1106, MJ1031	KN4530
EFI Controller (not available at launch)	GA1211EX
Fax Board	GD1250NX
2nd Line Fax	GD1260
Wireless LAN Adapter	GN1060
Bluetooth Adapter	GN2010
Wireless Antenna	GN3010
Meta Scan Enabler for e-CONNECT	GS1010
IP SEC Enabler	GP1080
Advanced Scanning	GB1280T

Miscellaneous Options

SmartCard Reader, HID iClass	ART11236
SmartCard Reader, HID Prox	ART11230
SmartCard Reader, Inditag	ART12161
SmartCard Reader, LEGIC	ART11248
SmartCard Reader, Multi ISO/Mifare	ART11443
SmartCard Reader, Multi 125	ART11242
Harness Kit for Coin Controller	QQ1110



Corporate Office

2 Musick, Irvine, CA 92618-1631 Tel: 949-462-6000	
East Coast 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-3136-2700	
Midwest 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000	
South 2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385	
West Coast 142 Technology, Suite 150, Irvine, CA 92618 Tel: 949-462-6262	
Web Site	www.copiers.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.