

- > Color MFP
- > Up to 65 PPM Color
- > Up to 75 PPM B&W
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Features

e-STUDIO™ 6550c series





- Color MFP
- Up to 65 PPM Color
- Up to 75 PPM B&W
- Med/Large Workgroup
- Copy, Print, Scan, Fax
- Secure MFP
- Eco Features

Specifications

Copying Process	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	4-Beam Color Laser (8 bit)
Copy/Print Resolution	600 x 600 dpi/1200 x 1200 dpi
Copy/Print Speed	e-STUDIO5540c – 55 PPM Color / 55 PPM B&W e-STUDIO6540c – 65 PPM Color / 65 PPM B&W e-STUDIO6550c – 65 PPM Color / 75 PPM B&W
Warm-Up Time	Approx. 180 Seconds
First Copy Out Time	e-STUDIO5540c – 6.5 Seconds Color / 5.3 Seconds B&W e-STUDIO6540c – 6.5 Seconds Color / 5.3 Seconds B&W e-STUDIO6550c – 6.5 Seconds Color / 4.6 Seconds B&W
Duty Cycle	225K / 250K / 275K Copies
Multiple Copying	Up to 9999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to 12" x 18" (17 lb Bond - 140 lb Index) Bypass: ST-R to 13" x 19" (17 lb Bond - 110 lb Cover) ST-R to 12" x 47" Banner (17 lb Bond - 110 lb Cover) LCF: LT (17 lb Bond - 140 lb Index)
Memory (Min/Max)	Page + Main Memory: 2 GB, PowerPC 1.5 GHz Processor HD: 80+ GB
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet Bypass (17 lb Bond - 110 lb Cover)
Control Panel	10.4 Color Super VGA Tilttable LCD Touch Panel
Paper Supply	Up to 6,000-Sheet Input Capacity (Tandem Version + LCF) 4 Drawer Version: 4 x 540-Sheet Cassettes (2,160 Sheets) Tandem Version: 2 x 540-Sheet Cassettes + 2,320-Sheet LCF 100-Sheet Bypass Optional 1 x 2,500-Sheet LCF
Duplex	Standard Automatic Duplex Unit (17 lb Bond - 140 lb Index)
Dimensions	Approx. 38.582" x 27.480" x 60.629" (W x D x H) Weight Approx. 573 lb
CMYK Toner Yield	CMY: 29.5K, K: 77.4K
Power Supply	120 V, 20 Amps
Power Consumption	Maximum 2.2 kW

Print Specifications

PDL Support	PCL6 & PostScript 3
Operating Systems	Netware 6.x, Windows XP, Windows Server 2003, 2008, Vista, Citrix MetaFrame, Macintosh, Linux, UNIX
Protocol Support	IPX/SPX, TCP/IP, V4/V6 Dual Stack, EtherTalk, AppleTalk PAP, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
Drivers	Windows 2000, Server 2003/2008-Windows 7, Vista, XP Macintosh OS 10.1/10.2/10.3, 10.4, 10.5 (OS 10.4 PPD) UNIX, AS400 via iData & Port 9100, SAP R/3
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g Wireless LAN, USB, Bluetooth (HCRP)
Device Management	TopAccess
Certification	Windows (XP, Vista, 7, 2003, 2008) (WHQL) Novell

Scan Specifications

Scan Resolution	Up to 600 dpi
Scan Speed	Up to 77 SPM Color / 77 SPM B&W
File Format	TIFF, PDF, JPEG, XPS

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH / MR / MMR /JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	500 MB Transmission, 200 MB Reception (HDD)
Memory Transmission	100 Jobs, 1,000 Destinations Max. 400 Destinations /Job
Scan Speed	.7 Seconds Per Page, Maximum 50 SPM

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

Security (Standard)

Data Encryption	128 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

Accessories (Options)

Additional Paper Options

Large Capacity Feeder (LCF): 2,500-Sheet Drawer, Letter	MP2501
---	--------

Finishing Options

Multi-Position Finisher Stationary Tray: 250-Sheets	MJ1103
Finishing Tray: 3,000-Sheets	
Staple Capacity: 50 Sheets	
Saddle-Stitch Finisher Stationary Tray: 250-Sheets	MJ1104
Finishing Tray: 3,000-Sheets	
Staple Capacity: 50 Sheets	
Saddle Tray Stitcher: Up to 50 Sets	
Side Exit Tray	KA6550
Hole Punch Unit (for MJ1103/MJ1104) 2- or 3-Hole Punch Capability	MJ6102

Connectivity/Security Options

EFI Controller (not available at launch)	GA1310EX
Fax Board	GD1270NX
2nd Line Fax	GD1260
Wireless LAN Adapter	GN1060
Bluetooth Adapter	GN2010
Wireless Antenna	GN3010
IP SEC Enabler	GP1080
Meta Scan Enabler for e-CONNECT	GS1010
Advanced Scanning	GB1280T

Miscellaneous Options

SmartCard Reader, HID iClass	ART11236
SmartCard Reader, HID Prox	ART11230
SmartCard Reader, Inditag	ART12161
SmartCard Reader, LEGIC	ART11248
SmartCard Reader, Multi ISO/Mifare	ART11443
SmartCard Reader, Multi 125	ART11242
Harness Kit for Coin Controller	GQ1200



Corporate Office

2 Musick, Irvine, CA 92618-1631

Tel: 949-462-6000

East Coast

959 Route 46 East, 5th Floor, Parsippany, NJ 07054

Tel: 973-3136-2700

Midwest

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631

Tel: 773-380-6000

South

2037 Bakers Mill Rd., Dacula, GA 30019

Tel: 678-546-9385

West Coast

142 Technology, Suite 150, Irvine, CA 92618

Tel: 949-462-6262

Web Site

www.copiers.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.