

- > Up to 85 PPM
- > Black & White MFP
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly





- > Black & White MFP
- > Up to 85 PPM
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Eco Friendly

**Specifications**

Copying Process/Type	IEPM (Dry Process)/Laser Technology
Original Reading Method	CCD Line Sensor
Copy/Print Resolution	2400 x 600 dpi
Gradation	256 Steps
Copy/Print Speed	55 / 65 / 75 / 85 cpm
Warm-Up Time	Appx. 130 Seconds
First Copy Time	555/655: Less Than 4.0 Seconds (Letter-Size) 755/855: Less Than 3.5 Seconds (Letter-Size)
Duty Cycle	460K / 515K / 540K / 600K
Multiple Copying	Up to 9,999 Copies
Standard Paper Supply	2 x 500-Sheet Drawer; 1 x 2,500-Sheet Tandem Drawer; 100-Sheet Stack Feed Bypass
Maximum Paper Supply	Up to 7,600 Sheets (w/Optional 4,000-Sheet LCF)
Acceptable Paper Size	Cassette: Statement-R to Ledger (17-110 lbs.) Bypass: Statement-R to 11" x 17" (17-110 lbs.) LCF: Letter Only (17-110 lbs.)
Special Paper	Std. Bond, Post Card Tab Sheets - Bypass + 1/2 Drawers
Memory	1GB RAM, 60 GB HDD
Reduction/Enlargement	25% to 400%
Bypass Tray	100-Sheet Stack Feed Bypass
Control Panel	9" Wide VGA Color Touch-Screen
Dimensions	Appx. 28" x 31" x 46" (W x D x H)
Weight	Appx. 462 lbs.
Power Supply	120 Volts; 20 Amps
Power Consumption	Maximum 2.0kW
PM Cycle	460K / 515K / 540K / 600K
Black Toner Yield	73.9K Impressions
Drum Type/Yield	460K / 515K / 540K / 600K
Developer Yield	460K / 515K / 540K / 600K

**Print (Standard)**

Print Speed	55 / 65 / 75 / 85 ppm
PDL Support	PCL6, PostScript3, XPS
Operating Systems	Windows 2000/XP/2003/Vista/2008/7; Mac X OS 10.2.4/10.3/10.4/10.5 UNIX, Linux, CUPS
Protocol Support	IPX/SPX, TCP/IP (IPv4/IPv6) EtherTalk, AppleTalk PAP, LPR/LPD IPP w/Authentication, Port 9100, SMB, Netware
Drivers	Windows 2000/XP/2003/Vista/2008/7; Mac X OS 10.2.4/10.3/10.4/10.5 (OS 10.4 PPD); UNIX, Linux, AS/400, SAP R/3
Connectivity	Ethernet 10/100/1000BaseT USB 2.0, 802.11b/g Wireless LAN
Device Management Certification	TopAccess WHQL, Novell, HPOS (Dazel), Vista Premium

**Scan (Standard)**

Scan Speed	77 spm Color / 80 spm B&W, LT-Size @300 dpi
Scan Resolution	150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
File Format	TIFF, PDF, JPEG, XPS, MS Word, MS Excel, Searchable PDF w/ Adv. Scanning option

**E-Filing (Standard)**

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box; 200 Private User Boxes
Capacity of Boxes	100 Folder per Box 400 Documents per Folder 1000 Pages per Documents

**Security (Standard)**

Data Encryption	256 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) standard 5220.22M
Authentication	LDAP, SMTP, Windows Server Domain

**Facsimile Option**

Compatibility	Super G3, G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Appx. 3 Seconds per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	Transmission 500MB (HDD) Reception 500MB (HDD) Backup Permanent (HDD)
Memory Transmission	100 Jobs; 1,000 Destinations Max; 400 Destinations/Job
Scan Speed	0.7 Seconds per Page; 50 Scans per Minute
Other Fax Functions	Internet Fax; Network Fax

**Accessories (Options)**

<b>Finishing Options</b>	
50-Sheet Stapler Console Finisher	MJ1027
50-Sheet Saddle-Stitch Finisher	MJ1028
100-Sheet Saddle-Stitch Finisher	MJ1029
Rails for Finisher	KN1017
2 or 3 Hole Punch Unit	MJ6003
Post Inserter Unit	MJ7001

**Additional Paper Options**

4,000-Sheet LT-Size Large Capacity Feeder	MP4004
---	--------

**Connectivity/Security Options**

Fax Kit	GD1250NXF
2nd Line Fax	GD1260F
Wireless LAN Adapter	GN1060
Antenna	GN3010
IPSec Kit	GP1080
Meta Scan Enabler	GS1010
Advanced Scanning	GB1280T

**Miscellaneous Options**

Smart Card Reader, HID iClass	ART11236
Smart Card Reader, HID Prox	ART11230
Smart Card Reader, Inditag	ART12161
Smart Card Reader, LEGIC	ART11248
Smart Card Reader, Multi ISO/Mifare	ART12443
Smart Card Reader, Multi 125	ART11242
Card Reader Bracket	6BC02231846
Harness Kit for Coin Controller	GQ1240



**Corporate Office**

2 Musick, Irvine, CA 92618-1631

Tel: 949-462-6000

**East Coast**

959 Route 46 East, 5th Floor, Parsippany, NJ 07054

Tel: 973-316-2700

**Midwest**

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631

Tel: 773-380-6000

**South**

2037 Bakers Mill Rd., Dacula, GA 30019

Tel: 678-546-9385

**West Coast**

142 Technology, Suite 150, Irvine, CA 92618

Tel: 949-462-6262

**Web Site**

www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for Availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.