

- > Black & White MFP
- > Up to 85 PPM
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered*



C:studio 557/657/757/857

C:studio 557/657/757/857





- Black & White MFP
- > Up to 85 PPM
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- Secure MFP
- > EPEAT Registered*

Specifications

Copying Process/Type	IEPM (Dry Process)/Laser Technology
Original Reading Method	I CCD Line Sensor
Copy/Print Resolution	2400 x 600 dpi
Gradation	256 Steps
Copy/Print Speed	55/65/75/85 PPM
Warm-Up Time	Approx. 130 Seconds
First Copy Time	556/656: Less Than 4.0 Seconds (Letter-Size)
	756/856: Less Than 3.5 Seconds (Letter-Size)
Duty Cycle	460K/515K/540K/600K
Multiple Copying	Up to 9,999 Copies
Standard Paper Supply	2 x 500-Sheet Drawer, 1 x 2,500-Sheet Tandem Drawer,
	100-Sheet Stack Feed Bypass
Maximum Paper Supply	Up to 7,600 Sheets (w/Optional 4,000-Sheet LCF)
Acceptable Paper Size	Cassette: Statement-R to Ledger (17-110 lb)
	Bypass: Statement-R to 11" x 17" (17-110 lb)
	LCF: Letter Only (17-110 lb), Tab Paper
Memory	2GB RAM, 320 GB FIPS 140-2 SED
Reduction/Enlargement	25% to 400%
Bypass Tray	100-Sheet Stack Feed Bypass
Control Panel	9" Wide VGA Color Touch Screen
Dimensions	Approx. 28" x 31" x 46" (W x D x H)
Weight	Approx. 462 lb
Power Supply	120 Volts, 20 Amps
Power Consumption	Maximum 2.0kW
Black Toner Yield	73.9K Impressions

e-BRIDGE Print Specifications

PDL Support Operating Systems	PCL6, PostScript 3, XPS Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO
Protocol Support	Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/ iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP
Drivers	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/q/n, Wireless LAN, USB
Wireless Device	AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)
Device Management	Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software)
Certification	Windows 7, 8, 8.1,2008R2, 2012, 2012 R2, WHQL, Novell, Citrix

Scan Specifications

Scan Speed	77 SPM Color/80 SPM B&W, LT-Size @300 dpi, 66 SPM LT-Size @ 600 dpi (When Copying)
Scan Resolution File Format	Up to 600 dpi TIFF, PDF, JPEG, XPS, MS Word, MS Excel, Searchable PDF w/Adv. Scanning Option

Facsimile Specifications

Compatibility	Super G3, G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Fax Memory	Transmission 500MB (HDD)
	Reception 500MB (HDD)
	Backup Permanent (HDD)
Memory Transmission	100 Jobs, 1,000 Destinations Max, 400 Destinations/Job
Scan Speed	0.7 Seconds Per Page, 50 Scans Per Minute
Other Fax Functions	Internet Fax, Network Fax

e-Filing Specifications

Operation Method Number of Boxes Capacity of Boxes Security (Standa	Color Touch Screen Control Panel or Client PC 1 Public Box, 200 Private User Boxes 100 Folder Per Box 400 Documents Per Folder 1000 Pages Per Documents rd)
Data Encryption	256 Bit AES
HDD Overwrite	Meets Department of Defense (DoD) Standard 5

 HDD Overvrite
 Meets Department of Defense (DoD) Standard 5220.22M

 Authentication
 LDAP, SMTP, Windows Server Domain

Accessories (Options)

Additional Paper Options 4,000-Sheet LT-Size Large Capacity Feeder	MP4004
Finishing Options 50-Sheet Stapler Console Finisher 50-Sheet Saddle-Stitch Finisher 100-Sheet Saddle-Stitch Finisher Rails for Finisher 2/3-Hole Punch Unit Post Inserter Unit	MJ1027 MJ1028 MJ1029 KN1017 MJ6003 MJ7001
Connectivity/Security Options	
Connectivity/Security Options Fax Kit 2nd Line Fax	GD1350 GD1260F
Fax Kit 2nd Line Fax Wireless LAN Adapter	GD1260F GN1060
Fax Kit 2nd Line Fax Wireless LAN Adapter Antenna	GD1260F GN1060 GN3010
Fax Kit 2nd Line Fax Wireless LAN Adapter	GD1260F GN1060
Fax Kit 2nd Line Fax Wireless LAN Adapter Antenna Advanced Scanning	GD1260F GN1060 GN3010 GB1280T



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631
	Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054
	Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
	Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019
	Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618
	Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

@ 2014 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv. Code: 22256 557/657/757/857 Spec Sheet ~6K PG 6/14