



Save time and increase efficiency with auto two-sided , multiple page scanning.

**Scan resolution:** 2400 x 2400 dpi<sup>1</sup>, 48 bit color depth, 256 grayscale levels

**Scan speed Preview mode:** Up to 7 sec<sup>2</sup>

**Scan media types:** Paper (banner, inkjet, photo, plain), envelopes, labels, cards (greeting, index), 3-D objects, 35 mm slides and negatives (using transparent materials adapter), iron-on transfers

**Enlargement range:** 10 to 2000% in 1% increments

**Features:** 50 sheet Automatic document feeder (two-sided), Transparent materials adapter: scans three slides or four 35 mm negative frames



## Two-sided, multi-page scans

- Unattended two-sided, multi-page scanning with included automatic document feeder.

## Fast

- Scan up to 8 pages—or 4 images—per minute and preview scans in about 7 seconds.
- Scan, copy, print, e-mail, and more—many features available using one-touch buttons.
- Plug and play using Hi-Speed USB-compatible with USB 2.0 specifications.
- Scan and e-mail photos and documents—no slow downloads or large attachments.

## Easy document management

- Scan documents with existing data management systems or included software.
- Choose copy quantity, settings, and more using convenient copy center buttons.

## Professional results

- High resolution scanning at 2400 dpi optical resolution and 48-bit color.
- Easy to learn and use software for graphic arts and digital photography projects.

## Scan more

- Scan slides and negatives with adapter, plus scan books, documents, 3-D objects, and more.

<sup>1</sup>The maximum dpi at which you can scan is limited by available computer memory, disk space, and other system factors.

<sup>2</sup>Scan speed: tests performed on a 1.7 GHz HP Vectra PC with 256 MB of RAM and Windows 2000.

