

TS654dn

Robust, ultra-fast and incredibly versatile, the Lexmark TS654dn fits every type of need. Whether you're looking for a serious performer for high-volume printing or an effective solution for printing on a wide range of media, this powerful monochrome laser printer delivers the ultimate combination of quality, low ownership costs and outstanding reliability.



Power and versatility for heavy business printing

Lexmark TS654dn

- Rock-solid reliability
- Fast print speeds, up to 55 ppm
- Powerful performance, 600MHz processor and 256MB standard memory
- Impressive print quality, up to 1200 x 1200 dpi
- Automatically adjusts toner darkness for consistent results page after page
- Ultra-reliable paper feeding supports diverse media, including card stock and labels
- Stapler option with 50-sheet capacity
- Optional drawers expand your input capacity up to 4,300 sheets
- Install up to two 5-bin mailboxes to personalize output options
- Job Waiting keeps your print queue flowing
- Eco-Mode reduces power consumption
- Optional extra-high-yield toner cartridges can conserve resources



TS654dn

For Midsize to Large Workgroups.



PRINT



DUPLEX
AVAILABLE



UP TO 55 PPM
MONO



NETWORK



MONO

The Competitive Edge.

| SPECIFICATIONS | Lexmark TS654dn | Samsung ML-4551N | HP P4015n |
|-------------------------|---------------------------------|--|---|
| Speed (ppm) | 55 | 45 | 52 |
| Processor (MHz) | 600 MHz | 500 MHz | 540 MHz |
| Memory Std / Max | 256 / 640 MB | 128/512 MB | 128 / 640 MB |
| TTFP - Ready/cold (sec) | 8.5 / <30 | 8.5 / NA | 8.5 / 8.5 |
| Resolution | 1200 x 1200, 2400 Image Quality | 1200 x 1200 | 1200 x 1200 |
| Emulation | PCL6, PS3, PPDS, PDF direct | PCL6, PS3, IBM ProPrinter, Epson, PDF direct | PCL5, PCL6, PS3 emulation, direct PDF (with 128 MB) |
| Connectivity - Ethernet | 10/100 | 10/100 | Gigabit |
| Acoustics dB(A) | 55 (51 at 35 ppm) | 60 | 58 |
| Input (Std./Max.) | 100+550 / 4300 | 100+500 / 2100 | 100+500 / 3100 |
| Output - face down+up | 550 | 250 + 100 | 500 + 100 |
| Duplex | Standard | Optional | Optional |

The Product.

| Description | Lexmark Part Number |
|--|---------------------|
| Lexmark TS654dn Monochrome Laser Printer | 30G0115 |



Lexmark reserves the right to change specifications or other product information without notice. LEXMARK PROVIDES THIS PUBLICATION "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Lexmark and Lexmark with diamond design are trademarks of Lexmark International, Inc. registered in the United States and/or other countries. All other trademarks are the property of their respective owners. © 2007 Lexmark International, Inc. 740 W. New Circle Rd., Lexington, KY 40550.

LEXMARK
TM