



XS658dfe
XS658dme

Easy. Smart. Fast.

High performance monochrome MFPs for large workgroups



XS658dfe



Why Lexmark?

Founded from an IBM heritage in Lexington, Kentucky, in 1991, Lexmark is one of the few American companies to own, develop and market inkjet, laser and color laser print technologies. As a long-term member of the Fortune 500, Lexmark is poised to deliver on its promise to produce quality, dependable products well into the future.

We listen to our customers and
we deliver solutions.
Raise your expectations, because
we are raising the bar.



Lexmark cares

When it comes to our planet, we know there is no substitute. We strive to provide industry-leading environmental practices that relate not only to our products, but also to everything we do, everywhere in the world. For more details on our environmental, health and safety practices, visit our website at www.lexmark.com.



Over **75 percent** of the world's top banks, retailers and pharmacies use Lexmark.

It's time to put Lexmark to work for you.
To read about our customers, visit
www.lexmark.com/casestudies.



LEXMARKTM

Outstanding Performance



Be more productive

- High-performance, space-saving multifunction laser
- Unique business solutions help you work smarter, not harder
- Intuitive, customizable touch screen for effortless operation
- Secure erase and data encryption for peace-of-mind
- Advanced media handling, including labels, card stock, envelopes and more
- High-capacity cartridges reduce printing costs and run longer with less waste

Lexmark's multifunction devices are **Easy.**
Smart.
Fast.




Easy

e-Task interface

The Lexmark e-Task interface is the entry point to your Lexmark multifunction device. It's a customizable touch screen with capabilities for high-demand multitasking. The e-Task interface requires virtually no set-up or installation and can be easily integrated with your network.

Lexmark's workflow software enables your business to print less, move more information fast, and manage documents more effectively.



embedded Solutions Framework (eSF)

Lexmark's eSF gives you control to accomplish a variety of tasks from the multifunction device, through an intuitive Java®-based platform. We offer a wide variety of embedded applications such as:



Card Copy - This innovative feature helps save paper and time by copying both sides of an insurance or ID card onto the front of a single sheet of paper.



Customer Support Application - An icon on the e-Task interface will link directly to your dealer's contact information for quick and easy service and supplies calls.



Remote Copy - Users can scan a document in full color from the mono MFP to be printed on a remote Lexmark color printer.



Forms on Demand - Users choose and then print selected forms right from the MFP touch screen.



Green Copy - This innovative feature helps save paper and toner, helping offices run more efficiently.

MFP Usage - This application tracks copy, fax, e-mail, and FTP usage on an MFP that has a hard drive. Statistics can be sent via email, FTP or to a network share on a scheduled basis.



Lexmark keeps you secure

Lexmark's MFPs and printers support industry best practices for network device protection, and Lexmark's enhanced security features seamlessly help protect user data without sacrificing performance.

- Confidential print
- Operator panel lock
- Secure data encryption and disk wiping
- MFP lockout
- IPSec, SNMPv3 and 802.1x network security
- IPV6
- Secure user authentication
- Industry-leading access restrictions, including LDAP
- HTTPS
- Proactively tracks and identifies security risks
- Physical locking capabilities (Kensington™)

Vertical Solutions

Lexmark offers a wide variety of bundled software solutions to help customers be more productive and work smarter.



Education Station

Solution integrated into the educational space where classroom testing and paperwork tasks can be performed with just one touch. Consists of Scan to Classroom, Print Test, Grade Test and Forms on Demand.



Clinical Assistant

Solution for the healthcare industry designed to save clinicians time and improve patient care by streamlining common healthcare workflow processes. Consists of Scan to EMR, Physician Order Routing, Forms on Demand and Card Copy.



Legal Partner

Solution for the legal industry designed to simplify law office workflow processes. Consists of Scan to Court, Scan to Network, Copitrak-Capable and Custom Screensaver.*

*Planned availability Q1 2009.

Fast

Network management

Easy network management is accomplished by well-designed tools that facilitate device administration—streamlining workflow in daily business operations. We understand networks.

Lexmark MarkVision Professional provides network administrators with timesaving and easy-to-use print management applications.

The **Lexmark embedded web server** provides administrators access to embedded web pages in order to view, monitor and configure the multifunction device directly from the user's computer.



Scanning capabilities

Lexmark provides a variety of scanning options, in monochrome and color. It is a fast, convenient way to communicate with colleagues and customers by scanning documents to your e-mail, desktop, network folder or FTP.

Scan Preview - Preview document prior to sending to ensure accuracy.

Scan to E-mail - With a single touch of a button, easily scan your paper based documents to e-mail accounts or groups. Seamlessly integrates into your corporate LDAP directory.

Scan to Desktop - Multiple ways to scan documents to a PC/desktop. The scanned file can be sent to an individual workstation via web browser, ScanBack utility, local or network TWAIN driver or scan to network embedded solution.

Scan to FTP - Ideal way to archive and share large files with multiple people.

Scan to Network - Users can scan documents to a shared network folder or to a desktop with the click of a button, saving space on the server and improving productivity.

LDAP/Active Directory can be used by the MFP to authenticate user credentials, and to look up e-mail or fax numbers from the corporate directory during scan-to-e-mail or scan-to-fax operations.

Quickly and easily scan and archive documents in a wide variety of file formats including: TIFF, MTIFF, JPEG, PDF and XPS.

Feature Gallery



XS658dfe
with additional
paper drawer
and integrated
card reader

1



Single-Pass Duplex Scanning

Scan two-sided
mono or color
jobs fast with
up to 75-sheet
capacity ADF

2



9-inch Color Touch Screen

Easy access to
a rich range of
functions and
features

3



Direct USB

Front USB port
for walk-up
printing and
scanning to
memory device
of certain file
formats

4



Easy Authentication

Can be
customized with
an integrated card
reader option for
security and ease
of use

5



Staple Smart II™ Finisher

Staples sets
of up to
50 pages

6





Paper Possibilities

Standard input
drawers hold up
to 550 sheets
each, maximum
input is up to
2,300 sheets

Space-saving design provides small footprint with exceptional performance.

Product Configurations



Configurations	 <p>XS658dfe - with StapleSmart II™ Finisher</p>	 <p>XS658dme - with 4-bin Mailbox</p>
Speeds	Black: Copy, Print, Scan up to 55 ppm	
Paper Handling	Paper Capacity: Standard Input: 1,200 (550 + 550 + 100 Bypass) Standard Output: 1,050 Maximum Input: 2,300 (550 + 550 + 550 + 550 + 100 Bypass) Maximum Output: 1,050	Paper Capacity: Standard Input: 1,200 (550 + 550 + 100 Bypass) Standard Output: 1,050 Maximum Input: 2,300 (550 + 550 + 550 + 550 + 100 Bypass) Maximum Output: 950
	Media Information: Types: Plain Paper, Paper Labels, Card Stock, Transparencies, Envelopes, Vinyl Labels, Polyester Labels, Dual Web and Integrated Labels Size: Letter, Legal, A4, A5, JIS B5, Executive, Folio, Statement, Universal (2.75 in. x 5 in. to 8.5 in. x 14 in.), Envelopes (7-3/4, 9, 10, DL) Weight: Plain Paper: 16 to 36 lb. (60 to 135 g/m ²); Card Stock: Up to 90 lb. Index (163 g/m ²)	
	ADF Capacity: Up to 75 sheets	
Copy	Memory: 256MB/1280MB Time to First Page: As Fast as 7.5 seconds Copy Resolution: Up to 600 x 600 dpi Copy Features: Reduce/Enlarge (25-400%), Paper Saver (2-up and 4-up), Collation, Darkness Adjustment, Original Size to Output Size Selection, Copy Select 1-999, Date/Time Stamp, Single-pass Duplex, Message Overlay, Priority Copy (Job Interrupt), Copy Countdown	
Print	Resolution: 2400 Image Quality Processor: 600 MHz Hard Drive Size: 80GB Connectivity (Standard): Ethernet, High Speed USB-A, High Speed USB-B, USB Direct Interface Connectivity (Optional): Parallel, Serial, Wireless, Card Reader	
Fax	Resolution: 200 x 100 dpi, 200 x 200 dpi, 300 x 300 dpi, 600 x 600 dpi Fax Features: Fax Redirect, Group Fax, Manual Fax, Fax from PC, up to 512-Character Shortcuts, Fax Preservation, LDAP Look-up, Caller ID, Speed Dials, Block Junk Faxes, Broadcast, Fax Shortcuts, Fax Forwarding	
Scan	Scan Features: Resolution: up to 600 x 600 dpi Black and Color Scan Destinations: USB Thumb Drive, E-mail, FTP, LDSS, Network or USB Connected Computer, Windows Network Folder File Formats: TIFF, MTIFF, JPG, PDF, XPS	
Supplies Yield	Toner Cartridges: These models ship with an 18,000*-Page Yield Print Cartridge. Aftermarket 36,000*-Page Extra High Yield Print Cartridge available. *Average standard page yield value declared in accordance with ISO/IEC19752.	
Recommended Monthly Volume	5,000 - 30,000 Pages per Month	
Other Options	Contact your dealer about Lexmark integrated card reader or other workflow solutions.	

Part #	Memory Options
1025041	256MB DDR2-DRAM
1025042	512MB DDR2-DRAM
1025043	1024MB DDR2-DRAM
14F0245	256MB Flash Card
30G0828	Japanese Font Card
30G0825	Korean Font Card
30G0826	Simplified Chinese Font Card
30G0827	Traditional Chinese Font Card

Part #	Connectivity
1021294	USB (2 Meter) Cable
1021231	Parallel (10") Cable
14F0037	MarkNet N8120 Gigabit Ethernet Print Server
14F0042	MarkNet N8130 Fiber Ethernet 100BaseFX, 10BaseFL Print Server
14F0040	MarkNet N8150 802.11b/g/n Wireless Print Server
14T0145	Lexmark N4050e 802.11g Wireless Print Server
14T0220	MarkNet™ N7020e Gigabit Ethernet Print Server
14F0000	Parallel 1284-B Interface Card
14F0100	RS-232C Serial Interface Card

Part #	Application Solutions
30G0829	Lexmark PrintCryption Card
16M1254	X65x Card for IPDS and SCS/TNE
16M1253	X65x Forms and Bar Code Card

Part #	Paper Handling
16M1100	X658 550-Sheet Drawer
30G0807	Envelope Feeder

