

Affordable, wireless HP LaserJet printing from virtually anywhere in the home or office with several users. Print at up to 19 ppm letter/18 ppm A4 with no need for extra wires.¹ Built-in environmental features can save money and resources.

Print Speed: Black (letter): Up to 19 ppm; Black (A4): Up to 18 ppm Print Resolution: Up to 400 x 600 x 2 dpi (600 dpi effective output) Print Technology Resolution: HP FastRes 600, HP FastRes 1200 Standard Connectivity: Hi-Speed USB 2.0 port, WiFi 802.11 b/g Recommended Monthly Page Volume: 250 to 1,500 Duplex Print Options: Manual (driver support provided)









Print from virtually anywhere in your home or office with wireless networking¹

- Network the printer without extra cables, using 802.11 b/g wireless networking.¹
- Print up to 19 ppm letter/18 ppm A4.
- Start and finish printing sooner with Instant-on Technology.
- Print on a wide variety of media, using the 150-sheet paper tray and 10-sheet priority input slot.

Rely on HP for an easy, dependable printing experience

- Install in a flash—no CD required—using HP Smart Install.²
- Set up and start printing right away with an easy-to-use, intuitive control panel.
- Receive consistent results with Original HP cartridges and easily reorder with HP SureSupply.³
- Get the services, solutions, software and support of HP Total Care.

Meet your environmental goals, while boosting your bottom line

- Conserve energy with Instant-on Technology and save even more with HP Auto-On/Auto-Off Technology.⁴
- Reduce wasted paper by printing only the content you want, using HP Smart Web Printing.⁵
- Save space with an ultra-compact printer with a sleek, industrial design.
- HP helps reduce your impact—less packaging, plus free cartridge recycling with HP Planet Partners.⁶

Create professional documents that make a statement for your business, while keeping your bottom line in check

- Produce professional-quality business prints with bold, crisp text and sharp images.
- Receive improved print quality with HP FastRes 1200.7

COHIGHLIGHTS HP LASERJET PRO P1102W PRINTER

- Reduce energy use up to 50% with Instant-on Technology.¹
- Save energy—HP Auto-On/Auto-Off Technology turns your printer on when you need it, off when you don't.²
- Print only the Web content you need with HP Smart Web Printing.³

ENERGY STAR® Qualified Product

¹Energy savings based on HP testing using ENERGY STAR® program's Typical Energy Consumption (TEC) method on HP LaserJet products with Instant-on Technology vs. top competitive models as of March 2009. ²/₄P Juto Do and Juto Off competitive whilet to priptic and settings

²HP Auto-On and Auto-Off capabilities subject to printer and settings ³Requires Internet Explorer 6.0–8.0.

WWW.hp.com/ecosolutions Please recycle your computing hardware and printing supplies.

¹Wireless performance is dependent upon physical environment and distance from access point. ²For Microsoft Windows only. Installation time may vary. ^{3p}rogram features and availability may vary by country. For more information, visit http://www.hp.com/learn/suresupply. ⁴HP Auto-On and Auto-Off capabilities subject to printer and settings. ³To use this feature, you need Internet Explorer 6.0-8.0. ⁶ HP print cartridge return and recycling is available in 49 countries and territories around the world, covering 88% of the addressable market; see <u>http://www.hp.com/recycle</u> for details. ³HP FastRes 1200 provides the best print quality setting for this device. Choose HP FastRes 600 for fast printing.















PRINT TECHNOLOGY	Laser	OPERATING	Opero
PRINT SPEED ¹	Black (letter): Up to 19 ppm; Black (A4): Up to 18 ppm	ENVIRONMENT	Recom Opera Recom
FIRST PAGE OUT	As fast as 8.5 seconds from Ready mode (letter)		(17.5
PRINT RESOLUTION	Black (best): Up to 600 x 600 x 2 dpi (1200 dpi effective output); Black (normal): Up to 400 x 600 x 2 dpi (600 dpi effective output)		Maxin Storag Non-C
PRINT TECHNOLOGY RESOLUTION	HP FastRes 600, HP FastRes 1200	ACOUSTICS	Acous Acous Acous
STANDARD PRINTER LANGUAGES	Host-based printing	POWER	Acous
NUMBER OF PRINT CARTRIDGES ²	1 (black)		60 Hz (+/- 2
SURESUPPLY SUPPORTED ³	Yes		Power Power
PRINTER MANAGEMENT	HP Status and Alerts, HP Usage tracking (CD install only)		(Auto-
STANDARD CONNECTIVITY	Hi-Speed USB 2.0 port, WiFi 802.11 b/g		ENER
WIRELESS CAPABILITY	Yes, WiFi 802.11 b/g		http://
NETWORK CAPABILITIES	Via built-in WiFi 802.11 b/g wireless network	PRODUCT DIMENSIONS	WXD
OPTIONAL CONNECTIVITY	HP Jetdirect en3700 Fast Ethernet Print Server; HP Jetdirect en1700 IPv4/IPv6 Print Server;	PRODUCT WEIGHT	Maxin 11.6
CONTROL PANEL	HP Jetdirect ew2500 802.11g Print Server 3 LED indicator lights (Wireless, Attention, Ready); 2 buttons (Wireless, Cancel)	WHAT'S IN THE BOX	HP Las print c docum
Recommended media Weight (Duplex)	16 to 28 lb	ACCESSORIES	Install Hi-Spe
RECOMMENDED MONTHLY PAGE VOLUME	250 to 1,500	REPLACEMENT CARTRIDGES	HP Las
MAXIMUM/STANDARAD	8 MB	WARRANTY	One-y
MEMORY MEDIA TYPES SUPPORTED	Paper (laser, plain, photo, rough, vellum), envelopes, labels, cardstock, transparencies, postcards	HP CARE PACK SERVICES	UG60 UG60 UH60
MEDIA SIZES SUPPORTED	Letter, legal, executive, postcards, envelopes (No. 10, Monarch)		US284
CUSTOM MEDIA SIZES	150-Sheet input Tray: 5.8 x 8.27 to 8.5 x 14 in; Priority Feed Slot: 3 x 5 to 8.5 x 14 in		with w US285 setup
PAPER HANDLING	Input Capacities: 10-sheet priority feed slot, 150-sheet input tray, Up to 160 sheets, Up to 15 envelopes Output Capacities: 100-sheet face-down bin, 100 sheets, Up to 15 envelopes, Up to 100 sheets transparencies	ADDITIONAL INFORM BUSINESS UNIT	
DUPLEX PRINT OPTIONS	Manual (driver support provided)	COUNTRY OF ORIGIN	Produ
PROCESSOR	Tensilica/266 MHz	MATERIAL TYPE CODE	FERT
SOFTWARE INCLUDED	HP Usage tracking, HP Status and Alerts, CD Launch Pad,	TARIFF NUMBER	84433
	Control Panel Simulator, Print Driver, Software Installer/Uninstaller	PALLET INFORMATION	Dimen Weigł
MINIMUM SYSTEM REQUIREMENTS	PC: Microsoft® Windows® 7 (32-bit/64-bit): 1 GB RAM, Windows Vista® (32-bit/64-bit), Windows® XP, Windows® Server 2008 (32-bit/64-bit), Windows® Server 2003: 512 MB RAM, all systems: 350 MB free hard disk space, CD-ROM drive, USB port; Mac: Mac OS X v 10.4, 10.5, 10.6, 256 MB RAM, 150 MB available hard disk space, CD-ROM drive, USB port		Layers
COMPATIBLE OPERATING SYSTEMS	Microsoft® Windows® 7 (32-bit/64-bit), Windows Vista® (32-bit/64-bit), Windows® XP (32-bit/64-bit), Windows® Server 2008 (32-bit/64-bit), Windows® Server 2003 (32-bit/64-bit), Mac OS X v 10.4, v 10.5, v 10.6, Linux (see http://www.hplip.net for current)		

OPERATING ENVIRONMENT	Operating Humidity Range: 10 to 80% RH; Recommended Humidity Operating Range: 30 to 70% RH; Operating Temperature Range: 15 to 32.5° C; Recommended Operating Temperature Range: 63.5 to 77° F (17.5 to 25° C); Maximum Operating Temperature Range: 59 to 90.5° F; Storage Temperature Range: -4 to 104° F (-20 to 40° C); Non-Operating Humidity: 10 to 90% RH	
ACOUSTICS	Acoustic Power Emissions: 6.4 B(A); Acoustic Power Emissions (Ready): Inaudible; Acoustic Pressure Emissions: 50 dB(A); Acoustic Pressure Emissions Bystander (Ready): Inaudible	
POWER	Power Requirements: Input voltage 115 to 127 VAC (+/- 10%), 60 Hz (+/- 2 Hz), 12 amp; 220 to 240 VAC (+/- 10%), 50 Hz (+/- 2 Hz), 6.0 amp; Power Supply Type: Internal; Power Consumption ⁴ : 370 watts active, 0.6 watts off, 2.0 watts (Auto-Off) powrsave, 2.7 watts standby ENERGY STAR [®] qualified models; see http://www.hp.com/go/energystar	
PRODUCT DIMENSIONS	W X D X H: 13.74 x 9.38 x 7.71 in (349 x 238 x 196 mm) Maximum: 13.74 x 16.15 x 8.98 in	
PRODUCT WEIGHT	11.6 lb (5.3 kg)	
WHAT'S IN THE BOX	HP LaserJet Pro P1102w Printer, introductory HP LaserJet Black print cartridge, power cord, CD(s) with printer software and documentation, Getting Started Guide, support flyer, Smart Install Flyer, USB install cable (1m)	
ACCESSORIES	Hi-Speed USB A to B printer cable (6 ft./1.8-meter, Q6264A	
REPLACEMENT CARTRIDGES	HP LaserJet Black Print Cartridge, CE285A	
WARRANTY	One-year limited warranty	
HP CARE PACK SERVICES	UG605E, HP 2-year NBD ExchPrinting and Imaging-M SVC UG608E, HP 3-year NBD ExchPrinting and Imaging-M SVC UH609E, HP 4-year NBD ExchPrinting and Imaging-M SVC US284E, HP Basic Installation Service for one consumer printer with wireless capability US285E, HP Premium Installation Service with wireless network setup for up to three PCs and/or printers	

N

BUSINESS UNIT	Transaction Laser Products
COUNTRY OF ORIGIN	Product of Vietnam
MATERIAL TYPE CODE	FERT
TARIFF NUMBER	8443321020
PALLET INFORMATION	Dimensions: 47.3 x 39.4 x 100 in Weight: 1390 lb Layers: 8

FOR MORE INFORMATION VISIT OUR WEBSITE AT WWW.HP.COM HP LASERJET PRO P1102W PRINTER Product Number: CE657A

¹Exact speed varies depending on the system configuration, software application, driver and document complexity. ²Introductory cartridge included; yields ~700 pages. Replacement cartridge declared yield ~1600 pages based on ISO/IEC 19752 and continuous printing. Actual yields vary considerable based on images printed and other factors. For details entry, only of the print of the pri are the highest values measured using all standard voltages.

©2010 Hewlett-Packard Development Company, L.P. HP is a registered trademark of the Hewlett Packard Company. ENERGY STAR and the ENERGY STAR logo are registered U.S. marks. All other trademarks are the property of their respective owners. Microsoft and Windows are registered trademarks of Microsoft Corporation. Adobe and Acrobat are trademarks of Adobe Systems Incorporated. This listing of non HP products does not constitute an endorsement by Hewlett Packard Company. The information contained herein is subject to change without notice and is provides "as is" without warranty of any kind. HP shall not be liable for technical or editorial errors or omissions contained herein. July 2010, Rev 1