



LASERJET ENTERPRISE M4555 MFP SERIES

M4555h • M4555f • M4555fskm

Achieve versatile, powerful MFP performance for a more productive printing environment. Print and copy at high speeds, use image preview to process jobs from the HP Easy Select pivoting color control panel and get robust paper handling up to 2100 sheets.¹ Expand the functionality of imaging and printing devices with market-leading management and extensibility. This ENERGY STAR[®] qualified MFP can help save on energy and paper, and advanced security features can help protect sensitive data.



Productive, dependable performance

- Stay productive with high performance speeds—print and copy at up to 55 ppm.²
- Boost productivity—get up to 2100-sheet paper capacity for large printing jobs from this workhorse MFP.¹
- Preview jobs using the pivoting color control panel and use image preview to make adjustments to scan jobs.
- Save time with easy installation, and get exceptional value from optional high-capacity print cartridges.³



Market-leading manageability and extensibility

- Proactively manage printing environments and get easy setup and configuration with HP management tools.
- Extend the capabilities of workgroup print environments with a rich portfolio of easy-to-integrate solutions.
- Easily update, manage and expand the capabilities of networked printers with HP FutureSmart Firmware.
- Make printing as mobile as you are with HP ePrint.



Advanced security for sensitive information

- Protect sensitive data stored on the HP MFP with the standard encrypted HP High-Performance Secure Hard Disk.
- Process jobs securely through user authentication, IPsec and IPv6.
- Create, print, scan and share sensitive business information securely via encrypted email and PDFs.
- Add optional authentication security solutions through the control panel's hardware integration pocket.⁷



Outstanding energy- and paper-saving features

- Reduce energy use with Instant-on Technology and Instant-on Copy.⁵
- Conserve resources and save paper—use automatic two-sided printing and PIN printing.
- Original HP LaserJet print cartridges with energy-efficient toner enable an energy savings of over 18%.⁴
- Get free, easy cartridge recycling,⁶ plus reduce shipping materials with HP ClearView packaging.

ecoHIGHLIGHTS

HP LaserJet Enterprise M4555 MFP series

ECO INFORMATION

- Reduce energy use with Instant-on Technology and Instant-on Copy.¹
- Reduce paper use by up to 50% using automatic two-sided printing.
- Reduce clutter and waste—scan, store and share documents digitally.

¹Compared with products that use traditional fusing and cold cathode fluorescent lamp (CCFL) copying.



ENERGY STAR[®] Qualified Product

www.hp.com/ecosolutions

Please recycle your computing hardware and printing supplies. HP asset management and recycling services make responsible disposal easy.




¹The 500-sheet feeder, 1 x 500 sheet feeder with cabinet and 3 x 500 sheet feeder with stand may be purchased separately for the HP LaserJet Enterprise M4555 MFP and the HP LaserJet Enterprise M4555h MFP. The 3 x 500 feeder with stand may be purchased separately for the HP LaserJet Enterprise M4555f MFP. ²Measured using ISO/IEC 24734, excludes first set of test documents. For more information see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ³The HP LaserJet CE390X Black Print Cartridge not included; please purchase separately. ⁴Energy savings based on comparing conventional toner and print system used in HP LaserJet M4345 MFP series with energy-efficient HP toner and print system used in HP LaserJet Enterprise M4555 MFP series. Testing per Energy Star Typical Electricity Consumption test. Actual savings may vary. ⁵Compared with products that use traditional fusing and cold cathode fluorescent lamp (CCFL) copying. ⁶Program availability varies. HP print cartridge return and recycling is currently available in more than 50 countries and territories around the world through the HP Planet Partners program. For more information, or to request return envelopes and bulk collection boxes, visit <http://www.hp.com/recycle>. ⁷Solutions deployed through the hardware integration pocket may require additional purchase.

HP LASERJET ENTERPRISE M4555 MFP SERIES

- 1 Intuitive HP Easy Select pivoting touch screen color control panel
- 2 Walkup USB port
- 3 Hardware Integration Pocket for solution integration
- 4 900-sheet 3-bin stapling mailbox
- 5 Built-in automatic two-sided printing
- 6 Four 500-sheet input trays for a 2,100-sheet total input capacity
- 7 50-sheet ADF scanner processes two-sided documents. Plate-glass scanner handles documents up to legal size
- 8 Top cover release lever allows convenient access to the toner cartridge
- 9 100-sheet multipurpose tray 1 handles heavy custom media
- 10 Hi-Speed USB 2.0 port
- 11 Access port for optional Kensington-style lock
- 12 HP Jetdirect Gigabit Ethernet embedded print server
- 13 1280 MB total memory and an 800 MHz processor quickly handle complex print jobs
- 14 Embedded HP Secure High Performance Hard Disk
- 15 One open EIO slot
- 16 RJ-11 fax port

HP LaserJet Enterprise M4555f/skm MFP shown



Series at a glance



	M4555h MFP	M4555f MFP	M4555f/skm MFP
Part number	CE738A	CE503A	CE504A
100-sheet multipurpose tray 1	√	√	√
500-sheet tray 2	√	√	√
500-sheet Paper Feeder	Optional		
1 x 500-sheet Paper Feeder with Cabinet	Optional	√	
3 x 500-sheet Paper Feeder with Stand	Optional	Optional	√
75-sheet Envelope Feeder	Optional	Optional	Optional
500-sheet Output Bin	√	√	
900-sheet 3-bin Stapling Mailbox	Optional	Optional	√
HP Secure High Performance Hard Disk	√	√	√
HP LaserJet MFP Analog Fax Accessory 500	Optional	√	√

TOP FEATURES

Maximize uptime with a productive MFP. Print and copy at up to 55 ppm,² and manage tasks from the HP Easy Select pivoting color control panel. Get paper capacity up to 2,100 sheets,¹ plus great value with optional high-capacity cartridges.³

Invest in an MFP that integrates into IT-managed print environments. Management tools monitor products and settings to control productivity and quality. Do more with the MFP—deploy HP and partner solutions via the hardware integration pocket.⁶

Stay in control of sensitive data and information with impressive security features from this MFP. The HP High-Performance Secure Hard Disk helps keep stored data secure.⁵ Process print jobs securely, and easily create encrypted emails and PDFs.

Conserve resources and meet environmental goals with this ENERGY STAR® qualified MFP. Save paper with automatic two-sided printing. Original HP LaserJet print cartridges with energy-efficient toner enable over 18% energy-savings with every print.⁴

Get the most out of your printer with HP accessories, supplies, and services.

HP Services

Because downtime can have serious business consequences, HP provides high-quality services that extend beyond the standard warranty and help you avoid unbudgeted repair costs. Benefits include reduced printing and infrastructure costs, maximized uptime, expert technical phone support, and predictable, consistent service delivery— even across multiple locations.

Recommended services:

- Same Day Onsite Service: An HP technician or authorized service provider arrives at your site within four hours after the service call is received, if this time falls within the coverage window
- Next Day Onsite Service: Technician delivered onsite service the next business day after the service call is received

These services and additional coverage options can be purchased as:

- HP Care Pack Services: easy-to-buy, easy-to-use support packages
- HP Contractual Services: a comprehensive portfolio for maintaining maximum IT availability

For more information visit: www.hp.com/go/printservices

MFP

HP LaserJet Enterprise M4555h MFP	CE738A
HP LaserJet Enterprise M4555f MFP	CE503A
HP LaserJet Enterprise M4555fsm MFP	CE504A

HP LaserJet Print Cartridges⁷

HP 90A Black LaserJet Toner Cartridge with Smart Printing (~ 10,000 pages)	CE390A
HP 90X Black LaserJet Toner Cartridge with Smart Printing (~ 24,000 pages)	CE390X

Accessories

1 x 500-sheet paper feeder with cabinet	CE734A
3 x 500-sheet paper feeder with stand	CE735A
3-bin, 900-sheet stapling mailbox	CE736A
500-sheet paper tray	CE737A
Staple cartridge refill	C8091A
75-sheet Envelope feeder	CB524A
110V Maintenance Kit	CE731A
220V Maintenance Kit	CE732A
ADF Printer Maintenance Kit	CE248A
HP LaserJet MFP Analog Fax Accessory 500	CC487A
HP BarCode Printing USB Solution	HG271US
HP BarCodes and More USB Solution	HG281US
HP Scalable BarCode Set USB Solution	HG282UT
HP MICR USB Solution	HG283US

HP Care Pack Services

HP 3y NBD LaserJet M4555 MFP HW Support	HN909E
HP 4y NBD LaserJet M4555 MFP HW Support	HP562E
HP 5y NBD LaserJet M4555 MFP HW Support	HP557E
HP 1y PW NBD LaserJet M4555 MFP Support	HP567PE
HP 2y PW NBD LaserJet M4555 MFP Support	HP564PE
HP Network Install mid-range LaserJet MFP SVC	U2010E

Connectivity

HP Jetdirect 635n IPv6/IPsec Print Server	J7961G
HP Jetdirect 690n IPv6/IPsec 802.11g Wireless Print Server	J8007G
HP Jetdirect ew2500 802.11b/g Wireless Print Server	J8021A

Paper

www.hp.com/go/paper

Software

HP Web Jetadmin: www.hp.com/go/wja
HP Easy Printer Care: www.hp.com/go/easyprintercare
HP Universal Print Driver: www.hp.com/go/upd
HP Install Network Printer Wizard: www.hp.com/go/inpw_sw

¹The 500-sheet feeder, 1 x 500 sheet feeder with cabinet and 3 x 500 sheet feeder with stand may be purchased separately for the HP LaserJet Enterprise M4555 MFP and the HP LaserJet Enterprise M4555h MFP. The 3 x 500 feeder with stand may be purchased separately for the HP LaserJet Enterprise M4555f MFP. ²Measured using ISO/IEC 24734, excludes first set of test documents. For more information see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ³The HP LaserJet CE390X Black Print Cartridge not included; please purchase separately. ⁴Energy savings based on comparing conventional toner and print system used in HP LaserJet M4345 MFP series with energy-efficient HP toner and print system used in HP LaserJet Enterprise M4555 MFP series. Testing per Energy Star Typical Electricity Consumption test. Actual savings may vary. ⁵The HP High-Performance Secure Hard Disk not included on the HP LaserJet Enterprise CM4555 MFP; only available through upgrade. ⁶Solutions deployed through the hardware integration pocket may require additional purchase. ⁷Declared yield value for black cartridge in accordance with ISO/IEC 19752. Actual yields vary considerably based on images printed and other factors. For more information, visit <http://www.hp.com/go/learnaboutsupplies>

HP LASERJET ENTERPRISE M4555 MFP SERIES

Technical specifications	HP LaserJet Enterprise M4555h MFP (CE738A)	HP LaserJet Enterprise M4555f MFP (CE503A)	HP LaserJet Enterprise M4555fsm MFP (CE504A)
Print Speed¹	Black: Up to 55 ppm letter		
Copy Speed	Black: Up to 55 cpm letter		
Scan Speed	Letter: Up to 57 ppm (b&w), up to 42 ppm (color)		
First Page Out²	Print: As fast as 9.5 sec; Copy: As fast as 8.5 sec (M4555h & M4555f only)		
Print Resolution	Up to 1200 x 1200 dpi (with HP FastRes 1200)		
Scanning Resolution	Hardware: Up to 600 x 600 dpi; Optical: Up to 600 dpi; 30 bit depth		
Control Panel	Rotating (adjustable angle); 8.07" color graphical display; touchscreen; job control buttons (Start, Stop, Sleep, Reset, Clear, Brightness Up/Down); numeric keypad; LED status lights (Ready, Data, Attention, Sleep); Hardware Integration Pocket; walk-up USB		
Features			
Scanning	Color flatbed scanner or ADF; Scan input modes: Front panel applications: Copy, Scan to E-mail, Save-to-Network Folder, Scan-to-USB, Save to Device Memory, Open Extensibility Platform (EXP) applications		
Copying	Up to 9,999 copies, reduce or enlarge from 25 to 400% (from scanner glass), scaling from 25 to 200% (from ADF)		
Faxing	NA	Fax speed ³ : Up to 33.6 kbps; Fax resolution: Up to 300 x 300 dpi (400 x 400 dpi for received faxes only); Auto Fax Reduction Supported: Yes; Fax Auto-redialing: Yes; Fax Broadcasting, Max Locations: 100; Fax Forwarding Supported: Yes; Fax Polling Supported: Yes (poll to receive only); Fax Speed Dialing, Max Numbers: Up to 100 numbers (each with 100 destinations); Junk Barrier Supported: Yes; PC Interface Supported: Yes	
Processor	Type: Intel LE80578; Speed: 800 MHz		
Memory	1280MB (not expandable) RAM		
Hard Disk	Standard, HP High-performance Secure Hard Disk (embedded)		
Durability Ratings	Duty cycle ⁴ : Up to 250,000 pages (letter); Recommended monthly page volume ⁵ : 5,000 to 20,000 pages		
Paper			
Input	100-sheet multipurpose tray 1, 500-sheet tray 2, 50-sheet automatic document feeder (ADF), automatic two-sided printing	100-sheet multipurpose tray 1, 500-sheet tray 2, 1 x 500-sheet feeder with cabinet, 50-sheet automatic document feeder (ADF), automatic two-sided printing	100-sheet multipurpose tray 1, 500-sheet tray 2, 3 x 500-sheet feeder with stand, 50-sheet automatic document feeder (ADF), automatic two-sided printing
Output	500-sheet output bin		900-sheet, 3-bin stapling mailbox
Two-sided Printing	Automatic		
Media Types	Paper (plain, light, bond, recycled, cardstock), transparency, labels, letterhead, envelope, preprinted, prepunched, colored, rough		
Media Sizes, Standard	Tray 1: 3 x 5 to 8.5 x 14 in; Tray 2: 5.8 x 8.3 to 8.5 x 14 in	Tray 1: 3 x 5 to 8.5 x 14 in; Tray 2-3: 5.8 x 8.3 to 8.5 x 14 in	Tray 1: 3 x 5 to 8.5 x 14 in; Tray 2-5: 5.8 x 8.3 to 8.5 x 14 in
Media Weight	Tray 1: 16 to 53 lb bond (plain), 16 to 24 lb (envelopes); Tray 2: 16 to 32 lb bond (plain)	Tray 1: 16 to 53 lb bond (plain), 16 to 24 lb (envelopes); Tray 2-3: 16 to 32 lb bond (plain)	Tray 1: 16 to 53 lb bond (plain), 16 to 24 lb (envelopes); Tray 2-5: 16 to 32 lb bond (plain)
Interfaces	1 Hi-Speed USB 2.0 Host port; 1 Hi-Speed USB 2.0 Device port; 1 Gigabit Ethernet 10/100/1000Base-TX network port; 1 open EIO slot; 1 Foreign Interface port; 1 Hardware Integration Pocket; 3 Internal USB Host ports		
Languages	HP PCL 6, HP PCL 5c (HP PCL 5c driver available from the Web only), HP postscript level 3 emulation, native PDF printing (v 1.4)		
Network Capabilities	Via HP Jetdirect Gigabit 10/100/1000Base-TX Ethernet embedded print server (standard); IPsec (standard), 802.11g wireless (optional)		
Fonts	105 internal TrueType fonts scalable in HP PCL, 92 internal scalable fonts in HP postscript Level 3 emulation (Euro symbol built-in); 1 internal Unicode Fonts (Andale Mono WorldType); 2 Internal Windows Vista 8 Fonts (Calibri, Cambria); additional font solutions available via third-party flash memory cards; HP LaserJet Fonts and IPDS Emulation available at http://www.hp.com/go/laserjetfonts		
Network Protocols	IPv4/IPv6: Apple Bonjour Compatible (Mac OS v 10.2.4 or higher), SNMPv1/v2c/v3, HTTP, HTTPS, FTP, TFTP, Port 9100, LPD, WS Discovery, IPP, Secure-IPP, IPsec/Firewall; IPv6: DHCPv6, MLDv1, ICMPv6; IPv4: Auto-IP, SLP, Telnet, IGMPv2, BOOTP/DHCP, WINS, IP Direct Mode, WS Print; Other: NetWare NDS, Bindery, NDPS, iPrint		
Security	Management security: SNMPv3, SSL/TLS, 802.1X authentication (EAP-PEAP, EAP-TLS), IPP over TLS, IPsec/Firewall with Certificate, Pre-Shared Key Authentication, and Kerberos Authentication; Support for WJA-10 IPsec Configuration using IPsec Plug-in		
Dimensions (w x d x h)	31.10 x 20.08 x 22.44 in (790 x 510 x 570 mm)	32.48 x 27.95 x 43.90 in (825 x 710 x 1115 mm)	39.96 x 27.95 x 43.90 in (1015 x 710 x 1115 mm)
Weight (with print cartridges)	115.4 lb (52.5 kg)	166.4 lb (75 kg)	192.9 lb (87.5 kg)
System Requirements, Windows	Microsoft® Windows 7®, Windows Vista®, Windows® XP SP2 or higher, Windows® Server 2003, Windows® Server 2008; operating system compatible hardware system requirements, see http://www.microsoft.com system requirements; 200 MB available hard disk space Mac: Mac OS X v 10.5 or higher; operating system compatible hardware system requirements, see: http://www.apple.com ; 150 MB available hard disk space		
What's in the Box	HP LaserJet Enterprise M4555h MFP (100-sheet multipurpose tray; 500-sheet input tray; HP Jetdirect Gigabit Ethernet embedded print server; Encrypted Hard Disk Drive); HP LaserJet Print cartridge standard capacity; CD with software and documentation; Documentation (Hardware Install Guide, Support flyer, Wall poster); power cord M4555f: As above plus 1 x 500 paper feeder with cabinet; HP Analog fax accessory 500 (built-in); phone cord M4555fsm: As above plus 3 x 500 paper feeder with stand; 900-sheet, 3-bin stapling mailbox; HP Analog fax accessory 500 (built-in); phone cord		
Warranty	One year next day on-site warranty, one year free phone support, chat, and e-mail		

Environmental Ranges

Temperature range	Operating: 10 to 30° C (50 to 86° F) Recommended: 15 to 27° C (59 to 80.6° F) Storage: 0 to 35° C (32 to 95° F)
Humidity range	Operating: 10 to 80% RH Recommended: 30 to 70% RH Non-operating: 10 to 90% RH
Acoustics	
Sound power emissions ⁶	Active, Print: 7.1 B(A), Copy/Scan: 7.2 B(A), Idle/Ready: 4.9 B(A)
Sound pressure (bystander position)	Active, Print: 57 dB(A), Copy/Scan: 58 dB(A), Idle/Ready: 35 dB(A)

Power

Power Supply required	Input voltage: 110 to 127 VAC (+/- 10%), 60 Hz (+/- 2 Hz), 12 A; 220 to 240 VAC (+/- 10%), 50 Hz (+/- 2 Hz), 6 A
-----------------------	--

Power Consumption ⁷	960 watts (Printing), 1024 watts (Copying), 54 watts (Ready), 21.6 watts (Sleep), 0.15 watts (Off)
Typical Electricity Consumption (TEC)	7.349 kWh/Week

Safety approvals and requirements

IEC 60950-1: 2005 (International), EN 60950-1: 2006 +A11 (EU), UL/cUL Listed (US/Canada), GS license (Europe), IEC 60825-1: 2007 (International), EN 60825-1: 2007 (Class 1 Laser/LED Device), Low Voltage Directive 2006/95/EC with CE Marking (Europe); other safety approvals as required by individual countries

Electromagnetic emission standard

CISPR 22: 2005+A1/EN 55022: 2006+A1 Class A, EN 61000-3-2: 2006, EN 61000-3-3: 2008, EN 55024: 1998+A1+A2, FCC Title 47 CFR, Part 15 Class A (USA), ICES-003, Issue 4, (Canada), GB9254-2008, EMC Directive 2004/108/EC with CE Marking (Europe), other EMC approvals as required by individual countries

¹Measured using ISO/IEC 24734, excludes first set of test documents. For more information see <http://www.hp.com/go/printerclaims>. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ²Exact speed varies depending on the system configuration, software application, driver and document complexity for first page out. A firmware upgrade may be required to realize stated first copy out time (FCOT). ³Based on standard ITU-T test image #1 at standard resolution. More complicated pages or higher resolution will take longer and use more memory. ⁴Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups. ⁵HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement intervals and device life over an extended warranty period. ⁶Declared per ISO 9296 and 7779; values are subject to change. Configuration tested: HP LaserJet Enterprise M4555 MFP. ⁷Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. Values subject to change. Power numbers are the highest average values measured using all standard voltages.



ENERGY STAR® qualified models; see: <http://www.hp.com/go/energystar>

© Copyright 2011 Hewlett-Packard Development Company, L.P.

The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. Microsoft, Windows, and Windows XP are registered trademarks of Microsoft Corporation.

Windows Vista is either a registered trademark or trademark of Microsoft Corporation in the United States and/or other countries.

To learn more, visit <http://www.hp.com>

4AA3-3260ENUC, March 2011

