

Lexmark CX410 Series Multifunction Color Laser Printer

Stunning Color. Stellar Versatility.

The Lexmark CX410 Series MFP color laser desktop printer does more than deliver PANTONE® color matching and fast print, fax, copy and scan speeds—it offers optional solutions to help streamline your business. *Want to do 2-sided printing capabilities? Choose the CX410de. Need more capacity? Get the CX410dte.*



Color



Up to 32 ppm



4.3-in. Touch
Screen



Solutions

Unison™
TONER



Accurate Color That's Brand-Worthy.

The Lexmark CX410 Series MFP delivers rich, consistent color printing that can enhance your company's materials and brand. It's faster and more reliable than ever.

Freedom to Print on the Fly - Produce professional color in-house, on demand. With 512 MB of upgradable memory and a fast dual-core processor, you'll have speed as well as power and convenience.

Professional Color Matching - Lexmark Named Color Replacement and PANTONE® calibration make it easy to develop a consistent brand image by accurately matching your colors.

High Resolution Graphics - With up to true 1200x1200 dpi resolution, images and graphics stay crisp. Lexmark's Unison™ Toner ensures consistent quality, too.

Super Fast and Quiet Output - Quickly print, copy and scan up to 32 pages per minute in black and color, plus produce a 1 page color document in as little as 11.5 seconds.

More Productivity. Less Hassle.

Produce everything on the spot—from in-store signage to customer presentations. Features, like an easy-to-read user control panel, large output bin and more, make printing a breeze.

Reliable Performance - Easily print up to 6,000 pages a month, plus enjoy fewer maintenance hassles, thanks to state-of-the-art paper handling.

Run Larger Jobs without Interruption - With an input capacity of up to 1,450 sheets and high yield toner cartridge options, you won't have to add paper or change cartridges as often.

Easy-to-Read Color Touch Screen - Stay on top of your jobs with our convenient 4.3-inch color touch screen and front direct USB port.

Innovative Toner That Optimizes Performance - Get greater system performance with Lexmark's Unison™ Toner, which delivers consistent image quality from first print to last.

Productive Workflows. Sustainable Design.

Quickly respond to changing business needs with our eco-friendly printers that streamline your workflow.

Help Workers Do More - With standard Gigabit Ethernet networking, our system can print jobs from the network faster, so your team stays productive.


Enjoy Enterprise-level Security - Now you can authenticate, authorize and audit employee usage. Plus, protect sensitive data using standard network security protocols.

Save Resources and the Planet - An instant warm-up fuser, built-in 2-sided printing⁸ plus Quiet, Hibernate and Eco modes minimize noise and save paper and energy.

Print Anytime and Anywhere⁶ - With this system, you can print from desktops as well as mobile devices that can run applications.

LEXMARK
™

Lexmark CX410 Series Multifunction Color Laser Printer



| Product specifications | Lexmark CX410e | Lexmark CX410de | Lexmark CX410dte |
|--|--|--|---|
| Printing | | | |
| Function | Color Copying, Color Faxing, Color Printing, Color Scanning | | |
| Display | Lexmark e-Task 4.3-inch (10.9 cm) color touch screen | | |
| Print Speed: Up to ¹ | Black: 32 ppm / Color: 32 ppm | | |
| Time to First Page: As fast as | Black: 10.5 seconds / Color: 11.5 seconds | | |
| Print Resolution | Black: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi) / Color: 1200 x 1200 dpi, 4800 Color Quality (2400 x 600 dpi) | | |
| Memory / Processor | Standard: 512 MB / Maximum: 2560 MB / Processor: Dual Core, 800 MHz | | |
| Hard Disk | Not Available | | |
| Recommended Monthly Page Volume ² | 800 - 6000 pages | | |
| Maximum Monthly Duty Cycle: Up to ³ | 75000 pages per month | | |
| Copying | | | |
| Copy Speed: Up to ⁴ | Black: 32 cpm / Color: 32 cpm | | |
| Time to First Copy: As fast as | Black: 10.8 seconds / Color: 11.6 seconds | | |
| Color Scanning | | | |
| Scanner Type / ADF Scan | Flatbed scanner with ADF / RADF (Reversing Duplex) / 50 pages 20 lb or 75 gsm bond | | |
| Duplex Scan Speed: Up to | A4/Ltr, Black: 13 / 14 sides per minute - A4/Ltr, Color: 13 / 14 sides per minute | | |
| Simplex Scan Speed: Up to | A4/Ltr, Black: 30 / 32 sides per minute - A4/Ltr, Color: 30 / 32 sides per minute | | |
| Optical Scanning Resolution | 600 X 600 ppi (color), 1200 X 600 ppi (black) | | |
| Faxing | | | |
| Modem Speed | ITU T.30, V.34 Half-Duplex, 33.6 Kbps | | |
| Supplies⁵ | | | |
| Laser Cartridge Yields | 1,000 ¹ -page Black and Color (CMYK) Cartridges, 2,000 ¹ -page Color (CMY) Cartridges, 2,500 ¹ -page Black Cartridge, 3,000 ¹ -page Color (CMY) High Yield Cartridges, 4,000 ¹ -page Black High Yield Cartridge | | |
| Cartridge(s) Shipping with Product | 1,400 ¹ -page Black and Color (CMYK) Starter Return Program Toner Cartridges | | |
| Paper Handling | | | |
| Included Paper Handling | 250-Sheet Input, 150-Sheet Output Bin, Single-Sheet Manual Feed | 250-Sheet Input, 150-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed | 250-Sheet Input, 550-Sheet Duo Tray with 100-Sheet Feeder, 150-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed |
| Optional Paper Handling | 550-Sheet Tray, 550-Sheet Duo Tray with 100-Sheet Feeder | 550-Sheet Tray, 550-Sheet Duo Tray with 100-Sheet Feeder | 550-Sheet Tray |
| Paper Input Capacity: Up to | Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 1450+1 pages 20 lb or 75 gsm bond | Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 1450+1 pages 20 lb or 75 gsm bond | Standard: 900+1 pages 20 lb or 75 gsm bond / Maximum: 1450+1 pages 20 lb or 75 gsm bond |
| Paper Output Capacity: Up to | Standard: 150 pages 20 lb or 75 gsm bond / Maximum: 150 pages 20 lb or 75 gsm bond | | |
| Media Types Supported | Card Stock, Paper Labels, Plain Paper, Transparencies, Refer to the Card Stock & Label Guide | Card Stock, Paper Labels, Plain Paper, Transparencies, Refer to the Card Stock & Label Guide | Card Stock, Envelopes, Paper Labels, Plain Paper, Transparencies, Refer to the Card Stock & Label Guide |
| Media Sizes Supported | A4, A5, Executive, Folio, JIS-B5, Legal, Letter, Universal, Oficio | A4, A5, Executive, Folio, JIS-B5, Legal, Letter, Universal, Oficio | 10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, Executive, Folio, JIS-B5, Legal, Letter, Statement, Universal, Oficio, A6 |
| General⁷ | | | |
| Standard Ports | USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified Port (Type A) | | |
| Optional Network Ports / Optional Local Ports | MarkNet N8352 802.11b/g/n Wireless | | |
| Noise Level, Operating | Printing: 49 dBA / Copy: 50 dBA / Scan: 50 dBA | | |
| Product Warranty | 1-Year Onsite Service, Next Business Day | | |
| Size (in. - H x W x D) / Weight (lb.) | 18.44 x 17.48 x 21.99 in. / 60.25 lb. | 18.44 x 17.48 x 21.99 in. / 60.25 lb. | 23.63 x 17.48 x 21.99 in. / 69.55 lb. |

¹ Average continuous black or continuous composite CMY declared cartridge yield up to this number of standard pages in accordance with ISO/IEC 19798. ² "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³ "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴ Print and copy speeds measured in accordance with ISO/IEC 24734, excludes first set of test documents. For more information see: www.lexmark.com/ISOspeeds. ⁵ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁶ For more information on Lexmark Mobile Solutions see: http://www1.lexmark.com/en_US/solutions/business-solutions/mobile-print/index.shtml ⁷ Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details. ⁸ Duplex (2-sided printing) models are ENERGY STAR compliant.

