

TOSHIBA

e-STUDIO™ 330AC/400AC

Experience everything about a larger MFP through a device that fits right on your desk or rolls up next to it. This color printer is a real team player, offering everything smaller workgroups need to move at the speed of today's business.

- Color A4 Multifunction Printer
- Up to 42 PPM
- Small/Medium Workgroups
- Copy, Print, Scan, Fax
- Advanced Features



Main Specifications

Copy System	Indirect Electrostatic Photographic Method/OPC/LED Printing/Heat Roller Fusing
Display	10.1" Color WSVGA Touch Screen Tilting Display
Copy Speed	35/42 PPM (LT)
First Copy Out	Color: 7.2/6.3 Seconds Monochrome: 5.7/5.1 Seconds
Warm-Up Time	Approx. 20 Seconds
Copy Resolution	600 × 600 dpi
Stack Feed Bypass	3.9" x 5.8" to 8.5" x 14" (LG), Envelope
Multiple Copying	Up to 999 Copies
Paper Capacity	Standard: 650 Sheets/Max. 3,200 Sheets
Original Feed	Standard 100-Sheet DSDF
Scan Speed & Weights	DSDF Scan: Up to 120 IPM Duplex, 60 IPM Simplex (Monochrome) Up to 82 IPM Duplex, 41 IPM Simplex (Color), 9.3-28lb Bond LG
Max. Original Size	Drawer 1: 550 Sheets-ST-R to LG
Paper Feed Sizes	Stack Feed Bypass: 100 Sheets-3.9" x 5.8" to 8.5" x 14" (LG), 12 x 47" Banner Opt. 550-Sheet Paper Feed Unit (up to 3)-ST-R to 8.5" x 14" (LG) Opt. 2,000-Sheet LCF (Pedestal Type)-LT Only Standard: 550 Sheets x 1-16 lb Bond-140 lb Index Stack Feed Bypass: 100 Sheets-14 lb Bond-140 lb Index Opt. 550-Sheet Paper Feed Unit-16 lb Bond-140 lb Index Opt. 2,000-Sheet LCF (Pedestal Type)-16 lb Bond-140 lb Index Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)
Paper Weights	
Duplex	Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)
Reproduction Ratio	25% to 400%
Max Duty Cycle	Max. 150K Month
Weight	Approx. 117 lb
Approx. Dimensions	20.5" (W) x 21.3" (D) x 25" (H)
CMYK Toner Yield	CMY: 17.4K, BK: 18.4K @ 5%
Power Source	120 Volts, 50/60 Hz, 12 Amps
Power Consumption	Maximum 1.5 kW (120 V)
CPU	Intel ApolloLake™ E3930 (Dual-Core)
Memory	4GB
Hard Disk Drive	320GB Self-Encrypting Drive

e-BRIDGE Next Print Specifications

PDL	PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG
Print Speed	35/42 Pages Per Minute (LT)
Print Resolution	600 × 600 dpi (5bit), 1,200 × 1,200 dpi (Color/2bit) or 3,600 (Equivalence) × 1,200 dpi (BW/with Smoothing) (PS3Only)
Operating Systems	Windows Server® 2008 R2, R2 SP1, 2008/SP2, Windows® 8.1, 10, Windows Server® 2012/R2, Windows Server® 2016, Macintosh® (macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13), Unix®, Linux® TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell®
Network Protocols	Environments, EtherTalk for Macintosh Environments
Printing Protocols	SMB, LPR/LPD, IPP (Ver. 2.0) w/Authentication, AppleTalk® PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/ iPrint, WS Print, FTP
Print Drivers	Windows Server® 2008 SP2 (32-bit, 64-bit) Windows Server® 2008 R2 SP1 (64-bit), SP1 (32-bit, 64-bit), Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows Server® 2016, Windows® 10 (32-bit, 64-bit), macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, 10.12, 10.13 RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed)
Interface	Optional IEEE802.11b/g/n, Wireless LAN, Optional Bluetooth
Wireless Device	AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play)
Account Control	Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows® Domain) or Login Name/Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function
Accessibility Features	Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Timeout and Audible Beep Message Alerts

*Requires FIPS 140-2 HDD



Security Features

User Authentication, SCEP, Disable e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS, SYSLOG), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408)* with HCD-PP v1.0*, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, NFC Authentication
*Conformance with HCD-PPv1.0 in High Security Mode.
ENERGY STAR® (V3.0), EPEAT Gold, Californian Proposition 65 WHQL (Windows® 8.1, 10, 2008 R2, 2012, 2012 R2), Novell®, Citrix®, SAP, AirPrint® and Mopria®

Environmental Stds. Certification

Scan Specifications

Scan Speed	DSDF Scan: Up to 120 IPM Duplex, 60 IPM Simplex (Monochrome) Up to 82 IPM Duplex, 41 IPM Simplex (Color)
Scan Modes	Standard: Full Color, Auto Color, Monochrome, Grayscale
Scan Resolution	600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi
File Formats	Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, Slim PDF
Image Compression	Color/Grayscale: JPEG (High, Middle, Low)

Facsimile Specifications

Compatibility	SuperG3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	Up to 33.6Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400Destinations/Job
Scan Speed	0.7 Seconds Per Page, Up to 120 IPM Duplex, 60 IPM Simplex (Monochrome or Color)

e-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder/Box, 200 Pages Per Document

Accessories (Options)

Paper Feed & Finishing Options	Software Options	
Paper Feed Unit	IPsec	GP1080NODE
2,000 Sheet LCF	Hardcopy Security	GP1190NODE
Spacer	Unicode Font	GS1007NODE
Caster	Metascan	GS1010NODE
Offline Stapler	Embedded OCR 1 License	GS1080NODE
Connectivity Options	Multi-Station Print 1 License	GS1090NODE
FAX Unit	Fax Over IP	GS1100NODE
FIPS 140-2 HDD	e-BRIDGE Replicator Ex	GB1550NODE
Wireless LAN Bluetooth Option	e-BRIDGE Job Point Ex	GB1560NODE
Miscellaneous Options	e-BRIDGE Job Separator Ex	GB1590NODE
Panel 10 Key Option 10.1"	e-BRIDGE Plus	
Card Reader Holder	for Exchange Online V3.0	GB2320NODE
Harness for Coin Controller	e-BRIDGE Job Build Ex	GB1610NODE
Stand	e-BRIDGE Plus for Onedrive	
Power Filter, 120V/15A,	for Business V3.0	GB2300NODE
Compact, 1 Receptacle	e-BRIDGE Plus	
	for Sharepoint Online V3.0	GB2310NODE
	e-BRIDGE Plus for Gmail	GB2380NODE
	e-BRIDGE Plus for Google Drive	GB2390NODE
	e-BRIDGE Plus for Docuware	GB2430NODE

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office	25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000
Website	business.toshiba.com