

# TOSHIBA

## e-STUDIO™ 479s

- Black & White A4 MFP
- 50 PPM Letter-Size
- Wi-Fi Enabled
- Solutions Ready
- Advanced Security
- Copy, Print, Scan, Fax



### Packs a lot of punch.

Toshiba's new e-STUDIO479S multifunction printer (MFP) is a powerful and versatile A4 monochrome device that delivers 50 letter-size pages per minute (PPM). It features copy, print, scan and fax capabilities right out of the box, and its large 7" touchscreen front panel makes programming complex jobs easy.

### Designed to handle volume.

This MFP is designed to handle volume, with a rated monthly page yield of up to 175K pages. Its integral 550-sheet cassette and 100-sheet multipurpose tray hold a variety of media, including letter or legal-size paper, specialty media, labels and letterhead. Need more paper? You can add up to three additional cassettes (with lockable drawer options) for a total capacity of 2,300 sheets. And with a high-yield toner cartridge (31K pages at 5%), you won't have to worry about running out of supplies for a while.

### Scans with the best of them.

The built-in 100-sheet Dual Scan Document Feeder (DSDf) scans monochrome originals at up to 104 duplex pages per minute (IPM) and color pages at up to 84 IPM. The large, legal-size platen lets you scan odd-sized originals and delicate documents.

### Keeps up the pace.

The e-STUDIO479S is also solutions ready, with a variety of internally developed applications available, such as the optional Optical Character Recognition (OCR), or other popular third-party offerings. Its 1.2GHz quad-core processor, 2GB of built-in RAM and standard 128GB Solid State Drive (SSD) ensure that it can keep pace with the busiest office environments.

### The latest security safeguards.

Your document and data security is our top priority. We've implemented the latest safeguards, including Trusted Platform Module 2.0 (TPM 2.0) with dedicated hardware encryption and encryption security for the built-in 802.11ac Wi-Fi. As a result, the e-STUDIO479S is FIPS140-2 validated and Common Criteria certified.

### Brings a lot to the table.

The feature-rich e-STUDIO479S is perfect for busy offices with limited space. Its compact design allows it to fit easily on a desk or tabletop, or you can choose one of the convenient stand options. Once you put this MFP to work, you'll see that it brings a lot to the table.

## Main Specifications

<b>Copy System</b>	Indirect Electrostatic Photographic Method/OPC/ Laser Printing/Heat Roller Fusing
<b>Display</b>	7" Color TFT Touch Screen Tilting Display
<b>Copy Speed</b>	50 PPM (LT)
<b>First Copy Out</b>	As Fast as 6 Seconds
<b>Warm-Up Time</b>	Approx. 65 Seconds
<b>Copy Resolution</b>	Up to 600 × 600 dpi
<b>Multipurpose Tray</b>	3.0" x 5.0" to LG, Envelope
<b>Multiple Copying</b>	Up to 9,999 Copies
<b>Paper Capacity</b>	Standard 650 Sheets/Max. 2,300 Sheets
<b>Original Feed</b>	Standard 100-Sheet DADF
<b>Scan Speed &amp; Weights</b>	DADF Scan: Mono - Up to 104 IPM Duplex, 52 IPM Simplex Color - Up to 84 IPM Duplex, 42 IPM Simplex
<b>Max. Original Size</b>	LG
<b>Paper Feed Sizes</b>	Drawer 1: 550 Sheets - 4.13" x 5.83" to LG Multipurpose Tray: 100 Sheets - 3.0" x 5.0" to LG Opt. Drawers: 550 Sheets - 4.13" x 5.83" to LG
<b>Paper Weights</b>	14 - 32 lb Bond, Drawers: 16 - 32 lb Bond, Multipurpose Tray: 16 - 58 lb Bond Standard Automatic Duplex Unit: 16 - 24 lb Bond Standard Automatic Duplex Unit: 16 - 24 lb Bond
<b>Duplex</b>	Standard Automatic Duplex Unit: 16 - 24 lb Bond
<b>Reproduction Ratio</b>	25% to 400%
<b>Max Duty Cycle</b>	Max. 175K Month
<b>Weight</b>	Approx. 47 lb.
<b>Approx. Dimensions</b>	20.2" (H) x 18.9" (W) x 17.8" (D)
<b>Toner Yield</b>	31K @5%
<b>Power Source</b>	120 Volts, 50/60 Hz, 15 Amps
<b>Power Consumption</b>	Maximum 1.5kW (120V)
<b>CPU</b>	1.2GHz (Quad-Core)
<b>Memory, Std./Max.</b>	2GB / 2GB
<b>Hard Disk Drive</b>	128GB SSD

## Print Specifications

<b>PDL</b>	PostScript 3, PCL 6, PCL 5, PCLm, PPDS, PDF v1.7, Direct Image
<b>Print Speed</b>	50 Pages Per Minute (LT)
<b>Print Resolution</b>	1200 × 1200 dpi, 2400 Image Quality, 1200 Image Quality, 600 × 600 dpi, 300 × 300 dpi
<b>Standard Ports</b>	Rear USB 2.0 Specification High Speed Certified Port (Type A), Front USB 2.0 Specification High Speed Certified Port (Type A), Gigabit Ethernet (10/100/1000), USB 2.0 Specification High Speed Certified Port (Type B), 802.11b/g/n/ac + BLE
<b>Optional Network Ports</b>	Wi-Fi 802.11 b/g/n/ac, Wi-Fi Direct
<b>Device Management</b>	Embedded Web Server
<b>Accessibility Features</b>	Tilt Front Panel, 508 Accessibility Support, Voice Guidance
<b>Security Features</b>	TPM (2.0), 802.1x, Audit Logging, Digitally Signed Firmware Updates, Certificate Management, HTTPS, SNMPv3, Secure Password Reset, TCP Connection Filtering, Port Filtering, Access Controls, Operator Panel Lock, Confidential Print, Non- Volatile Memory Wipe, Physical Lock Support, IPSEC, Secure NTP, Protected USB Ports, Login Restrictions, Microsoft Active Directory Domain Enrollment, Incoming Fax Holding, SSD or HDD Encryption, Automatic Hard Disk Wiping, End of Life Disk Wiping, FIPS140-2 & Common Criteria Certifications
<b>Environmental Features</b>	Sleep & Hibernate Modes, Eco Mode, Quiet Mode, Blue Angel/ RAL-UZ-122 Certification, RoHS Compliant, ENERGY STAR® Certified, EPEAT Silver, Mercury Free, Support for Recycled Paper, TEC: 0.64 kilowatt-hours per week
<b>Certifications</b>	Windows Vista™, 7, 8, 8.1, Server 2008/2008 R2, 2012/2012 R2,10, 11, Server 2022 USB, AirPrint®, Mopria®, Novell, Citrix®, SAP

## Scan Specifications

<b>Scan Speed</b>	DADF Scan: Mono - Up to 104 IPM Duplex, 52 IPM Simplex Color - Up to 84 IPM Duplex, 42 IPM Simplex
<b>Scan Destinations</b>	USB Thumb Drive, E-Mail, FTP, Network or USB Connected Computer, Windows Network Folder
<b>Scan Resolution</b>	600 dpi (Max)
<b>File Formats</b>	TIFF, JPG (JPEG), PDF (Regular, Secure, Archival (PDF/A), Searchable (If Optional OCR Installed), TXT, RTF, DOCX
<b>Image Compression</b>	PDF 1 bit: CCITT G4, ZLIB (Flate), 8/24 bit: ZLIB (Flate), JPEG, MRC (Mixed Raster Content), TIFF 1 bit: CCITT G4, 8/24 bit - Packbits, LZW, JPEG, JPG 8/24 bit: JPEG, XPS 1 bit: ZLIB (Flate), 8/24 bit - JPEG, ZLIB (Flate)

## Facsimile Specifications

<b>Compatibility</b>	Super G3
<b>Transmission Speed</b>	Approx. 3 Seconds Per Page
<b>Fax Modem Speed</b>	Up to 33.6 Kbps
<b>Fax Shortcuts</b>	1,000 - Based on an Average Shortcut 128 Characters for Name, 10 Characters for Number and 5 Characters for Shortcut ID. Maximum Characters - 512 and Each Location Separated by a Semicolon. 46 Locations Using a 10-Digit Phone Number, 64 Locations Using a 7-Digit Phone Number
<b>Broadcast Fax</b>	400 Locations - Each number in a fax shortcut is a location.

## Accessories (Options)

<b>250-Sheet Tray</b>	KD1076
<b>550-Sheet Tray</b>	KD1077
<b>550-Sheet Lockable Tray</b>	38S3130
<b>Convenience Stapler</b>	MJ1049US
<b>Contact Authentication Device</b>	GB2140LXX
<b>Contactless Authentication Device</b>	GB2150LXX
<b>Contactless Front Solutions Module (Primary)</b>	KP2020
<b>English Keyboard Kit</b>	GR1350
<b>IPDS Print License</b>	82S1203
<b>Barcode Print License</b>	GF1270
<b>N8230 Fiber Ethernet Print Server</b>	GB2120LXX
<b>Parallel 1284-b Interface Card</b>	27X0901
<b>Rs-232c Serial Interface Card</b>	GB2110LXX
<b>500+ GB Hard Disk</b>	GE1250
<b>Stand e-STUDIO479S 14"</b>	STAND479SSHORT
<b>Stand e-STUDIO479S 20"</b>	STAND479STALL
<b>Power Filter</b>	W1500-15-120
<b>Fax Over IP</b>	82S0945
<b>Fax Over IP M&amp;S</b>	82S1197
<b>OCR</b>	82S0984
<b>OCR M&amp;S</b>	82S0990

## Supplies

<b>Toner*</b>	T449UR
---------------	--------

\*Ships with 3K Yield Starter Toner Cartridge

This product includes software developed by the OpenSSL Project for  
use in the Open SSL Toolkit (<http://www.openssl.org/>).



Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

## Corporate Office

25530 Commercentre Drive, Lake Forest, CA 92630  
Tel: 949-462-6000

## East Coast

959 Route 46 East, 5th Floor, Parsippany, NJ 07054  
Tel: 973-316-2700

## Midwest

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631  
Tel: 773-380-6000

## South

2037 Bakers Mill Rd., Dacula, GA 30019  
Tel: 678-546-9385

## West Coast

25530 Commercentre Drive, Lake Forest, CA 92630  
Tel: 949-462-6000

## Website

business.toshiba.com