

TOSHIBA

e-STUDIO™ 2822AM/2822AF

- Black & White Multifunction Printer
- Up to 28 PPM
- Small Workgroup
- Copy, Print, Scan, Fax*
- Mobile Enabled



Improve your efficiency and productivity.

This robust, compact e-STUDIO2822AM/2822AF from Toshiba allows smaller businesses to think even bigger.

Performance in numbers.

Copy, print and scan up to ledger-sized output, and add faxing with the AF model. Both models offer high-end functions like an impressive first copy out time of 6.5 seconds and crisp 2,400 × 600 dpi output delivered at 28 pages per minute.

Save time, paper and costs.

For money-savings with two-sided copying and printing, there's a Reversing Automatic Document Feeder (RADF) and Automatic Duplex Unit (ADU).

Seamless connectivity.

An Ethernet network interface and optional wireless connectivity ensure seamless integration. Mobile users can share the device, thanks to Toshiba's unique e-BRIDGE Print & Capture application.

*Fax available with AF model only

Specifications

Copying/Printing Process Type	Indirect Electrostatic Photographic Method Desktop
Original Scanning Method	Contact Image Sensor (CIS)
Resolution	2400 × 600 dpi (with Smoothing)
Gradation	256 Steps
Original Platen Type	Fixed Hard Platen, 50-Sheet RADF (14-28 lb)
Available Original Size	ST-R to LD
Available Paper Size	Drawer: LT Only Stack Feed Bypass: ST-R, LT, LD, Envelope
Paper Supply	Standard: Drawer (250 Sheets x 1) Stack Feed Bypass (50 Sheets)
Available Paper Weight	Drawer: 17-20 lb Stack Feed Bypass: 14-120 lb Index Auto Duplexing Unit: 17-20 lb
Paper Exit	Face Down/Inner Tray
Warm-up Time	Approx. 18 Seconds (Scanner Function Available During Warm-Up)
Counter	Electronic Counter (Indication by LCD Display)
Memory	512 MB
Department Codes	100
Power Supply	115 Volts, 12 Amps
Power Consumption	Maximum: 1.5kW
TEC Value	1.4kWh/week
Dimensions	Approx. 15.3" x 21.25" x 20" (W x D x H)
Weight	Approx. 58.3/62.7 lb
Special Features	Energy Saver, Auto Sleep Mode, Department Code
Max Duty Cycle	64K Copies
Certifications	Energy Star V3.0, EPEAT (GOLD) & WEE (Argentina Model) + RoHS Compliant
Worldwide Safety Stds.	UL, GS, CE, CDRH, SASO, IRAM, EAC, CCC
Black Toner Yield	17.5K Impressions @ 5%

Copy Specifications

Copying Speed	28 PPM
Original Scan Speed	25 SPM (by Using RADF)
Scan Resolution	600 × 600 dpi (for Copying)
First Copy Time	Less Than 6.5 Seconds
Original/Copy Size	ST-R to LD
Original Mode	Photo, Text/Photo, Text, Background Erase
Image Density Control	Automatic/Manual (11 Steps)
Reproduction Ratio	Zoom: 25% to 400% in 1% Increments
Multiple Copying	Up to 999 Copies (Ten Key Input)
Special Features	Department Codes (100) Interrupt, APS/AMS, Auto Job Start, Automatic Sort Mode, ID Card Copy, One Touch Keys (2)

Print Specifications

Printing Speed	28 PPM
Printing Resolution	2400 × 600 dpi (with Smoothing)
Interface	Standard: 10/100 Base-T, USB 2.0 Optional: 802.11 b/g/n
PDL	PCL 6 Emulation
USB Direct Printing	JPEG, TIFF, PDF (Only PDF created by MFP can be direct printed)
Support OS	Windows 7, 8, 8.1, 10, 2008R2, 2012, 2012 R2, (WHQL), CUPS PCL Unix, Linux 5.10.x, 6.5.x

Scan Specifications

Connection Type	Standard: 10/100 Base-T Optional: 802.11 b/g/n
Scanning Resolution	100/150/200/300/400/600 dpi
Scanning Speed	25 SPM (BW) at 600 dpi, 22 SPM (Color) @ 200 dpi, 13 SPM @ 300 dpi
Scan Agent	Scan to File, SMB, FTP, Scan to Email, Scan to USB, TWAIN IOS & Android Support Via e-BRIDGE Print & Capture App

Paper Handling

Reversing Automatic Document Feeder (RADF)

Stack Capacity	50 Sheets
Original Setting	Face Up
Original Paper Size	ST-R to LD
Original Paper Weight	14-28 lb

FAX Specifications (e-STUDIO2822AF Only)

Compatibility	Super G3, G3
Image Format on PSTN	JBIG, MMR, MR, MH
Document Size	ST-R-LD
Modem Speed	33.6 kbps to 2.4 kbps (Automatic fallback)
Transmission Speed	Approx. 3 Seconds
Communication Protocols	ITU-T T.30
Memory Transmission	Max 256 Jobs, 220 Destinations/Job, 384 Pages/File

Options

Cabinet	STAND2505
Wireless LAN Module	GN1160
Damp Heater (for Drum)	MF2505U
Harness for Coin Controller	GQ1131



*Fax available with AF model only

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office

East Coast	25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000
Website	business.toshiba.com