

- > 20/25 PPM
- > Black & White MFP
- > Small Workgroup
- > Copy, Print, Scan, Fax
- > Network Ready





- > Black and White MFP
- > 20/25 PPM
- > Small Workgroup
- > Copy, Print, Scan, Fax
- > Network Ready

**General Specifications**

Copy/Print Process Type	Indirect Electrostatic Photographic Method Desktop
Original Scanning Method Resolution	Contact Image Sensor (CIS) Scanning: 600 x 600 dpi Printing: 2400 x 600 dpi (with smoothing)
Gradation	256 Steps
Original Platen Type	Fixed Hard Platen (optional RADF)
Available Original Size	Maximum Ledger
Available Paper Size	Drawer: Statement-R to Ledger Bypass: Statement-R to Ledger
Paper Supply	Standard Drawer (250 sheets), Bypass (100 sheets) Optional: Paper Feed Unit (250 sheets), Paper Feed Pedestal (550 sheets), Drawer Module for PFP (550 sheets)
Available Paper Weight	Drawer: 17 lb - 21 lb Bond Bypass: 14 lb Bond - 90 lb Index (Single-feed), 17 lb - 21 lb Bond (Multi-feed) Auto Duplexing Unit: 17 lb - 21 lb Bond
Paper Exit	Face Down, Inner Tray
Memory	512 MB
Warm-up Time	Approx. 20 Seconds
Counter	Electronic Counter
Power Supply	110 Volts
Power Consumption	1.5kW
Reduction/Enlargement	25% to 400%
Dimensions	Standard: Approx. 22.6" x 21.2" x 16" (W x D x H) With PFU: Approx. 23" x 22.2 x 20" (W x D x H)
Weight	Approx. 56.2 lbs.
Special Features	Auto Sleep Mode, Auto Energy Saver, Department Codes
Toner Yield	10K Impressions @ 6%
Max Duty Cycle	65K/80K Copies

**Copy Specifications**

Copy Speed	20/25 PPM (LT), 16/16 PPM (LG), 14/14 PPM (LD)
Original Scan Speed	25/25 SPM (LT)
First Copy Time	7.1 Seconds
Original/Copy Size	ST-R to LD
Original Mode	Text/Photo, Photo, Text, Background Mode
Image Density Control	Automatic/Manual (9 steps)
Reproduction Ratio	Zoom: 25% to 400% in 1% increments
Multiple Copying	Up to 999 Copies (ten key input)
Special Features	APS/AMS*, Auto Job Start, Auto Drawer Change*, Automatic Electronic Sort Mode, Thick Paper Mode, ID Card Copy *Options are required.

**Print Specifications**

Maximum Print Speed	20/25 PPM (LT), 16/16 PPM (LG), 14/14 PPM (LD)
Printing Resolution	600 x 600 dpi, 2400 x 600 dpi (with smoothing)
Interface	10Base-T/100Base-TX, USB2.0 (High-speed)
Printer Language	PCL6 (compatible)
Support OS	Windows XP/Vista/7/8/Server 2003/2008/2008R2/2012
Network Protocols	TCP/IP (IPv4/IPv6), NetBIOS over TCP/IP
IP Addressing	Auto IP, Static IP, DHCP, DNS, Dynamic DNS LLMNR (under IPv6 environment)
Printing Protocols	SMB, LPR/LPD, IPP ver1.0, Port9100 (bi-directional), FTP
Special Features	N-up Printing, Watermark, Toner Save, Halftone Type, Omit Blank Page

**Scan Specifications**

<b>Network Scanner</b>	
Connection Type	Network (Ethernet)
Scanning Resolution	600, 300, 150 dpi
Scanning Speed	25 SPM (BW), up to 8 SPM (color)
File Format	PDF, TIFF, JPEG
Compatibility	TWAIN
Scan Agent	Scan to File, SMB/FTP, Scan to Email, Scan to USB, Remote TWAIN
Original Mode	Photo, Text/Photo, Text
Protocol	Scan to file: SMB, FTP Scan to Email: SMTP, MIME (Base64)
<b>Local Scanner</b>	
Connection Type	USB 2.0 (high speed)
Scanning Resolution	600, 300, 150 dpi
Compatibility	TWAIN

**Paper Handling Options**

Automatic Document Feeder (RADF)	MR3027
Paper Feed Unit (PFU)	MY1043
Automatic Duplexing Unit (ADU)	MD0106
Paper Feed Pedestal (PFP)	KD1039
Drawer Module	MY1044

**Other Options**

Fax Kit	GD1330
Wireless LAN Adaptor	GN1080
Harness Kit for Coin Controller	GQ1131
Cabinet Stand	STAND2507
Platen Cover	KA2507



<b>Corporate Office</b>	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.