

TOSHIBA
Leading Innovation >>>

- > Black & White MFP
- > Up to 55 PPM
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP



e-STUDIO™ 477sL/527s





- > Black & White MFP
- > Up to 55 PPM
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP

Specifications

| | |
|----------------------------------|---|
| Copying Process | Indirect Electrostatic Photographic Transfer System with Internal Transfer Belt |
| Copying Type | LED Head Printing |
| Copy/Print Resolution | 600 x 600 dpi (1200 x 1200 dpi - PS3 only) |
| Copy/Print Speed | 49/55 PPM B&W |
| Warm-Up Time | Approx. 60 Seconds |
| First Copy Out Time | 8 Seconds |
| Multiple Copying | Up to 999 Copies |
| Acceptable Paper Size and Weight | Cassette: ST-R to LG (17lb Bond - 120lb Index) Bypass: 3" x 5" to LG, Banner 8.5" x 52" (17lb Bond - 138lb Index) |
| Memory (Max) | Main Memory: 2GB HD: 320GB FIPS 140-2 Validated SED |
| Document Feeder | 100-Sheet |
| Reduction/Enlargement | 25% to 400% |
| Bypass | 100-Sheet "Smart" Bypass (17lb Bond - 138lb Index) |
| Control Panel | Color 9" LCD Touch Panel |
| Paper Supply | Up to 3,160-Sheet Input Capacity Standard 1 x 530-Sheet Cassettes 100-Sheet Bypass Optional 3 x 530-Sheet Cassette Optional 2,000-Sheet LCF |
| Duplex | Std. Automatic Duplex Unit (17lb Bond - 120lb Index) |
| Dimensions | 477sL: Approx. 20.55" x 22.2" x 26.5" (W x D x H) 527s: Approx. 20.55" x 22.2" x 32" (W x D x H) |
| Weight | Approx. 115lb |
| Toner Yield | 36K |
| Power Supply | 120 V, 15 Amps |
| Power Consumption | Maximum 1.5 kW |
| Max Duty Cycle | 200K/225K Copies |

e-BRIDGE Print Specifications

| | |
|-------------------|--|
| PDL Support | PCL6, PostScript 3, XPS |
| Operating Systems | Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO |
| Protocol Support | Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP |
| Drivers | Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9 |
| Connectivity | 10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB |
| Wireless Device | AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play) |
| Device Management | Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software) |
| Certification | Windows 7, 8, 8.1, 2008R2, 2012, 2012 R2, WHQL, Novell, Citrix |

Scan Specifications

| | |
|-----------------|--|
| Scan Resolution | 100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi |
| Scan Speed | 55 SPM B&W, 40 SPM Color (@ 300 dpi) |
| File Format | TIFF, PDF, Secure PDF, JPEG, XPS (with HDD) |

Facsimile Specifications

| | |
|--------------------|-------------------------------------|
| Compatibility | Super G3 |
| Data Compression | MH/MR/MMR/JBIG |
| Transmission Speed | Approx. 3 Seconds Per Page |
| Fax Modem Speed | 33.6 Kbps |
| Scan Speed | .7 Seconds Per Page, Maximum 42 SPM |

E-Filing Specifications

| | |
|-------------------|---|
| Operation Method | Color Touch Screen Control Panel or Client PC |
| Number of Boxes | 1 Public Box, 200 Private User Boxes |
| Capacity of Boxes | 100 Folders Per Box, 400 Documents Per Folder, 200 Pages Per Document |

Security

| | |
|-----------------|--|
| Data Encryption | 256 Bit AES (SED Hard Drive) |
| Disk Overwrite | 1-5 Time Overwrite (meets DOD standard) |
| Authentication | LDAP, SMTP, Windows Server Domain, Local |

Accessories (Options)

Additional Paper Options, Spacers, Caster Base

| | |
|--|----------------------|
| Spacer: (For Adjusting Machine Height Replacing a Stand) | GR1160 |
| Caster Base: (Caster Base for PFU, LCF or Spacer) | GR1170 |
| Cassettes: 530-Sheet Pedestal, ST-R to LG | MY1046 |
| Large Capacity Feeder (LCF): 2,000-Sheet Drawer, LT, Stand (Use in place of LCF) | KD1040 STAND407CS |

Finishing Options

| | |
|---|--------|
| Inner Finisher (For e-STUDIO527s Only): 1 Tray: 500 Sheets | MJ1038 |
| Damper Kits | KK1003 |
| Offline Stapler | MJ1039 |

Connectivity/Security Options

| | |
|---------------------------------|----------|
| Fax Board | GD1340 |
| Meta Scan Enabler for e-CONNECT | GS1010 |
| IPsec Enabler | GP1080 |
| Advanced Scanning (Re-Rite) | GB1280V8 |
| SharePoint Connector | GB1440 |
| Exchange Connector | GB1450 |
| Google Docs Connector | GB1540 |



| | |
|-------------------------|---|
| Corporate Office | 9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000 |
| East Coast | 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700 |
| Midwest | 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000 |
| South | 2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385 |
| West Coast | 9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000 |
| Web Site | www.business.toshiba.com |

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support vary by client/network operating system.