TOSHIBA

Leading Innovation >>>

- > Black & White MFP
- > Up to 50 PPM
- > Small/Med. Workgroup
- ➤ Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered



Exceed expectations in powerful ways.

The e-STUDIO507 series from Toshiba has been designed to bring small and medium workgroups the same power and performance typically reserved for larger businesses. It's easy to use, allowing you to create professional looking documents without extensive training or experience.

Expand your possibilities.

Toshiba has taken the performance and functionality of larger monochrome MFPs and designed a smaller, more compact version. Introducing the e-STUDIO507 series. In addition to copying, faxing, printing and color scanning, it handles even the most challenging jobs quickly and easily. You'll be impressed with handy features like a walk-up USB printing port and a crisp 9" color touch screen that gives you instant access to all sorts of other possibilities.

Less work and more flow.

Start with a 20-second warm-up and a first copy out time of 3.7 seconds. Output is produced at the speed that fits your needs – from 35 to 50 pages per minute. Image quality is outstanding at 2,400 x 600 dpi. Need a lot of copies? You can opt for up to a 3,200-sheet capacity. And, its modular design allows you to get the most paper in the sizes you need, with a tandem LCF or 4-drawer configuration.







Get more done in less time with advantages like USB printing and paper that can be added midstream.



It's the business of helping businesses.

At Toshiba, we realize the challenges that businesses face every day. The new e-STUDIO507 series is the perfect solution for small to medium size businesses looking for a high quality, fully functional MFP to help them meet those challenges.

Relax and let technology handle it.

Because the e-STUDIO507 series has incorporated the latest e-BRIDGE technology, business applications and vendor solutions are easily integrated. With 320GB of safe and secure storage, frequently used documents can be stored right on the MFP by using

the convenient e-Filing feature and then printed as needed. Settings such as finishing selections can be saved with a job or changed on the fly to ensure accurate reproduction every time.

User friendly and eager to please.

The e-STUDIO507 series can handle jobs with ease, even large volumes of various types of documents.

Take advantage of up to a 150,000 monthly copy volume and a 36,600 toner yield at 6%. Also, there are several finisher options including a space saving 50-Sheet Inner

Finisher or a High-Capacity
Finisher with Saddle-Stitch,
plus 2/3-Hole Punch.
You'll be impressed
from start to finish.

- > Superb Image Quality
- > e-BRIDGE Technology
- > Universal Print Driver
- > Fast First Copy Out Times
- > Up to 3,200 Capacity
- > Service Module Design
- > Saddle Stitch Finisher
- > 2/3 Hole Punch



Protection for your business and the planet.

As the need for tougher data security and improved environmental protection continue to increase, Toshiba is prepared to answer the call. Much of our R&D is spent in these areas. That's because your concerns are our concerns.



Protecting your data means you're protecting your entire business. Fortunately, the e-STUDIO507 series has been designed to preserve the integrity and confidentiality of all your data. A new 320GB FIPS 140-2 Validated Self-Encrypting Drive (SED) with Data Overwrite are standard. An IPsec option to encrypt data being sent to or from the MFP, and Hard Copy Security are also available to keep your data right where it belongs.

Eco-consciousness.

At Toshiba, we realize we're responsible for helping our planet thrive. Whether it's our products, our company, or worthwhile environmental projects in your communities, we put green into action. The Toshiba e-STUDIO507 series has a low power sleep mode that meets the stringent requirements of Energy Star Tier 2. It is also RoHS eco-friendly features, the Toshiba e-STUDIO507 series is EPEAT purchasers choose products that reduce environmental impact. Together we can reduce, reuse and recycle in meaningful ways.







TOSHIBA Leading Innovation >>>



There's a configuration that is just right for every business need. And all of them are secure and EPEAT Registered.



Small and compact yet feature rich.

The Toshiba e-STUDIO507 series has features and benefits galore. You'll be impressed to find so much in such a compact footprint.



Efficient printing

Choose your speed at 35, 45, or 50 pages per minute. Also, first copy out times are as fast as 3.7 seconds.



Broad paper handling

Use up to a 3,200-sheet paper capacity and up to 110 lb index. You can select from a variety of paper sizes with 4 drawers or a tandem LCF.



Ease of use

A large 9" tilting touch panel is easy to read and use. A context sensitive help button that will provide you with whatever instructions you might need. Scanning or printing can be done on the go using a convenient USB port.



Reliability

The monthly copy volume goes up to 150,000 with a toner yield of 36,600 at 6% coverage and toner that can be changed on the fly. A compact service module design allows for surprisingly faster and easier periodic maintenance.



Connectivity and functionality

PCL6, PostScript3, and XPS as well as a Universal Printer Driver means you only need one driver across your entire fleet.



Innovative technology

Gigabit Ethernet support, e-filing for frequently reprinted jobs and an automatic OCR option for expert scanning are just a few of our leading innovations.



Latest e-BRIDGE platform

Toshiba's proprietary platform improves connectivity, security and fleet management. Take advantage of access to third-party solutions like PaperCut, Docuware and more.



Advanced finishing options

There is a convenient Inner Finisher, 50-Sheet High-Capacity Finisher, and a High-Capacity with Saddle-Stitch plus 2/3-Hole Punch.



Expert security

A 320GB FIPS 140-2 Validated Self-Encrypting Drive (SED) with Automatic Data Invalidation and Data Overwrite come standard. Also, an IPsec option encrypts data, and Hard Copy Security prevents the copying of sensitive documents.



Environmentally responsible

The e-STUDIO507 series is RoHS Compliant, Energy Star Tier 2 rated and EPEAT Registered (as part of the definitive global registry for greener electronics).

C-STUDIO 357/457/507



- > Black & White MFP
- > Up to 50 PPM
- > Small/Medium Workgroup
- > Copy, Print, Scan, Fax
- Secure MFP
- > EPEAT Registered

Specifications

Copying Process/Type IEPM (Dry Process)/Laser Technology

Original Reading Method CCD Line Sensor

Copy/Print Resolution 2400 x 600 dpi (with Smoothing)

Copy/Print Speed 35/45/50 PPM Warm-Up Time Approx. 20 Seconds First Copy Time 3.7 Seconds **Duty Cycle** 125K/150K/150K Multiple Copying Up to 999 Copies

Standard Paper Supply 2 x 550-Sheet, 100-Sheet Stack Feed Bypass

Maximum Paper Supply Up to 3,200 Sheets

Cassette: Statement-R to Ledger (17-28 lb), Bypass: Acceptable Paper Size

Statement-R to Ledger (17-110 lb), LCF: Letter (17-28 lb)

2GB RAM, 320 GB FIPS 140-2 SED Memory

Reduction/Enlargement 25% to 400%

100-Sheet Stack Feed Bypass Bypass Tray 9" Wide VGA Color Touch-Screen Control Panel Dimensions Approx. 23" x 23" x 30" (W x D x H)

Weight Approx. 132 lb Power Supply 115 Volts, 15 Amps Maximum 1.5kW Power Consumption PM Cycle 125K/150K/150K Black Toner Yield 36.6K Impressions @ 6%

e-BRIDGE Print Specifications

PCL6, PostScript 3, XPS PDL Support

Operating Systems Windows Server 2003, 2008, 2012, Vista SP2, 7, 8,

NetWare 6.5, Citrix, Macintosh 10.4-10.9

Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) Protocol Support w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/ iPrint, Apple Talk PAP or

EtherTalk, Port 9100 (bi-directional), WS Print, FTP Windows Server 2003, 2008, 2012, Vista SP2, 7, 8,

Macintosh OS 10.4-10.9 10/100/1000BaseTX Ethernet, Connectivity

802.11b/g/n, Wireless LAN, USB

AirPrint, e-BRIDGE Print & Capture Application on iOS and Wireless Device

Android (Available via Apple App Store or Google Play)

Top Access Device Management

eFMS 6.0 (e-BRIDGE Fleet Management Software) Certification

Windows 7, 8, 8.1,2008R2, 2012, 2012 R2,

WHQL, Novell, Citrix

Scan Specifications

Drivers

Scan Speed 57 SPM LT-Size @ 300 dpi, 45 SPM LT-Size @ 600 dpi

(When Copying), 43 SPM LT-Size @ 300 dpi (Color Scanning)

Scan Resolution Up to 600 dpi

File Format TIFF, PDF, Slim PDF, JPEG, XPS,

MS Word, MS Excel, Searchable PDF w/Adv. Scanning Option

Facsimile Specifications

Compatibility Super G3, G3 Data Compression MH/MR/MMR/JBIG Approx. 3 Seconds Per Page Transmission Speed

Fax Modem Speed 33.6 Kbps

Transmission and Reception 1GB (HDD), Fax Memory

Backup Permanent (HDD)

100 Jobs, 2,000 Destinations Max, 400 Destinations/Job Memory Transmission

0.7 Seconds Per Page, 50 Scans Per Minute Scan Speed

Internet Fax Network Fax Other Fax Functions

e-Filing Specifications

Operation Method Color Touch Screen Control Panel or Client PC Number of Boxes 1 Public Box, 200 Private User Boxes Capacity of Boxes 100 Folder Per Box. 400 Documents Per Folder.

1000 Pages Per Documents



Security (Standard)

Data Encryption 256 Bit AES

HDD Overwrite Meets Department of Defense (DoD) Standard 5220,22M

Authentication LDAP, SMTP, Windows Server Domain

Accessories (Options)

Input Options

100-Sheet RADF MR3028 Platen Cover KA1640PC

Additional Paper Options

550-Sheet Paper Feed Pedestal KD1025 KD1026 2,000-Sheet Large Capacity Feeder 550-Sheet Paper Feed Unit MY1033

Finishing Options

Job Separator MJ5006 Work Trav KK4550 Bridge Kit for Finisher KN2520N 50-Sheet Inner Finisher MJ1032N Saddle-Stitch Finisher (High Capacity) MJ1108 Saddle-Stitch Finisher (Low Capacity) MJ1033 50-Sheet Staple Console Finisher MJ1107 2/3-Hole Punch Unit for MJ1032N MJ6007 2/3-Hole Punch Unit for MJ1107 and MJ1108 MJ6104 2/3-Hole Punch Unit for MJ1033 MJ6008

Connectivity/Security Options

Fax Kit GD1350 2nd Line Fax GD1260F IPsec Enabler GP1080 Wireless LAN Adapter GN1050 GN3010 Antenna Meta Scan Enabler GS1010 Advanced Scanning GB1280T Harness Kit for Coin Controller GQ1180





















9740 Irvine Blvd., Irvine, CA 92618-1631 **Corporate Office**

Tel: 949-462-6000

East Coast 959 Route 46 East, 5th Floor, Parsippany, NJ 07054

Tel: 973-316-2700

Midwest 8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631

Tel: 773-380-6000

South 2037 Bakers Mill Rd., Dacula, GA 30019

Tel: 678-546-9385

West Coast 9740 Irvine Blvd Irvine CA 92618

Tel: 949-462-6000

Web Site www.business.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

© 2014 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv. Code: 22257 357/457/507 Brochure 5K PG 6/14