

Make a big impression – letter, legal or ledger.

e-STUDIO™ 360CP



TOSHIBA
Don't copy. Lead.



e-STUDIO™ 360CP

Digital Color Printer

The e-STUDIO360CP is a powerful color printer designed for large workgroups with ledger printing requirements. It produces black & white output at the rate of 36 pages per minute with a first print out time of just 9.5 seconds and color at 32 pages per minute with a 13.5 second first print out time. Also, a 2400 Image Quality mode creates crisp, brilliant images that are letter, legal or ledger size.



36/32

PAGES PER MINUTE

The e-STUDIO360CP offers 36 PPM monochrome and 32 PPM full-color printing.



2400 dpi Image Quality with Automatic Color Correction.



The e-STUDIO360CP offers standard network printing up to 11 x 17.

FEATURES

Dynamic Performance and Productivity

- Fast 36/32 Pages Per Minute Monochrome/Color
- 9.5/13.5 Sec. First Print Out Time Monochrome/Color
- Powerful 1 GHz Processor
- Excellent 2400 dpi Image Quality with Color Correction Control System
- Up to 200K Pages Per Month

Flexible Connectivity

- Standard 10/100BaseT
- USB Connection
- Parallel Connection
- USB Direct Print
- Optional 802.11b Wireless Connectivity

Effective Paper Handling

- Input Capacity up to 5,300 Sheets
- Output Capacity up to 1,650 Sheets
- Standard 550-Sheet Drawer
- Standard 100-Sheet Bypass
- Optional Duplex
- 11 x 17 Paper Size
- Specialty Stocks up to 102 lb. Index
- Envelope Printing through Bypass

Long Life Consumables

- 8K Yield Starter Toner (C,M,Y,K)
- 15K Yield Replacement Toner (Black)
- 14K Yield Replacement Toner (C,M,Y)
- Separate Drum and Toner Components
- User Changeable Supplies

OPTIONS

e-STUDIO360CP	36 PPM Mono/32 PPM Color LED Printer - 110V
1010042	802.11b Wireless Adapter
13N1778	550-Sheet Drawer
13N1781	3,000-Sheet Large Capacity Feeder
13N1782	2 x 550-Sheet Paper Feed Pedestal w/Stand
13N1783	Duplex Unit
13N1784	Finisher - Staple, 3 Hole Punch, Offset (Letter)
13N1786	Printer Cabinet/Stand, Tall
13N1787	Printer Stand, Short
13N1526	512 MB Memory
13N1530	40 GB Hard Disk Drive
X221930	14K Yield Cyan Toner Cartridge
X221936	14K Yield Magenta Toner Cartridge
X221939	14K Yield Yellow Toner Cartridge
X221933	15K Yield Black Toner Cartridge
X221232	Color Photoconductor Kit (3 Drums)
X221233	Black Photoconductor
X221234	Oil Coat Roller

SPECIFICATIONS

Engine Technology	Color LED
Print Speed	36 PPM Monochrome/32 PPM Color 9.5 Second First Print Out Time (FPOT) Monochrome 13.5 Second First Print Out Time (FPOT) Color
Print Quality	2400 dpi Image Quality
Processor	1 GHz
Memory	256 MB - Standard 1 GB - Maximum
Connectivity (Standard)	10/100BaseT Connection USB/Parallel Port USB Direct
Connectivity (Options)	802.11b Wireless Adapter
Compatibility	PostScript™ 3 Emulation PCL6™ Emulation
Paper Handling	Input Standard/Maximum – 650/5,300 Sheets Output Standard/Maximum – 650/1,650 Sheets
Media Sizes	Letter, Legal, Ledger, A3, A4, A5, JIS B4, JIS B5, Executive, Tabloid, and Universal (2.75" x 5" to 9.01" x 14"); Envelopes: DL, C4, C5, B5, 7, 9, 10
Media Types	Plain Paper, Envelopes, Card Stock, Transparencies, Paper Labels
Media Weights	Up to 102 lb. Index - Multipurpose Tray and Drawers Up to 102 lb. Index - Drawers 2-4 Up to 28 lb. Bond - LCF
Supplies	Ships with 8K Yield Starter Cartridges 14K Yield (C,M,Y) Replacement Color Cartridges 15K Yield (K) Replacement Black Cartridge
Operating Systems	Windows® 95 4.00950 or higher, 98, 2000, Me, Windows® NT 4.0, XP, Macintosh® 9.x, and 10.2 or higher, Novell® NetWare 3.x, 4.x, 5.x, 6.x, UNIX®, OS/400
Size	20.2" (H) x 27.4" (W) x 27.8" (D) 512mm x 695mm x 705mm
Weight	177 lb. (80.5 kg)
Acoustics	55 dBA Printing 45 dBA Idle
Maximum Monthly Volume	Up to 200,000 Pages Per Month

Corporate Office: 2 Musick, Irvine, California 92618-1631

East Coast: 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054
Tel: 973/316-2700 Fax: 973/263-2393

Midwest: 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631
Tel: 773/380-6000 Fax: 773/380-8077

South: 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024
Tel: 770/209-8540 Fax: 770/209-8556

West Coast: 142 Technology, Suite 150, Irvine, California 92618
Tel: 949/462-6262 Fax: 949/462-2700

Web Site: www.copiers.toshiba.com or www.fax.toshiba.com

© 2006 Toshiba America Business Solutions, Inc., Electronic Imaging Division
e-STUDIO360CP Specification Sheet/Inv. Code ES360CP2

Designs and specifications subject to change without notice. Actual specifications based on engine design and may vary according to usage and environment. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Toner yields are estimates, based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability.

AUTHORIZED TOSHIBA DEALER

TOSHIBA
COPY ■ PRINT ■ FAX ■ SCAN