

# > WILLPOS C10



# > WILLPOS C10

Compact and Multi-purpose Touchscreen Terminal

## > A ONE-STOP SOLUTION

Toshiba works with 'best of breed' software partners to provide a complete solution that can be tailored to the customer's requirements.

A support network in the majority of countries provides essential peace of mind that, once installed, the POS will be serviced and maintained by experienced engineers and service staff.



## > GREEN CREDENTIALS



Toshiba is committed to the design and manufacture of products that reduce environmental impact, creating environmental quality standards for each product and prescribing them with the highest levels required by the industry.

All Toshiba products are RoHS compliant.  
<http://www.toshibatec.co.jp/csr/report>

## > FEATURES AND BENEFITS

- Touchscreen
- Drip-proof
- Fan-less
- Small footprint
- Wall-mountable
- Integrated printer
- Optional battery\*
- Multi-colour design

**The Toshiba WILLPOS C10 –  
 Compact, multi-purpose, touchscreen terminal**

\* Future options

Your TOSHIBA Dealer:

WILLPOS C10	
<b>CHARACTERISTICS</b>	
<b>CPU</b>	Intel ATOM N450 1.66GHz
<b>Memory</b>	1GB (2GB Max.), DDR2 SODIMM, 2 x memory slots
<b>Display</b>	10.4" TFT touch (800 x 600)
<b>Built-in Customer Display</b>	20 characters x 4 lines
<b>Storage</b>	2.5" HDD SATA (160GB or over) / SSD (32GB or over)
<b>Interfaces</b>	1 x COM D-sub 9 pin (male) 5 x USB (front x 1, rear x 4) 1 x 24V drawer interface 1 x VGA (for 2nd display) 1 x LAN 10/100/1000-base ethernet 1 x SD card slot
<b>Audio</b>	Line-out / mic-in; mono speaker
<b>Operating System</b>	Microsoft® Windows XP (SP3), WEPOS1.1, POSReady 2009, Microsoft® Windows 7 Pro 32bit (SP1), SUSE® Linux Enterprise 11.0 (SP1)
<b>Driver</b>	OPOS, Java POS for Microsoft® Windows and Linux
<b>Colour</b>	Black & silver or white & silver (depending on model)
<b>Dimensions</b>	274(W) x 273(D) x 160(H) mm 10.8(W) x 10.7(D) x 6.3(H) inches
<b>Weight</b>	4.6kg / 10.14 lb including AC adaptor but without built-in customer display 4.7kg / 10.36 lb including AC adaptor and built-in customer display
<b>Power Supply</b>	Input 100 to 240V AC, Output : 24V DC; AC adapter
<b>INTEGRATED THERMAL PRINTER</b>	
<b>Max. Printing Speed</b>	Max. 170 mm/s
<b>Paper Width</b>	80 mm
<b>Cutter</b>	Auto cut (partial)
<b>OPTIONS</b>	
	Card reader (MSR), remote line display, wireless LAN adapter (USB)



The WILLPOS C10 'all-in-one' touchscreen terminal solution with its integrated printer and fan-less design is ideally suited to the most diverse range of markets. Mounted on the wall or sitting on the counter, mobile or wired, it is the stylish system with advanced functionality designed for applications in retail, manufacturing, transportation and hospitality.

## TOSHIBA

### TOSHIBA TEC AMERICA RETAIL INFORMATION SYSTEMS, INC.

2 Musick,  
 Irvine, CA, 92618-1631 USA  
 TEL: +1-949-462-2850  
<http://www.toshibatecusa.com>

### TOSHIBA TEC CANADA INC.

370 Britannia Road East, Unit 1  
 Mississauga, Ontario, Canada  
 L4Z 1X9  
 TEL: +1-905-890-8283  
<http://www.toshibateccanada.com>

DESIGNHUT.CO.UK - JINGBINAUS

# TOSHIBA

Leading Innovation >>>







**WILLPOS C10**

# > COMPACT AND FLEXIBLE: THE ALL-IN-ONE POS PACKAGE

Rugged and reliable, the WILLPOS C10 is designed for the widest range of applications and environments - a truly multi-purpose solution with stylish aesthetics, fan-less operation and the smallest of footprints.



*In-built customer display*



## > COMPACT PERFORMER

With its tiny footprint, the WILLPOS C10 touchscreen terminal easily fits into the vast majority of counter set-ups. The integrated silent thermal receipt printer with auto-cut and easy media loading makes the WILLPOS C10 a truly diminutive 'all-in-one' business solution.



## > FLEXIBLE SET-UP

The WILLPOS C10 can be configured either on a counter or wall. This means it can be used in applications such as transportation, kiosks, concessions and others not normally possible with traditional POS solutions.



## > ENERGY NOT POWER

The innovative Intel Atom 1.66 Ghz processor has a low power consumption and low heat emissions giving the WILLPOS C10 excellent performance without needing the associated high power to drive it.




## > RUGGED & SPILL-PROOF

With rugged casing and a splash-proof design, the WILLPOS C10 can operate in the most harsh service environments, providing a durable and stable platform with a low total cost of ownership.



## > CLASSY LOOKS

A perfect fit for even the most chic shops and restaurants, the WILLPOS C10 boasts clean and stylish aesthetics, a sleek 10.4 inch touch TFT and silent operation. And, with a wide choice of colour panels, it can be tailored to reflect a store's image and brand.



## > TRUSTED RELIABILITY

Toshiba manufactures all components within its entire range of POS solutions to guarantee reliability and consistency. The WILLPOS C10 has been designed with non-moving parts and fan-less operation to maximise this reliability and the low cost of ownership throughout the life of the product.



## > MOBILE OPTIONS

An integrated battery\* option offers flexibility for both fixed and mobile retailing applications. With approximately 5 hours battery life, the WILLPOS C10 can seamlessly operate in wireless trading environments, offering a solution adjustable to the customer's needs.



## > THE TOTAL PACKAGE

The Windows® 7-ready WILLPOS C10 is available with a full range of options, including customer display and MSR. A number of communication devices and expandable COM ports\* ensure the system is future-proofed and flexible.



*\* Future options*

**TOSHIBA**  
Leading Innovation >>>



Mobile Kiosks



Café



Fashion Stores



Bars



Corner Shops