

TOSHIBA

e-STUDIO™ 6518AG

e-STUDIO™ 8518AG

- > Black & White Multifunction Printer
- > Up to 85 PPM
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Customizable UI



e-STUDIO™ 6518AG/8518AG

Main Specifications

Copy System	Indirect Electrostatic Photographic Method/ Laser Printing/ Heat Roller Fusing
Display	10.1" Color WSVGA Touch Screen Tilting Display
Copy Speed	65/85 PPM (LT)
First Copy Out	5.2/4.1 Seconds
Warm-Up Time	Approx. 24/20 Seconds
Copy Resolution	2400 dpi (Equivalence) x 600 dpi (with Smoothing)
Stack Feed Bypass	3.9" x 5.8" to 13" x 19", 12" x 47" Banner, Envelope
Multiple Copying	Up to 9,999 Copies
Paper Capacity	Standard 3,520 Sheets/Max. 6,020 Sheets (Tandem Drawer)
Original Feed	Standard 300-Sheet DSDP
Scan Speed & Weights	DSDP Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color), Simplex: 9.3-110 lb Index, Duplex: 9.3-110 lb Index
Max. Original Size	LD
Paper Feed Sizes	Drawers: 540 Sheets-ST-R to 12" x 18" Integral Tandem LCF 1,160 x 2 LT-Only Stack Feed Bypass: 120 Sheets-3.9" x 5.8" to 13" x 19", 12" x 47" Banner Opt. 2,500-Sheet Ext. LCF LT-Only
Paper Weights	Tandem LCF 1,160 Sheets x 2-16 lb Bond-140 lb Index Plus 540 Sheets x 2-16 lb Bond-140 lb Index Stack Feed Bypass: 120 Sheets-16 lb Bond-110 lb Cover Opt. 2,500-Sheet Ext. LCF LT-Only-16 lb Bond-140 lb Index Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)
Duplex	
Reproduction Ratio	25% to 400%
Max Duty Cycle	Max. 590K/720K Month
Weight	Approx. 430 lb
Approx. Dimensions	37.6" (W) x 27.5" (D) x 48.3" (H)
Toner Yield	106,600 @ 5%
Power Source	120 Volts, 50/60 Hz, 16 Amps
Power Consumption	Maximum 2.0kW (I20V)
CPU	Intel Atom™ 1.33 GHz (Dual-Core)
Memory	4GB
Hard Disk Drive	320GB FIPS 140-2 Validated Self-Encrypting Drive

e-BRIDGE Next Print Specifications

PDL	PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG
Print Speed	65/85 PPM (LT)
Print Resolution	600 x 600 dpi, 2,400 (Equivalence) x 600 dpi (With Smoothing), 1,200 x 1,200 dpi (2-bit) or 3,600 (Equivalence) x 1,200 dpi, PS Only
Operating Systems	Windows Server® 2008 R2, R2 SP1, 2008/SP2, Windows® 7,8.1,10, Windows Server® 2012/R2, Windows Server 2016®, Macintosh® (macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, macOS 10.12, 10.13), Unix®, Linux®
Network Protocols	TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, EtherTalk for Macintosh® Environments
Printing Protocols	SMB, LPR/LPD, IPP (Ver.2.0) w/Authentication, AppleTalk® PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/ iPrint, WS Print, FTP
Print Drivers	Windows Server® 2008 SP2 (32-bit, 64-bit) Windows Server® 2008 R2 SP1 (64-bit), Windows® 7 SP1 (32-bit,64-bit), Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows Server 2016®, Windows® 10 (32-bit, 64-bit), macOS X 10.7.4, 10.8, 10.9, 10.10, 10.11, macOS 10.12, 10.13
Interface	RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed) Optional
Wireless Device	802.11b/g/n, Wireless LAN, Optional Bluetooth
Device Management	AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play)
Account Control	TopAccess, EFMS 6.3 (e-BRIDGE Fleet Management Software)
Accessibility Features	Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows® Domain) or Login Name/Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function
	Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Timeout and Audible Beep Message Alerts



Security Features

User Authentication, On-Board Data Scramble Function, SCEP, Disable e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408)* with HCD-PP v1.0, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, NFC Authentication *Conformance with HCD-PPv1.0 in High Security Mode.

Environmental Stds. Certification

ENERGY STAR® (V2.0), EPEAT Gold
WHQL (Windows® 7, 8, 8.1, 10, 2008 R2, 2012, 2012 R2), Novell®, Citrix®, SAP, AirPrint®, Mopria®

Scan Specifications

Scan Speed	DSDP Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color)
Scan Modes	Standard: Full Color, Auto Color, Monochrome, Grayscale
Scan Resolution	600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi
File Formats	Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG, TIFF-Multi/Single Page, PDF-Multi/Single Page, Slim PDF, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.)
Image Compression	Color/Grayscale: JPEG (High, Middle, Low)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	Up to 33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job
Scan Speed	0.7 Seconds Per Page, Maximum 73 IPM

e-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder/Box, 200 Pages Per Document

Accessories (Options)

Additional Paper Options		IPsec Enabler	GP1080
Large Capacity Feeder	MP2502B	Unicode Font Enabler	GS1007
Finishing Options		Embedded OCR Enabler	
50-Sheet Staple Finisher	MJ1111B	Per Seat License	GS1080
Saddle-Stitch Finisher	MJ1112B	Multi-Station Print Enabler	
Hole Punch Unit for MJ1111B/MJ1112B	MJ6106N	Per Seat License	GS1090
Side Exit Tray	KA6551	SharePoint® Connector	GB1440
Finisher Guide Rail	KN1103	Exchange Connector	GB1450
		Google Docs™ Connector	GB1540
Connectivity/Security Options		Miscellaneous Options	
FAX Unit/2nd Line for FAX Unit	GD1370N	Accessible Arm	KK2550
Wireless LAN/Bluetooth	GN4020	Harness Kit for Coin Controller	GQ1280
Bluetooth Keyboard	GR9000	Manual Pocket	KK5008
Accessory Tray	GR1330		
Panel 10-Key Option	GR1340		
Card Reader Holder	GR1320		
Meta Scan Enabler	GS1010		

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

Corporate Office

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000

East Coast

959 Route 46 East, 5th Floor, Parsippany, NJ 07054
Tel: 973-316-2700

Midwest

8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631
Tel: 773-380-6000

South

2037 Bakers Mill Rd., Dacula, GA 30019
Tel: 678-546-9385

West Coast

25530 Commercentre Drive, Lake Forest, CA 92630
Tel: 949-462-6000

Web Site

www.business.toshiba.com