

TOSHIBA

TOSHIBA PRINTER AND PANTHER SHADOW PRINT & APPLY SYSTEM

- Entry Level Print and Apply System
- Toshiba BEX4T1 or BEX4T2 Industrial printers
- Prints and applies label up to 4.7" x 8"
- Applies 10-40 labels per minute*
- 800 meter/2,624' – 8'OD Ribbon (BEX4T1)
- Stand-Alone or automated production integration



*Varies depending on label length, printer speed, and height of the product labeled.

STANDARD FEATURES



Printer

- > Rugged Industrial printer series
- > BEX4T1 or BEX4T2 printer
- > Thermal Transfer or Direct Thermal printers
- > Resolution in 200 or 300 DPI
- > Maximum print speed – 14 IPS (BEX4T1)
12 IPS (BEX4T2)
- > Label Roll 8” OD, 3” Roll Core
- > Large Ribbon Capacity
800 meter (BEX4T1)
600 meter (BEX4T2)
- > Label Roll 8” OD, 3” Roll Core

- > Long head life warranty –
3 million linear inches
- > Programming language –
TPCL (Toshiba), ZPL (Zebra)
- > Printer Communication Interface –
USB and Ethernet

Applicator

- > 13” Stroke (Peel/Home to base +13”)
- > Auto – Tamp Product Contact Sensing
- > Print Request Push Button
- > Table Top mount

OPTIONAL STAND




Top Apply-Optional Stand



Side Apply-Optional Stand

Models	PASHADOWT1	PASHADOWT2
Printer Specification		
Printer Model	BEX4T1GS12DM01	BEX4T2GS12M01
Head Type	New Edge	Flat
Technology	Thermal Transfer/Direct Thermal	Thermal Transfer/Direct Thermal
Resolution	203 or 305 DPI	200 or 300 DPI
Print Speed	14 IPS	12 IPS
Print Width (Max)	4.09”	4.09”
Media		
Ribbon Length (Max)	800M (2,624’)	600M (1,968’)
Ribbon Core Diameter	1”	1”
Ribbon Outer Diameter (OD)	3.45”	3.45”
Ribbon Type	CSO	CSO
Label Width (Min-Max)	.98” – 4.72”	.98” – 4.72”
Label Length (Min-Max)	2” – 8”	2” – 8”
Label Core Diameter	3”	3”
Label Outer Diameter (OD)	8” Roll	8” Roll
Printer Communication (Std)	USB, Ethernet	USB, Ethernet
Printer Communication (Opt)	USB, Ethernet, Serial USB, Ethernet, Parallel USB, Ethernet, Wireless (802.11 b/g) RFID, Ribbon Save	USB, Ethernet, Serial USB, Ethernet, Parallel USB, Ethernet, Wireless (802.11 b/g)
Options		
Printer Environment		
Operating Temperature	40 °- 104° F (5° to 40°C)	40 °- 104° F (5° to 40°C)
Humidity	25-85% RH (Non-Condensing)	25-85% RH (Non-Condensing)
Shadow Applicator (standard)		
Type	Electric – No Compressed Air	Electric – No Compressed Air
Stroke	13” (Peel/Home to Base +13”)	13” (Peel/Home to Base +13”)
Tamp	Auto-Tamp Product Contact Sensing Print Request Push Button	Auto-Tamp Product Contact Sensing Print Request Push Button
Power	Electrical 115-240 VAC, 50/60 Hz at 5A max (No Air Required)	Electrical 115-240 VAC, 50/60 Hz at 5A max (No Air Required)
Configuration	Table - Top	Table - Top
Applicator (option)	Stand Mount – Side Apply Stand Mount – Top Apply Palm Switch Foot Switch	Stand Mount – Side Apply Stand Mount – Top Apply Palm Switch Foot Switch
Applicator Shipping Weight	97 LBS	97 LBS


SPECIFICATIONS



Side View



Front View



Top View



Scan for more info

