TOSHIBA

e-STUDIO™2525AC/3025AC/3525AC/4525AC

Introducing a new generation of Toshiba MFPs – with high-performance, advanced security and cloud-ready features, these printers are the perfect choice for today's modern work environments.

- Highly Productive Color MFPs
- High-speed – 25, 30, 35 & 45 PPM
- Leading-edge Security Features
- Cloud Print & Service Capabilities
- Built-in Optical Character Recognition



e-STUDIO 2525AC/3025AC/3525AC/4525AC

Main Specifications

Copy System	Indirect Electrostatic Photographic/OPC/Laser Printing/Heat Roller Fusing
Display	10.1" Color WSVGA Touch Screen Tilting Display
Copy Speed	25/30/35/45 PPM (LT)
First Copy Out	Color: Less Than 7.8/7.8/7.8/5.7 Seconds Monochrome: Less Than 5.9/5.9/5.9/4.4 Seconds
Warm-Up Time	From powering on: Approx. 20 Seconds From Sleep & Low Power: Less Than 12 Seconds
Copy Resolution	600 × 600 dpi
Stack Feed Bypass	3.9" x 5.8" to 12" x 18", 12" x 47" Banner, Envelope
Multiple Copying	Up to 999 Copies
Paper Capacity	Standard 1,200 Sheets/Max. 5,200 Sheets
Original Feed	300-Sheet DSDF or DSDF with Double Feed Detection or 100-Sheet RADF
Scan Speed & Weights	DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color), RADF Scan: Up to 73 IPM (Monochrome or Color), DSDF Simplex or Duplex: 9.3-110lb Index, RADF Scan: Simplex: 9.3-41.8lb Bond, Duplex: 13.3-41.8lb Bond
Max. Original Size	LD/A3
Paper Feed Sizes	Drawer 1: 550 Sheets-ST-R to LD Drawer 2: 550 Sheets-ST-R to 12" x 18" Stack Feed Bypass: 100 Sheets-3.9" x 5.8" to 12" x 18", 12" x 47" Banner Opt. 550-Sheet Paper Feed Pedestal-ST-R to 12" x 18" Opt. 550-Sheet Drawer for PFP-ST-R to 12" x 18" Opt. Envelope Cassette for PFP-Approx. 60 Envelopes/550 Sheets-ST-R to LG Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-LT Only Opt. 2,000-Sheet External LCF-LT Only
Paper Weights	Standard: 550 Sheets x 2-16lb Bond-110lb Cover Stack Feed Bypass: 100 Sheets-14lb Bond-110lb Cover Opt. 550-Sheet Paper Feed Pedestal-16lb Bond-110lb Cover Opt. 550 Sheets Drawer for PFP-16lb Bond-110lb Cover Opt. Envelope Cassette for PFP-16lb Bond-140lb Index Opt. 2,000-Sheet Tandem LCF (Pedestal Type)-17lb-28lb Bond Opt. 2,000-Sheet External LCF-LT 16lb Bond-110lb Cover
Duplex	Standard Automatic Duplex Unit (16lb Bond-140lb Index)
Reproduction Ratio	25% to 400%
Max Duty Cycle	Max. 75K/90K/105K/105K Month (Color: 100%) Max. 150K/180K/210K/210K Month (Monochrome: 100%)
Weight	Approx. 169lb/172lb
Approx. Dimensions	23" (W) x 25.2" (D) x 31" (H)
CMYK Toner Yield	CMY: 38K, K: 39.8K @ 5%
Power Source	120 Volts, 50/60 Hz, 12 Amps
Power Consumption	Maximum 1.8kW (120V)
Plug Type	NEMA 5-15
Memory	4GB
Hard Disk Drive	128GB Solid State Drive (SSD)

e-BRIDGE Next Print Specifications

PDL	PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG
Print Resolution	600 × 600 dpi (5 bit), 1,200 × 1,200 dpi (Color/2 bit) or 3,600 (Equivalence) x 1,200 dpi (BW/with Smoothing) (PS3 Only)
Operating Systems	Windows® 8.1,10, 11, Windows Server® 2012/R2, Windows Server® 2016/19/22, Macintosh® (macOS X 10.10-15, 12), Unix®, Linux®
Network Protocols	TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, EtherTalk for Macintosh Environments
Printing Protocols	SMB V1-3, LPR/LPD, IPP V1.2 w/Authentication (TLS 1.2/1.3), AppleTalk® PAP or EtherTalk, Port 9100 (Bi-Directional), NetWare P-SERVER LPD w/iPrint, Bluetooth (HCRP/BIP/OPP/FTP), WS Print, FTP
Print Drivers	Windows® 8.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows Server® 2016/19/22, Windows® 10, 11 (64-bit), macOS X 10.12-15, 11, 12
Interface	RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-Speed) Optional IEEE802.11b/g/n, Wireless LAN, Optional Bluetooth
Wireless Device	AirPrint®, Mopria®, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple® App Store or Google Play)
Device Management	TopAccess
Account Control	Up to 10,000 Users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows® Domain) or Login Name/Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function
Accessibility Features	Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Timeout, Audible Beeps, Optional Voice Assist
Security Features	User Authentication, Trusted Platform Module, On-Board Data Scramble Function, SCEP, Disable, e-Filing, Disable Copy, Disk Overwrite* , IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL/TLS (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS, SYSLOG), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408)* with HCD-PP v1.0, IEEE802.1X (Wired/Wireless), Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp, Role Based Access Control, Secure PDF, Digital Signature for Firmware Update, Integrity Check Function, Image Log, Card Authentication, Biometric Authentication *Requires FIPS HDD, Conformance with HCD-PPv1.0 in High Security Mode
Environmental Standards	ENERGY STAR® (V3.1), EPEAT Gold, Californian Proposition 65
Certifications	WHQL (Windows® 8, 8.1, 10, 11, 2012, 2012 R2, 2016/19/22), Novell®, Citrix®, SAP, AirPrint® and Mopria®

Scan Specifications

Scan Speed	DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color) RADF Scan: Up to 73 IPM (Monochrome or Color)
Scan Modes	Standard: Full Color, Auto Color, Monochrome, Grayscale
OCR	DOC/XLS/PPT/PDF
Scan Resolution	600 dpi, 400 dpi, 300 dpi, 200 dpi, 150 dpi, 100 dpi
File Formats	Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, PDF/A, Searchable PDF, XPS-Multi/Single Page, DOCX, XLSX, PPTX, Color/Grayscale: JPEG, TIFFMulti/Single Page, PDF-Multi/Single Page, PDF/A, Slim PDF, Searchable PDF, XPSMulti/Single Page, DOCX, XLSX, PPTX
Image Compression	Color/Grayscale: JPEG (High, Middle, Low)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	Up to 33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job
Scan Speed	0.7 Seconds Per Page, Maximum 73 IPM

e-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder/Box, 200 Pages Per Document

Accessories (Options)

Platen & Document Feeder Options	
DSDF	MR4010
DSDF with Double Feed Detection	MR4020
RADF	MR3033
Platen Cover	KA5005PC
Additional Paper Options	
Paper Feed Pedestal	KD1072
Drawer Module	MY1052
Envelope Cassette Option	MY1053
Large Capacity Feeder	KD1073LT
External Large Capacity Feeder	MP2002
Finishing Options	
50-Sheet Inner Finisher	MJ1048
65-Sheet Staple Finisher	MJ1113
65-Sheet Saddle-Stitch Finisher	MJ1114
Hole Punch for MJ1048	MJ6011
Hole Punch for MJ1113/MJ1114	MJ6107
Bridge Kit	KN5005
Job Separator	MJ5015
Connectivity/Security Options	
FAX Unit/2nd Line for FAX Unit	GD1370N
Wireless LAN/Bluetooth	GN4030A3
Fax Over IP License Key	GS1100NODE
Bluetooth Keyboard	GR9001
2nd NIC Holder	GR1430
USB Hub	GR1420
Meta Scan Enabler	GS1010NODE
IPSec Enabler	GP1080NODE
Unicode Font Enabler	GS1007NODE
Multi-Station Print Enabler Per Seat License	GS1090NODE
e-BRIDGE Plus for OneDrive for Business V3.0	GB2300NODE
e-BRIDGE Plus for SharePoint Online V3.0	GB2310NODE
e-BRIDGE Plus for Exchange Online V3.0	GB2320NODE
e-BRIDGE Plus for Gmail	GB2380NODE
e-BRIDGE Plus for Google Workspace	GB2390NODE
Hardcopy Security Printing	GP1190NODE
Security SSD (512GB)	GE1280
FIPS SSD (512GB)	GE1350
e-BRIDGE Plus Voice Guidance	GB2540NODE
e-BRIDGE Global Print	GB2550NODE
Miscellaneous Options	
Card Reader Holder	GR1320
Accessory Tray	GR1330
Panel 10-Key Option	GR1340
Stand	STAND5015
Work Tray	KK5005
Manual Pocket	KK5008
Harness for Coin Controller	GQ1280
Accessible Arm	KK2560
Power Filter 120V/15A	W1500-15-120

Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Product names may be trademarks of their respective companies. AirPrint® and the AirPrint® logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1. All company and/or product names are trademarks and/or registered trademarks of their respective manufacturers in their markets and/or countries.

© 2026 Toshiba America Business Solutions, Inc. Electronic Imaging Division
Inv. Code 22413 e-STUDIO2525AC/3025AC/3525AC/4525AC Spec Sheet 6/26

Corporate Office	25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	25530 Commercentre Drive, Lake Forest, CA 92630 Tel: 949-462-6000
Website	business.toshiba.com