

Safety Data Sheet

1. Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier:

Product name: T-FC34U-Y

e-STUDIO407CS Series

SDS NO. TFC34UY-1

1.2 Relevant identified uses of the substance or mixture and uses advised against

Toner for electrophotographic equipment

1.3 Details of the supplier of the safety data sheet

Manufacturer Toshiba TEC Corporation

Address: Gate City Ohsaki West Tower 1-11-1,Osaki,Shinagawa-ku,Tokyo,141-8562,Japan

Telephone number: +81-3-6830-9100

Supplier

Toshiba America Business Solutions, Inc.

Emergency Telephone.No. +1-800-424-9300(CHEMTREC)

For calls within the U.S.only.

+1 703-527-3887(collect calls accepted) (CHEMTREC)

Outside USA and Canada

Toshiba of Canada Limited

Telephone No.+1-905-470-3500

For calls within Canada only.

2. Hazards identification

GHS classification and label elements of the product

2.1 Classification of the substance or mixture

HEALTH HAZARDS

Acute toxicity Oral: Out of class

Skin corrosion/irritation: Out of class

Skin sensitization: Out of class

(Note) GHS classification without description: Not applicable/Out of classification/Not classifiable

3. Composition/information on ingredients

Substance/Mixture:

3.2 Mixture

Ingredient name	Content(%)	CAS No.
Polyester resin	-----	-----
Pigment	-----	-----
Wax(1)	-----	-----
Wax(2)	-----	-----
Surface Additive	-----	68611-44-9

----- TRADE SECRET

4. First-aid measures

4.1 Descriptions of first-aid measures

Inhalation

Remove from exposure area to fresh air immediately.

Contact a physician if there is any difficulty in breathing or other signs of distress.

Skin Contact

Wash with soap and water.

If irritation occurs or is persistent, seek medical attention.

Eye Contact

Immediately flush eyes with plenty of water for at least 15 minutes.

If irritation persists, call a physician.

Ingestion

Dilute stomach contents with several glasses of water.

5. Fire-fighting measures

5.1 Extinguishing media

Suitable extinguishing media

Foam, carbon dioxide, dry chemical, water fog

Unsuitable extinguishing media

None

5.2 Special Hazards

Can form explosive dust-air mixtures when finely dispersed in air.

5.3 Advice for firefighters

Special protective equipment and precautions for fire-fighters

Wear cold insulating gloves/face shield/eye protection.

6. Accidental release measures

6.1 Personnel precautions, protective equipment and emergency procedures

Wear proper protective equipment.

Avoid breathing dust.

6.2 Environmental precautions

Do not wash away into shower or waterway.

6.3 Methods and materials for containment and cleaning up

Sweep slowly spilled toner/developer and carefully transfer into a waste container.

7. Handling and storage

7.1 Precautions for safe handling

Preventive measures

Do not breathe dust.

Exhaust/ventilator

No special ventilation equipment is needed under intended use.

7.2 Conditions for safe storage, including any incompatibilities

Recommendation for storage

Store in a dry place.

Keep out of the reach of children.

7.3 Specific end use(s)

Toner for electrophotographic equipment

8. Exposure controls/personal protection

8.1 Control parameters

ACGIH

(as the product)

TWA 15mg/m³(Total dust)5mg/m³(Respirable fraction)

DMG-MAK

(as the product)

4mg/m³(Inhalable fraction)1.5mg/m³(Respirable fraction)

8.2 Exposure controls

Individual protection measures

Respiratory protection

Not required under intended use.

Hand protection

Not required under intended use.

Eye protection

Not required under intended use.

Skin and body protection

Not required under intended use.

9. Physical and Chemical Properties

9.1 Information on basic physical and chemical properties

Physical properties

Appearance: Powder/granule

Color: Yellow

Odor: None

Specific gravity/Density: 1.2g/cm³

Solubility

Solubility in water: Insoluble

9.2 Other information

Explosive Properties

Little possibility in intended use.

According to Explosive Evaluation, can form explosive dust-air mixtures when finely dispersed in air, like most finely grained organic powder.

10. Stability and Reactivity

10.2 Chemical stability

Stable.

10.3 Possibility of hazardous reactions

None

10.5 Incompatible materials

None

10.6 Hazardous decomposition products

None

11. Toxicological Information

11.1 Information on toxicological effects

Acute toxicity

Acute toxicity (Oral), Product

LD50 > 2,000mg/kg

(This was the highest attainable mass.)

Irritant properties

Skin corrosion/irritation

Non-irritant.

Skin sensitization

Non-sensitizer

Germ cell mutagenicity

Ames test :Negative

No Carcinogenic effects data available

No reproductive toxicity data available

Delayed and immediate effects and also chronic effects from short- and long-term exposure

Chronic Effects

In a study in rats by chronic inhalation exposure to a typical toner, a mild to moderate degree of lung fibrosis was observed in 92 % of the rats in the high concentration (16 mg/m³) exposure group, and a minimal to mild degree of fibrosis was noted in 22% of the animals in the middle (4mg/m³) exposure group. These findings are attributed to "lung overloading", a general response to excessive amounts of any dust retained in the lungs for a prolonged period.

No Aspiration hazard data available

12. Ecological Information

12.1 Toxicity

No Aquatic toxicity data available

No Persistence and degradability data available

No Bioaccumulative potential data available

No Mobility in soil data available

Ozone depleting chemical data not available

13. Disposal considerations

13.1 Waste treatment methods

Dispose of in accordance with local, state and federal regulations.

Empty plastic container may be recycled.

14. Transport Information

UN No, UN CLASS

Not applicable to UN NO.

Land DOT 49 CFR,ADR :Not classified as Dangerous Goods

Sea IMDG Code :Not classified as Dangerous Goods

Air ICAO-TI :Not classified as Dangerous Goods

15. Regulatory Information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

US/Canada Information

Toxic Substance Control Act (TSCA)

All chemical substances in this product comply with all applicable rules or orders under TSCA.

California Proposition 65

Not regulated.

OSHA Hazard Communication Standard, 29CFR 1910.1200
Not regulated.
RCRA(40 CFR 261)
Product or components not listed.
CERCLA/SARA Information
Not regulated.
NTP Annual Report on Carcinogens
Not listed as an NTP carcinogen.

Controlled Products Regulations(Canada)
This product has been classified in accordance with the hazard criteria of the CPR.
Workplace Hazardous Materials Information System (Canada)
No toxicology information available.

EU Information
Regulation(EC)No.1907/2006(REACH)
All chemical substances in this product comply with all applicable rules or order under 1907/2006.

Australian Information
Not classified as hazardous according to criteria of NOHSC
The substance is being imported or manufactured under a permit granted under section 21U of the Industrial Chemicals (Notification and Assessment) Act 1989

16. Other information

Reference Book

Globally Harmonized System of classification and labelling of chemicals, (4th ed., 2011), UN Recommendations on the TRANSPORT OF DANGEROUS GOODS 18th edit., 2013 UN Classification, labelling and packaging of substances and mixtures (table 3-1 ECNO6182012)
2012 EMERGENCY RESPONSE GUIDEBOOK(US DOT)
2014 TLVs and BEIs. (ACGIH)
<http://monographs.iarc.fr/ENG/Classification/index.php>
Pulmonary Response to Toner upon Chronic Inhalation Exposure in Rats
H.Muhle et.al; Fundamental and Applied Toxicology 17.280-299(1991)
Lung Clearance and Retention of Toner, Utilizing a Tracer Technique, during Chronic Inhalation Exposure in Rats
B.Bellmann; Fundamental and Applied Toxicology 17.300-313(1991)

Definitions and Abbreviations

OSHA PEL stands for Permissible Exposure Limit under Occupational Safety and Health Administration (USA)
ACGIH TLV stands for Threshold Limit Value under American Conference of Governmental Industrial Hygienists (USA)
DFG-MAK stands for Maximale Arbeitsplatzkonzentrationen under Deutsche Forschungsgemeinschaft
TWA stands for Time Weighted Average
IARC stands for International Agency for Research on Cancer
NTP stands for National Toxicology Program (USA)
DOT stands for Department of Transportation (USA)
NOHSC stands for National Occupational Health and Safety Commission (Australia)
ADG stands for Australian Dangerous Goods

Restrictions

This information contained in this data sheet represents the best information currently available to us. However, no warranty is made with respect to its completeness and we assume no liability resulting from its use. It is advised to make their own tests to determine the safety and suitability of each such product or combination for their own

purposes.

The data given here is based on current knowledge and experience. The purpose of this Safety Data Sheet is to describe the products in terms of their safety requirements. The data does not signify any warranty with regard to the products' properties.