

# TOSHIBA MATERIAL SAFETY DATA SHEET

Date of Preparation : 24 July, 2013  
Date of Revised :

No. : EOIL965W1W

Page 1 of 5

## SECTION 1 CHEMICAL PRODUCT AND COMPANY IDENTIFICATION

Product Name : OIL-965(Oil in FR-KIT-FC50/FR-KIT-FC50H)  
Used for : Toshiba MFP for e-STUDIO4555C/5055C  
Company Name : Toshiba TEC Corporation  
Address : Gate City Ohsaki West Tower  
1-11-1, Osaki, Shinagawa-ku, Tokyo 141-8562, Japan  
Telephone Number : TEL +81-3-6830-9100

Contact : (1) Toshiba America Business Solutions, Inc.  
Emergency Telephone. No. : +1-800-424-9300  
For calls within the U.S. only.

(2) Toshiba of Canada Limited  
Telephone. No. : +1-905-405-3500  
For calls within Canada only.

(3) Toshiba TEC Germany Imaging Systems GmbH  
Telephone. No. : +49-2131-1245-0  
(European Headquarter)

(4) Toshiba (Australia) Pty, Ltd.  
Telephone. No. : +61-2-98873322

(5) Toshiba Tec Information Systems(ShenZhen)Co.,Ltd  
Emergency Telephone. No. : +86-755-27311901  
For calls within China only

(6) Toshiba Singapore Pte Ltd  
Telephone No. : +65-6516-0380

(7) TAISHIBA INTERNATIONAL CO.,LTD.  
Telephone. No. : +886-2-2718-7879 Ext.2750  
For calls within Taiwan only.

## SECTION 2 COMPOSITION/INFORMATION ON INGREDIENTS

This product is classified as a Single

<u>INGREDIENT(S)</u>	<u>CAS No.</u>	<u>wt.%</u>
Polydimethylsiloxane	Confidential	100

No hazardous materials present

## SECTION 3 HAZARDS IDENTIFICATION

HAZARDS CLASSIFICATION:

: None (based on IMO)  
: None (based on DOT)

FIRE AND EXPLOSION

: Not considered flammable nor combustible, but will burn if involved in a fire.

POTENTIAL HEALTH EFFECT

SKIN contact : May cause slight skin irritation, but no significant effect.  
EYES contact : May cause slight eyes irritation.  
INGESTION : No information is available.

# MATERIAL SAFETY DATA SHEET

Product Identity

: OIL-965(Oil in FR-KIT-FC50/FR-KIT-FC50H)

No. : EOIL965W1W

Page 2 of 5

---

## SECTION 4 FIRST AID MEASURES

- Eye Contact : Immediately wash out with running water for at least 15 minutes. Seek medical treatment.
- Skin Contact : Immediately wash out with soap and running water. Seek medical treatment, depending on the symptoms.
- Inhalation : Rest in fresh air and seek medical treatment, depending on the symptoms.
- Ingestion : Wash out mouth with water provided person is conscious. Never give anything by mouth to an unconscious person. Call a physician immediately.

## SECTION 5 FIRE FIGHTING MEASURES

### EXTINGUISHING MEDIA

- : Foam, dry chemical or carbon dioxide

### SPECIAL FIRE FIGHTING PROCEDURE

- : None

### UNUSUAL FIRE AND EXPLOSION HAZARD

- : None

## SECTION 6 ACCIDENTAL RELEASE MEASURES

### STEP TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED

- : Contain the spill or leak.  
Scrape up with cardboard or rag and place in container.

## SECTION 7 HANDLING AND STORAGE

- Handling : Keep container closed when not in use.  
Avoid contact with eyes and prolonged or repeated skin contact.  
Keep out of reach of children.
- Storage : Store in a cool place. Keep away from heat and flame.  
Do not lay the container on its side.

## SECTION 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Administrative Exposure Limit . : Not established

### EXPOSURE GUIDELINES

ACGIH TLV-TWA : Not established

OSHA PEL : Not established

### RESPIRATORY PROTECTION(specify type)

- : See SECTION 11 of this MSDS for OTHER INFORMATION

### VENTILATION:

LOCAL EXHAUST: : See SECTION 11 of this MSDS for OTHER INFORMATION

Special : Unknown

Other : Unknown

Protective Gloves . : Plastic film or rubber gloves

Eye and Face Protection . : Safety glasses

### OTHER PROTECTIVE CLOTHING OR EQUIPMENT

- : Eyewash equipment

### WORK/HYGIENIC PRACTICES

- : Wash hands after handling.
-

# MATERIAL SAFETY DATA SHEET

Product Identity

: OIL-965(Oil in FR-KIT-FC50/FR-KIT-FC50H)

No. : EOIL965W1W

Page 3 of 5

---

## SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Fluid and Brown  
Odor : Odorless  
Boiling Point : Not applicable  
Melting Point : Not applicable  
Specific Gravity(H<sub>2</sub>O=1) : 0.97 (25 degrees C)  
Vapor Pressure : Negligible (25 degrees C)  
First Boiling Point : Not applicable  
Volatility : Not applicable  
Solubility in Water : Insoluble  
Other : No data

## SECTION 10 STABILITY AND REACTIVITY

STABILITY: : Stable

CONDITION TO AVOID: : None

INCOMPATIBILITY(material to avoid)

: None

HAZARDOUS DECOMPOSITION OR BY-PRODUCT

: Thermal breakdown of this product during fire or very high heat condition may evolve the following hazardous decomposition product: Carbon oxides and traces of incompletely burned carbon compounds. Silicon dioxide. Formaldehyde.

HAZARDOUS POLYMERIZAT : Will not occur

CONDITION TO AVOID: : None

## SECTION 11 SUPPLEMENTAL HEALTH INFORMATION

SKIN IRRITATION : No information is available.

EYE IRRITATION : No information is available.

ACUTE TOXICITY(LD50) : Not classified\*

CHRONIC TOXICITY: : No information is available.

skin : Not classified\*

others : No information is available.

CARCINOGENICITY: : NTP:Not listed, IARC:Not listed, OSHA REGULATED:Not listed  
No information is available.

Ames Test : Negative\*

OTHER INFORMATION:

: This product can generate formaldehyde at approximately 150 degrees C(300°F) and above in the presence of air. Formaldehyde is a skin and respiratory sensitizer, eye and throat irritant, acute toxicant and potential cancer hazard. So, use adequate ventilation or wear protective equipment such as gloves, goggles or protective clothing when this product is heated at approximately 150 degrees C(300°F) and above in the presence of air.

(Note)

\* Estimation from Similar polymer

---

# MATERIAL SAFETY DATA SHEET

Product Identity

: OIL-965(Oil in FR-KIT-FC50/FR-KIT-FC50H)

No. : EOIL965W1W

Page 4 of 5

---

## SECTION 12 ECOLOGICAL INFORMATION

BIODEGRADATION: : No information is available.  
BIOACCUMULATION: : No information is available.  
AQUATIC TOXICITY: : No information is available.  
OTHER INFORMATION: : May cause decomposition in dry soils.

## SECTION 13 DISPOSAL CONSIDERATION

Can be burned in a chemical incinerator equipped with an afterburner and scrubber.  
Do not dispose the emptied container unlawfully.  
Observe all federal, state, and local laws.

## SECTION 14 TRANSPORTATION INFORMATION

UN No.: : None  
IMO CLASSIFICATION AND CLASS: None  
PACKAGING GROUP: : None  
PROPER SHIPPING NAME: : None  
TECHNICAL SHIPPING NAME: : None  
MARINE POLLUTANT: : None  
DOT REPORTABLE QUANTITY(RQ) :  
HAZARD SUBSTANCE(S) NAME / (CAS No.), CONTENTS AND RQ  
: Not applicable

## SECTION 15 REGULATORY INFORMATION

TOXIC SUBSTANCES CONTROL ACT(TSCA) STATUS:  
Listed on the TSCA Inventory.

SUPERFUND AMENDMENTS AND REAUTHORIZATION ACT OF 1986(SARA)  
TITLE III SECTION 313 SUPPLIER NOTIFICATION:

This regulation requires submission of annual reports of toxic chemical(s) that appear in section 313 of the emergency planning and community Right-To-Know Act of 1986 and 40 CFR 372.

This information must be included in all MSDS's that are copied and distributed for the material.

The toxic chemical(s) contained in this product are:

CHEMICAL NAME/(CAS No.) AND CONTENTS

\*\* None \*\*

CALIFORNIA PROPOSITION 65:

This regulation requires a warning for California Proposition 65 Chemical(s) under the statute.

The California Proposition 65 Chemical(s) contained in this product are:

CHEMICAL NAME/(CAS No.) AND CONTENTS

\*\* None \*\*

---

# MATERIAL SAFETY DATA SHEET

Product Identity

: OIL-965(Oil in FR-KIT-FC50/FR-KIT-FC50H)

No. : EOIL965W1W

Page 5 of 5

---

\*\*\*\*\*

## EUROPEAN INVENTORY OF EXISTING COMMERCIAL CHEMICAL SUBSTANCES

EINECS : Listed on the EINECS.

## LABELING ACCORDING TO EC-REGULATIONS REQUIRED:

SYMBOL : Not required

R-PHRASE : Not required

S-PHRASE : Not required

CONTAINS : None

\*\*\*\*\*

## SECTION 16 OTHER INFORMATION

This materials safety data sheet is offered solely for your information, consideration and investigation.

The data described in this MSDS consist of data on literature, our acquisitional data and analogical inference by data of similar chemical substance or product.

Shin-Etsu Chemical Co., Ltd. provides no warranties, either express or implied, and assumes no responsibility for the accuracy or completeness of the data contained herein.

---