

- > Up to 50 PPM
- > Color MFP
- > Med/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP



A new standard has officially been set.

Multiple functions, innumerable benefits and millions of colors have never been more accessible. The e-STUDIO5055c series is easily integrated, customizable and solutions ready, with an open platform. You'll also appreciate cloud and mobile printing and scanning along with a host of other benefits.

Easy integration

Includes flexible customization, new EFMS device management and system software upgraded by patch, cloning and F/W updates.



Open platform

Take advantage of flexible integration into solution applications, output management interface, and an embedded Web browser that can be registered in a template.



Cloud, internet, and mobile printing/scanning

Enjoy mobile convenience with e-BRIDGE support for new cloud computing and mobile applications as well as Internet browsing and printing from the Internet.



Universal print driver

One driver works for all users, tandem print comes standard, and additional optional plug-ins can be put directly into the driver.



Impressive image quality

Low temperature color toner increases range of colors. Other benefits include high gloss output, e-BRIDGE Color Profiler and spot-on color matching.



AquaAce specialty paper support

Achieve brilliant color that's water, weather and fade resistant. It's like laminated paper without the lamination, in legal and letter sizes. Banner printing can be done using paper up to 12" x 47".



Compact and lightweight

It has one of the smallest footprints of any comparable MFP. It's 37% lighter than before and substantially quieter.



Low power consumption

New energy saving technologies have been incorporated, resulting in reduced power consumption.



Improved serviceability

The replacement of process units is easier and can be performed without a screwdriver. Automatic detection and initialization of a new unit has been added.



High security

A unique Self Encrypting Drive (SED) includes Toshiba's proprietary Wipe Technology along with a suite of security functions that create a level of data protection that's unequalled.



There's more to Toshiba color than ever before.

Now you can copy, print, scan and fax with an MFP that's smaller, quieter, sleeker, and faster than ever. The new e-STUDIO5055c series from Toshiba is designed to replace black and white printing with affordable full color, while still offering high quality black and white.

Color options to match your needs.

For all those times you want to print in color but settle for black and white, there's the e-STUDIO5055c series. It's designed to make color more efficient and accessible. Whether you want to spruce up a presentation with color produced at a remarkable 45/50 pages per minute or print crisp, clear black and white, you'll be impressed with all that the e-STUDIO5055c series has to offer. Unique features like the e-BRIDGE Universal Print Driver, the only driver needed for multiple users, allowing you to switch between PS and PCL. It includes plug-ins so you can add features.

More compact with more impact.

Even though it's chock-full of extraordinary features, the e-STUDIO5055c series has one of the smallest footprints of any MFP in its class. So, it can be used wherever space is limited. It's lighter, too, which makes it easier to ship and move around the

office. Even the noise level has been reduced, with a quieter drive motor, fan motor and clutch. And none of these efficiencies affect the output. In fact, image quality is incredible, thanks to a new low temperature color toner that increases the color gamut.



e-STUDIO™4555c/5055c

Your data has never been more secure.

Toshiba knows that security is a high priority for businesses today. That's why we've put leading innovation to work and developed security measures that are unsurpassed.

Wipe Technology – it's like the data was never there.

It makes perfect sense. The best way to keep your data secure is to use a method no one else has replicated. That's just what we've done at Toshiba with our proprietary Wipe Technology. The e-STUDIO5055c series offers Toshiba's proprietary Self-Encrypting Drive equipped with our Wipe Technology as well as a suite of impressive security functions to keep data protected. If the HDD is taken from the MFP and installed into another device, all of the data is automatically erased. In addition,

the HDD data is quickly invalidated at the end of life so you do not have to worry about that either. There is also an encryption key that's securely stored on the HDD.

Security taken to the next level.

Additional security features include a secure PDF encryption feature with up to 128-bit AES, IP/MAC address filtering, Role Based Access Control, an SNMPv3 protocol for enhanced security administration and an optional IPsec protocol, to name a few. In all, the features permit a security mode that complies with the extremely high security level—IEEE2600.1.

- Self Encrypting Drive
- IPsec Enabler (optional)
- Common Criteria EAL 3+
- IP Filtering
- Network Port Control
- Secure PDF
- Private Print



Benefits include a 3,200-sheet capacity (including an optional 2,000-sheet LCF), direct USB printing, and tiltable display.

Manage, capture and deliver documents with simple one-touch control using the large, 9" color control panel. It's designed to be easy to read and use.

Environmentally friendly as well as user friendly.


At Toshiba, we work hard to make certain our products minimize environmental impact. Many of our leading innovations include new ways to save energy and save the environment.

Saving energy and saving you money.

An added benefit to our new energy-saving technologies is that they save you money, too. Take, for instance, our new low temperature fusing toner. Color reproduction is improved while energy consumption is reduced. Energy consumption is reduced even further, thanks to a dramatic reduction in the power usage during sleep mode. Other ways in which Toshiba puts environmental responsibility into action include a recycling program, reduction of CO₂ emissions, and the recycling of plastics. Reduction or elimination of hazardous materials such as lead and mercury enable the series to comply with environmental standards around the world. Everything together qualifies the series for the new EPEAT certification.



Print professional-looking, full-color newsletters and brochures using an optional saddle-stitch or staple finisher.



Doing more for our planet.

From our zero-waste-to-landfill toner recycling to greener manufacturing, Toshiba is a recognized environmental leader. At Toshiba we're investing in programs that help both our business and yours to better reduce, reuse and recycle.



e-STUDIO5055c with Saddle-Stitch Finisher.



e-STUDIO5055c with Paper Feed Pedestal.



e-STUDIO5055c with Large Capacity Feeder.





- > Color MFP
- > Up to 50 PPM
- > Medium/Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP

Specifications

Copying Process	Indirect Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	LED Head Printing
Copy/Print Resolution	600 x 1200 dpi (PS Driver)
Copy/Print Speed	45/45, 50/50 PPM Color/B&W
Warm-Up Time	Approx. 27 Seconds
First Copy Out Time	6.1/4.7 Seconds Color/B&W
Max Duty Cycle	200K/225K Copies
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette 1: LD to ST-R (16 lb. Bond- 140 lb. Index) Cassette 2 (and opt. KD1032, MY1039): ST-R to 12 x 18 (16 lb. Bond- 140 lb. Index) Bypass: 3.9" x 5.8" to LD (14 lb Bond - 100 lb Cover) 12" x 47" (24 lb Bond - 90 lb Index) PPF: ST-R to LD (16 lb Bond - 140 lb Index) LCF: LT (17 lb - 28 lb Bond)
Memory (Max)	Main Memory: 2 GB HD: 320 GB SED
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet "Smart" Bypass (14 lb Bond - 100 lb Cover)
Control Panel	Color 9" LCD Touch Panel
Paper Supply	Up to 3,200-Sheet Input Capacity Standard 2 x 550-Sheet Cassettes 100-Sheet Bypass 1 x 550-Sheet PPF (3rd Cassette), 1 x 550-Sheet Cassette (4th Cassette) for PPF Optional 1 x 2,000-Sheet LCF
Duplex	Standard Automatic Duplex Unit (16 lb Bond - 140 lb Index)
Dimensions	Approx. 23" x 25.3" x 31" (W x D x H)
Weight	Approx. 166.4 lbs.
CMYK Toner Yield	CMY: 28K, BK: 32K
Power Supply	120 V, 15 Amps
Power Consumption	Maximum 1.5 kW

e-BRIDGE Print Specifications

PDL Support	PCL6, PostScript 3, XPS
Operating Systems	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO
Protocol Support	Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/ iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP
Drivers	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB
Wireless Device	AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)
Device Management	Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software)
Certification	Windows 7, 8, 8.1, 2008R2, 2012, 2012 R2, WHQL, Novell, Citrix

Scan Specifications

Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	73 SPM Color/73 SPM B&W (@ 300 dpi)
File Format	TIFF, PDF, Secure PDF, JPEG, XPS (with HDD)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH / MR / MMR / JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations /Job
Scan Speed	.7 Seconds Per Page, Maximum 73 SPM

E-Filing Specifications

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

Security (Standard)

Data Encryption	256 Bit AES (SED Hard Drive)
Authentication	LDAP, SMTP, Windows Server Domain, Local

Accessories (Options)

Additional Paper Options

Platen:	KA1640PC
RADF: 100 Sheets	MR3025
Paper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger	KD1032N
Cassette Module :550-Sheet Pedestal, Statement-R to Ledger	MY1039
Large Capacity Feeder (LCF): 2,000-Sheet Drawer, Letter	KD1031

Finishing Options

Saddle-Stitch Finisher:	MJ1108
Tray 1 Stack Capacity: 3,000 Sheets + 250 Sheet Stationary Tray (Lt)	
Staple Capacity: 50 Sheets	
60 Pages (15 Sheets) SS Booklets	
Multi-Position Hole Punch Unit for Saddle-Stitch Finisher	MJ6104
Multi-Position Console Finisher:	MJ1107
Tray 1 Stack Capacity: 2,000 Sheets (Lt)	
Staple Capacity: 50 Sheets	
Multi-Position Hole Punch Unit for Console Finisher	MJ6104
Inner Finisher	MJ1036N
2 Tray: 500 Sheets (LT)	
Staple Capacity: 50 Sheets	
Multi-Position Hole Punch Unit for Inner Finisher	MJ6007

Connectivity/Security Options

Bridge Kit Required with MJ1108 and MJ1107	KN2550
Fax Board	GD1320NX
2nd Line Fax	GD1260F
Wireless LAN Adapter	GN1060
Wireless Antenna	GN3010
Meta Scan Enabler for e-CONNECT	GS1010
IP Sec Enabler	GP1080
Advanced Scanning (ReRite)	GB1280V8
SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540

Miscellaneous Options

Accessible Arm Handle	KK2550
-----------------------	--------



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and Specifications subject to change without notice. For best results and reliable performance, always use supplies manufacturer or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.