TOSHIBA

STUDIO[®] 5508A STUDIO[®] 6508A STUDIO[®] 7508A STUDIO[®] 8508A

- > Black & White Multifunction Printer
- > Up to 85 PPM
- > Large Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > Solutions Ready



CONNECT. INTEGRATE. SIMPLIFY.

Technology for every office, delivering advanced functionality, ease of use and peace of mind.

Every industry has unique workflow needs. Toshiba has developed customizable MFPs to make your job easier. Intuitive and smartly integrated, our products simplify complex tasks and give you control while providing the reliability Toshiba is known for.

Toshiba's latest series delivers on our promise of Together Information – our commitment to collaborate with clients in order to provide tailored, cost-effective solutions that meet your print, document management and content needs while helping you meet your green objectives.

- > Speeds of 55, 65, 75 and 85 PPM black & white
- > Outstanding image guality and extra-high volume
- Advanced e-BRIDGE Next technology
- Fast dual-core processor

Faster, sleeker, and more volume than ever.

Toshiba is now introducing a sleek new lineup that looks great inside and out. Along with an ultra-modern look, you'll also find innovative technology like crisp, clean monochrome output delivered at up to 85 pages per minute with an impressive 6,020-sheet maximum capacity.

- Precise 2,400 dpi x 600 dpi with smoothing for text
- > Up to 3,600 dpi x 1,200 dpi in PostScript mode
- New high-speed, high-capacity Dual-Scan Document Feeder
- > Up to 720K maximum monthly copy volume



FEATURES AND BENEFITS AND MORE OF THEM.

With the Toshiba e-STUDIO8508A series, you can improve workgroup connection, integrate and simplify while improving efficiency with ultra-high quality output at unprecedented volumes.

Higher Robust Speeds include 55/65/75/85 monochrome pages per minute.

Fast Dual-Scan Document Feeder handles up to 300 sheets at a time and seamlessly scans both sides of each page in a single pass to produce a full 240 images per minute (IPM).

Fast First Copy Out Times at 5.2/5.2/4.5/4.1 seconds respectively.

9" Tablet-Style Touch Screen works intuitively, helping you access instructions, functions, and commands with the swipe of the finger.

Print Around eliminates printing bottlenecks by allowing other print jobs to go around one job that's held-up due to requiring a specific paper size or type.

Limitless Job Reservation will queue up multiple copy or print jobs so users can send jobs whenever.

Saddle/Fold Capabilities offer saddle-stitch finishing and the option to fold without stapling.

Scan-to and Print-from USB lets you print straight from your USB drive or scan documents to it.

Advanced e-BRIDGE Next Technology enables the MFP to drive Toshiba's internally developed embedded solutions or those from a third party with ease.

Notifications Feature takes the hassle out of checking for depleted supplies or maintenance needs.

Paper Volume Indicators on the front panel make it easy to see the paper sizes, types and levels in each cassette.

Help Button provides instant, thorough explanations straight from the manual to help as needed.









TOSHIBA

HOW TOSHIBA IS RAISING THE STANDARD.

When it comes to seamless workflow and simplified integration, the e-STUDIO8508A series represents the finest Toshiba has to offer. The latest e-BRIDGE Next technology enables complete third-party integration and support for internally driven solutions. A universal driver along with PCL 6, PS3, and XPS support provide fast and easy connectivity to Windows[®], Macintosh[®] and more.

AirPrint and Mopria[™] support means mobile users can print to the MFP with ease. The e-BRIDGE Print & Capture application provides additional capabilities including the ability to scan from the MFP back to your mobile device. Also, a Dual-Line Fax option can handle heavy fax volumes with ease.

Cloud Support

New Scan-to-Cloud and Cloud Print capabilities increase productivity by allowing users to access, store and print documents remotely from the MFP. Whether it's Dropbox, OneDrive or Google Drive, the new e-STUDIO8508A series makes scanning to these cloud-based locations a breeze, while embedded support for Google Cloud Print enables easy printing to the MFP from anywhere you may be.

Advanced Security

Even more important than functionality is the security offered by the e-STUDIO8508A series. Such technological advancements include:

- > A 320GB Self-Encrypting Drive (SED) with Automatic Drive Invalidation (ADI) & Data Overwrite capability provides top level security
- FIPS 140-2 Validated SED meets and exceeds government requirements
- IPsec is available to securely encrypt data sent to and from the MFP

Environmental Responsibility

Because we have been working to protect the environment as well as your security, you can rest assured Toshiba has what it takes to protect both.

- RoHS compliance, the use of recycled plastics, and Low-Power (0.6W) Super Sleep Mode work to help the environment
- EPEAT Gold Registered in the global registry for greener electronics, designed to help purchasers choose products that reduce environmental impact
- Energy Star V2.0 meets the latest, more stringent requirements



PROOF WE'RE CONSTANTLY REACHING HIGHER.

1 Accessory Tray & Keyboard Options

GR1250 – Accessory Tray GR9000 – Bluetooth Keyboard GR1260 – 10-Key Numeric Keypad

2 Finishing Options

MJ1111 – 50-Sheet Console Finisher MJ1112 – 50-Sheet Saddle Stitch Finisher MJ6106 – Hole Punch Unit KA6551 – Side Exit Tray

3 Connectivity Options

GD1370 – Fax Unit/2nd Line for Fax Unit GN4020 – Wireless LAN/Bluetooth Module

4 Additional Paper Options MP2502 – 2,500 Sheet Large Capacity Feeder

Additional Option Highlights

- > IPsec Security Enabler
- > Multi-Station Print Enabler
- > Embedded OCR Enabler



The Toshiba e-STUDIO8508A series tops all previous machines and helps large workgroups improve productivity and connectivity while simplifying the overall workflow.

Double the Scan Speed

A 300-sheet high-speed, high-capacity Dual-Scan Document Feeder (DSDF) produces up to 120 IPM simplex and 240 IPM duplex.

Bluetooth/WiFi Option

Bluetooth feature provides support for a wireless keyboard to simplify workflow processes at the MFP, while the WiFi capability enables WiFi-Direct printing making it ideal for mobile users

Volumes and Volumes

A high monthly copy volume is 520K/590K/660K/720K respectively. Impressive toner yields are 106,600 at 5% coverage.

Multi-Station Print Enabler

Toshiba's internally developed Multi-Station Print Enabler allows users to send print jobs from their desktop and retrieve them at any convenient MFP by simply swiping their badge and authenticating at that device.

Advanced e-BRIDGE Next Technology

Built on Linux®, this latest generation e-BRIDGE Next architecture features an Embedded Web Browser, an Intel Atom[™] dual-core processor, 4GB RAM and a 320GB FIPS 140-2 Validated SED enabling the MFP to easily drive Toshiba's internally developed solutions or even third-party applications.

C-studio"5508a/6508a/7508a/8508a

Main Specifications

Copy System	Indirect Electrostatic Photographic Method/OPC/Laser Printing/ Heat Roller Fusing		
Display	9" Color WVGA Touch Screen Tilting Display		
Copy Speed	55/65/75/85 PPM (LT)		
First Copy Out	5.2/5.2/4.5/4.1		
Warm-Up Time	Approx. 24/24/20/20 Seconds		
Copy Resolution	600 x 600 dpi		
Stack Feed Bypass	3.9" x 5.8" to 13" x 19", 12" x 47" Banner, Envelope		
Multiple Copying	Up to 9,999 Copies		
Paper Capacity	Standard 3,520 Sheets/Max. 6,020 Sheets (Tandem Drawer)		
Original Feed	Standard 300-Sheet DSDF		
	DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color),		
ocan opeed a weights	Simplex: 9.3-110 lb Index, Duplex: 9.3-110 lb Index		
Max. Original Size			
Paper Feed Sizes	Drawers: 540 Sheets-ST-B to 12" x 18"		
	Integral Tandem LCF 1,160 x 2 LT-Only		
	Stack Feed Bypass: 120 Sheets-3.9" x 5.8" to 13" x 19", 12" x 47" Banner		
	2.500-Sheet Ext. LCF LT-Only		
Paper Weights	Tandem LCF 1.160 Sheets x 2-16 lb Bond-140 lb Index		
i apoi froigino	Plus 540 Sheets x 2-16 lb Bond-140 lb Index		
	Stack Feed Bypass: 120 Sheets-16 lb Bond-110 lb Cover		
	Opt. 2.500-Sheet Ext. LCF LT-Only -16 lb Bond-140 lb Index		
Duplex	Standard Automatic Duplex Unit (16 lb Bond-140 lb Index)		
Reproduction Ratio	25% to 400%		
Max Duty Cycle	Max. 520K/590K/660K/720K Month		
Weight	Approx.430 lb		
Approx. Dimensions	37.6" (W) x 28.9" (D) x 48.3" (H)		
Toner Yield	106.600 @ 5%		
Power Source	120 Volts, 50/60 Hz, 16 Amps		
Power Consumption	Maximum 2.0kW (120V)		
CPU	Intel Atom [™] 1.33 GHz (Dual-Core)		
Memory	4GB		
Hard Disk Drive	320GB Self-Encrypting Drive FIPS 140-2 Validated		
	SEGRE CON ENCLOSING DIVOTILIO THO E Validadou		

e-BRIDGE Next Print Specifications

PDL Print Speed Print Resolution	PCL5e, PCL5c, PCL6 (PCL XL), PS3, PDF, XPS, JPEG 55/65/75/85 PPM (LT) 600 x 600 dpi, 2,400 x 600 dpi (With Smoothing), 1,200 x 1,200 dpi (2-bit) or 3,600 x 1,200 dpi (With Smoothing) PS Only
Operating Systems	Windows® Vista, Windows Server® 2008/R2, Windows® 7, 8, 8.1, 10, Windows Server® 2012/R2, Macintosh® (Mac OS X 10.6, 10.7, 10.8, 10.9, 10.10, 10.11), Unix®, Linux®
Network Protocols	TCP/IP (IPv4, IPv6), NetBIOS over TCP/IP, IPX/SPX® for Novell® Environments, EtherTalk® for Macintosh Environments
Printing Protocols	SMB, LPR/LPD, IPP (Ver.1.1) w/Authentication, AppleTalk PAP or EtherTalk [™] , Port 9100 (bi-directional), NetWare P-SERVER LPD w/ iPrint, WS Print, FTP
Print Drivers	Windows® Vista SP2 (32-bit, 64-bit), Windows Server® 2008 SP2 (32-bit, 64- bit), Windows Server® 2008 R2 SP1 (64-bit), Windows® 7 SP1 (32-bit, 64-bit), Windows® (84.1 (32-bit, 64-bit), Windows Server® 2012/R2 (64-bit), Windows® 10 (32-bit, 64-bit), Mac OS® X 10.6.8, 10.7.4, 10.8, 10.9, 10.10, 10.11
Interface	RJ-45 Ethernet (10/100/1000 Base-T), USB 2.0 (High-speed) Optional 802.11b/g/n, Wireless LAN, Optional Bluetooth
Wireless Device	AirPrint [™] , Mopria [®] , e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)
Device Management Account Control	TopAccess, EFMS 6.2 (e-BRIDGE Fleet Management Software) Up to 10,000 users or 1,000 Departments Supports User Authentication (on Device), Login Name/Password (via Windows domain) or Login Name/ Password (via LDAP Server) for Copy, Print, Scan, Fax, List, and User Function
Accessibility Features	: Tilt Front Panel, Job Programs, Universal Grip for Paper Trays, Disable Screen Timeout and Audible Beep Message Alerts



Designs and specifications subject to change without notice. Specifications may vary by conditions of use and/or environmental usage. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/ network operating system. Product names may be trademarks of their respective companies. AirPrint and the AirPrint logo are trademarks of Apple Inc. This is a Class 1 laser product complying with IEC60825-1.

© 2017 Toshiba America Business Solutions, Inc. Electronic Imaging Division Inv. Code 22308 5508A/6508A/75086A/8508A Brochure 5K PG 7/17

Security Features	User Authentication, On-Board Data Scramble Function, SCEP, Disable e-Filing, Disable Copy, Disk Overwrite, IP Address Filtering (10 Sets), MAC Address Filtering (10 Sets), Network Service Control, Network Port Control, SMB Packet Signing, SSL (HTTP, IPP, LDAP, SMTP, POP, FTP, DPWS), IPsec (IKEv1, IKEv2), Security Mode Change, CC Certified (ISO/IEC15408 EAL3+)*, IEEE2600.1, IEEE802.1X, Digital Signature for Client Utilities, Password Policy, Password Lock, Password Expiration, Self Testing, Job Access Control, Log Access Control for Job Log, Security Stamp "Compliant with IEEE2600.1 in High Security Mode.
Environmental Stds.	Energy Star (V2.0), EPEAT Gold, RoHS
Certification	WHQL (Windows 7, 8, 8.1, 10, 2008 R2, 2012, 2012 R2), Novell, Citrix, SAP

Scan Specifications

Scan Speed Scan Modes Scan Resolution File Formats	DSDF Scan: Up to 240 IPM Duplex, 120 IPM Simplex (Monochrome or Color) Standard: Full Color, Auto Color, Monochrome, Grayscale 600 dpi, 400 dpi, 300 dpi, 150 dpi, 150 dpi Monochrome: TIFF-Multi/Single Page, PDF-Multi/Single Page, Searchable PDF (Opt), XPS-Multi/Single Page, DOCX (Opt), XLSX Color/Grayscale: JPEG, TIFF-Multi/Single Page, DDF Xlopt), PDF, Searchable PDF (Opt), XPS-Multi/Single Page, DOCX (Opt), XLSX
Image Compression	PDF, Searchable PDF (Opt.), XPS-Multi/Single Page, DOCX (Opt.), XLSX (Opt.), PPTX (Opt.) Color/Grayscale: JPEG (High, Middle, Low)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	Up to 33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job
Scan Speed	0.7 Seconds Per Page, Maximum 73 IPM

e-Filing Specifications

Operation Method Color Touch Screen Control Panel or Client PC Number of Boxes 1 Public Box, 200 Private User Boxes Capacity of Boxes 100 Folders Per Box, 400 Documents Per Folder/Box, 200 Pages Per Document

GR1290 GS1010

GP1080

Accessories (Options)

Additional Paper Options Large Capacity Feeder MP250 **Finishing Options** 50-Sheet Staple Finisher MJ111 Saddle-Stitch Finisher MJ1112 MJ610

Hole Punch Unit for MJ1111/MJ1112 Side Exit Tray Finisher Guide Rail

Connectivity/Security Options

FAX Unit/2nd Line for FAX Unit Wireless LAN/Bluetooth Bluetooth Keyboard Accessory Tray Panel 10-Key Option Card Reader Holder Meta Scan Enabler IPsec Enabler

s)		
	Unicode Font Enabler	GS1007
MP2502	Embedded OCR Enabler Single License	GS1080
MJ1111	Five Licenses Multi-Station Print Enabler	GS1085
MJ1112 MJ6106	Single License	GS1090
KA6551	Five Licenses	GS1095
KN1103	Advanced Scanning (ReRite)	GB1280V8
KINI 103	SharePoint Connector	GB1440
	Exchange Connector	GB1450
GD1370	Google Drive Connector	GB1540
GN4020 GR9000 GR1250 GR1260	Miscellaneous Options Accessible Arm Harness Kit for Coin Controller	KK2560 GQ1280
2		