

# Small Footprint. Big Impact.

*Professional copy, print, and scan in one efficient design.*



**e-STUDIO™ 166**



16



Workgroup



Black & White



Copy/Print/Scan

**TOSHIBA**  
Don't copy. Lead.

# e-STUDIO™ 166

## SPECIFICATIONS

### SPECIAL FEATURES

- Interrupt
- Energy Saver
- APS/AMS (with Optional ADF)
- Auto Job Start
- Auto Cassette Change
- Auto Sleep Mode
- Manual Exposure Control
- Zoom Ratio 25% – 200%
- Coin Controller (Harness Option Required)
- eSort (with Optional 64 MB Memory and ADF)
- Scan Once/Print Many
- Access Code - 99 Codes



**16**  
PAGES PER MINUTE

**3 in 1**  
COPY, PRINT, SCAN

**Compact**  
DESIGN

### SPECIFICATIONS

<b>Copying Technology</b>	Digital Copier
<b>Type</b>	Desktop
<b>Copying Resolution</b>	2,400 x 600 dpi (with Smoothing)
<b>Scanning Resolution</b>	600 dpi
<b>Printing Resolution</b>	600 x 600 dpi
<b>Copying Speed (LT/LG/LD)</b>	16/13/11 PPM
<b>Maximum Monthly Volume</b>	50,000 Impressions
<b>First Copy Out Time</b>	7.6 Seconds
<b>Warm-Up Time</b>	25 Seconds
<b>Multiple Copying</b>	Up to 999 Copies
<b>Paper Supply</b>	Standard 250-Sheet Cassette Standard 100-Sheet Bypass Tray Optional 250-Sheet Cassette
<b>Acceptable Paper Size</b>	Cassette 1/2: LT – LD (17-20 lbs. Bond) Bypass Tray: ST-R – LD (17-90 lbs. Index)
<b>Reduction/Enlargement</b>	25% – 200%
<b>Image Density Control</b>	Text/Text – Photo/Photo
<b>Dimensions</b>	23.62" x 25.31" x 18.21" (W x D x H)
<b>Weight</b>	70.1 lbs.
<b>PM Cycle</b>	72,000 Impressions
<b>Drum Yield</b>	72,000 Impressions
<b>Developer Yield</b>	72,000 Impressions
<b>Toner Type</b>	Cartridge
<b>Toner Yield</b>	24,000 Impressions (100% Recyclable)
<b>Power Supply</b>	115 Volts/12 Amps

### PRINT / SCAN FEATURES

<b>Standard Printing</b>	Windows GDI Printing
<b>Max Print Speed</b>	16 PPM
<b>Standard Scanning</b>	TWAIN Scanning
<b>Software</b>	Toshiba Viewer
<b>Interface</b>	USB 2.0
<b>Operating System Support</b>	Windows 98, 2000, Me, XP, Server 2003, (only 32 bit)

### CONFORMANCE TO STANDARD

<b>Environmental</b>	Energy Star Compliant
<b>Safety Standard</b>	UL, CSA, CDRH
<b>Emission/Immunity</b>	FCC (IC/Part 15 Class A)

### OPTIONAL FEATURES

Part Number	Description
KA1640PC	Platen Cover
MR2017	100-Sheet Automatic Document Feeder (ST-R – LD/17-33.8 lbs. Bond)
MY1027	250-Sheet Cassette (LT-LD/17-20 lbs. Bond)
GC1240	64 MB Memory for eSort
GQ1130	Coin Controller Harness

**Corporate Office:** 2 Musick, Irvine, California 92618-1631

**East Coast:** 959 Route 46 East, 5th Floor, Parsippany, New Jersey 07054  
Tel: 973/316-2700 Fax: 973/263-2393

**Midwest:** 8770 W. Bryn Mawr Avenue, Suite 700, Chicago, Illinois 60631  
Tel: 773/380-6000 Fax: 773/380-8077

**South:** 4855 Peachtree Industrial Blvd., Suite 210, Norcross, Georgia 30092-3024  
Tel: 770/209-8540 Fax: 770/209-8556

**West Coast:** 142 Technology, Suite 150, Irvine, California 92618  
Tel: 949/462-6262 Fax: 949/462-2700

**Web Site:** [www.copiers.toshiba.com](http://www.copiers.toshiba.com) or [www.fax.toshiba.com](http://www.fax.toshiba.com)



Designs and specifications subject to change without notice. Actual specifications based on engine design and may vary according to usage and environment. For best results and reliable performance always use supplies manufactured or designated by Toshiba. Toner yields are estimates, based on 5% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability.

AUTHORIZED TOSHIBA DEALER

**TOSHIBA**  
Leading Innovation >>>