

- > Up to 25 PPM
- > Color MFP
- > Small/Med. Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered



The color MFP you didn't know you could afford.

Many small businesses and home offices have been limited to color printers' basic features, until now. That's because Toshiba technology, performance and quality are available as entry-level MFPs. Introducing the e-STUDIO2550c series, only from Toshiba. We've taken "entry-level" to a whole new level.

Think economy, print luxury.

As companies continue to look for new ways to cut costs while maintaining or improving performance, Toshiba offers the ideal solution. The e-STUDIO2550c series makes workgroup caliber MFPs available for use by small businesses. You can copy, print, scan and fax while utilizing advanced Toshiba technology and enjoying features and benefits included in MFPs designed for much larger workgroups. In fact, the e-STUDIO2550c series includes the newest e-BRIDGE controller with a user interface that makes it easy to navigate through even the most complex jobs.

Standard, optional and extraordinary.

The e-STUDIO2550c series balances functions and price so that it's adaptable to a variety of budgets and needs. A standard model can become a robust, full-featured color MFP, or anything in between.

You have your choice of 20 or 25 pages per minute at up to 600 x 1200 dpi. A large 9" control panel makes it easier than ever to program complex jobs. An Automatic Duplexing Unit lets you print on both sides and a variety of finishing options like multi-position stapling, hole-punch and even saddle stitch booklet making enable you to create documents that are polished and professional looking.

With the latest generation e-BRIDGE platform, it's easy to connect and manage your fleet. And, if you're looking for more than copy, print and scan, opt for a fax feature and even a second line. Additionally, the External Interface Enabler allows for seamless integration of a variety of popular workflow solutions. Even with numerous capabilities, the e-STUDIO2550c series is compact, lightweight and quiet, making it ideal in small spaces or large rooms.



So many functions have never been so accessible.

An MFP might seem like more than you ever thought you'd need. Just wait until you've used the e-STUDIO2550c and you'll wonder how you ever got along without it. Beginning with the All-in-One, network ready architecture for color copying, printing and scanning, Toshiba style.

Universal appeal.

The e-STUDIO2550c series has a new Universal Printer Driver that helps produce the same look and functionality whether you're using PostScript, PCL6 or even Microsoft XPS. This Universal Driver is supported by Toshiba's entire e-BRIDGE-driven MFP lineup from 20-85 PPM color and monochrome, allowing administrators to use a single driver across the entire fleet.

Toshiba also offers additional low-cost driver plug-ins so you can add whatever functionality you might need. For instance, the Job Point plug-in lets users split large print jobs over as many as 10 Toshiba MFPs, while the Job Replicator simplifies the process of printing multi-part forms. Job Build allows users to print different document types such as Word, PDF, Excel and others together as a set, while Job Separator enables users to create multiple sets of a job and divide each set with a separately printed divider page. With the e-STUDIO2550c series, if you need a new feature, you can simply plug it in.

Multiple functions with a single touch.

Walk up to the e-STUDIO2550c and you'll immediately notice how easy it is to use. Adjust the large, tilttable 9" VGA color control panel to avoid glare and increase visibility. It utilizes large, easy to read text and a dynamic, interactive copier diagram that clearly illustrates paper configurations and copier status. Use the simple, one-touch access keys for whatever MFP function you want—copy, print, scan, fax or e-Filing. It's that simple, and that versatile.

- > Easy Replaceable Units
- > Easy Manageability
- > Network Print/Scan
- > Remote Management
- > Gigabit Connectivity
- > Template Feature Keys



Security features designed to meet your strict standards.

Businesses of all sizes are concerned about security these days. That's why Toshiba packed the e-STUDIO2550c series with heavy-duty, high-security features. These advanced features can be accessed through easy-to-use controls and simple operations so you don't have to be a security expert in order to put them into action.

- > Self Encrypting Drive
- > IPsec Enabler (optional)
- > Common Criteria EAL 3+
- > IP Filtering
- > Network Port Control
- > Secure PDF
- > Private Print



Not only can you perform multiple functions with ease, everything you do is protected with the most advanced security measures available.

Exceeding the highest security standards is standard.

Toshiba's e-STUDIO2550c series incorporates the most stringent security requirements of the IEEE2600 standards for multifunction products. Our proprietary 320GB Self-Encrypting-Drive (SED) is now standard and features Automatic Data Invalidation to help prevent the retrieval of data from the drive if it is removed and placed in another device. This exclusive Toshiba design utilizes the 256 Advanced Encryption Standard (AES) and is FIPS 140-2 validated, while the optional Data Overwrite Kit meets Department of

Defense requirements. Even data being sent to or from the e-STUDIO2550c series can be encrypted with an optional IPsec Enabler.

Other security features include full device authentication with Role Based Access Control that allows administrators to restrict user access to specific functions. This can be tied in with secure access ID cards, such as building access cards, to further strengthen the authentication process. For even more security, IP and MAC address filtering enables you to control electronic access to print and scan functions.

secureMFP™

Security provides peace of mind.

Other MFP features help you make sure you only share the information you want to share. A Secure PDF feature lets users scan and email documents at the MFP using a password so only those recipients who know the password can access or print the document.

Whatever your security concerns, the Toshiba e-STUDIO2550c series has what it takes to help you rest assured your data will stay protected.

Exceptional performance that's exceptionally green.

While using advanced technology to achieve exceptional performance, Toshiba has continued to develop and implement many of the world's leading solutions for conserving energy and protecting the environment. We've dispelled the myth that environmental safety has to come at the cost of performance. There are ways to enhance both at the same time.

Where quality and productivity go hand in hand.

Some of the greatest advantages of the e-STUDIO2550c series, besides the multiple functions themselves, include the decrease in downtime and increase in productivity. Now you can perform high-volume print jobs in much less time. The downtime is reduced, thanks to easily replaceable units (ERUs) that eliminate the need for extensive

maintenance. Instead of overhauling the entire machine, certain features can be restored with the replacement of a single component. The use of tandem printing with another e-STUDIO on the network reduces print time. And if a job is temporarily halted, job skip allows others to print around it.



e-STUDIO2550c with
Saddle-Stitch Finisher.



e-STUDIO2550c
with Inner Finisher.



e-STUDIO2050c with
Paper Feed Pedestal.




e-STUDIO2050c
Base Model



The advanced technology of environmental responsibility.

Long before it became a trend, Toshiba started developing ways to reduce the environmental impact. The e-STUDIO MFPs are a result of that. The e-STUDIO2550c series is RoHS Compliant, EPEAT Registered (as part of the definitive global registry for greener electronics), and Energy Star Tier 2 rated. Rest assured that the small, compact e-STUDIO2550c has a small carbon footprint, too.



From duplex printing to easily replaceable units to tandem printing, the e-STUDIO2550c series is designed with the environment in mind.



- > Color MFP
- > Up to 25 PPM
- > Small/Medium Workgroup
- > Copy, Print, Scan, Fax
- > Secure MFP
- > EPEAT Registered

Specifications

Copying Process	Indirect Electrostatic Photographic Transfer System with Internal Transfer Belt
Copying Type	LED Head Printing
Copy/Print Resolution	600 x 600 dpi/600 x 600 dpi, (600 x 1200 dpi, PS only)
Copy/Print Speed	e-STUDIO2050C~20 PPM Color/B&W e-STUDIO2550C~25 PPM Color/B&W
Warm-Up Time	Approx. 35 Seconds
First Copy Out Time	e-STUDIO2050C~10.3 Seconds Color/8.2 Seconds B&W e-STUDIO2550C~10.3 Seconds Color/8.2 Seconds B&W
Duty Cycle	56K/70K/Copies
Multiple Copying	Up to 999 Copies
Acceptable Paper Size and Weight	Cassette: ST-R to LD (16lb Bond - 90lb Index) Bypass: 3.9" x 5.2" to LD (16lb Bond - 110lb Index) PFP: ST-R to LD (16lb Bond - 90lb Index) LCF: LT (17lb - 28lb Bond), Envelope (Bypass Only)
Memory (Max)	Main Memory: 2GB, SSD: 8GB 320GB FIPS 140-2 SED
Reduction/Enlargement	25% to 400%
Bypass	100-Sheet "Smart" Bypass (16lb Bond - 110lb Index)
Control Panel	Color 9" LCD Touch Panel
Paper Supply	Up to 2,900-Sheet Input Capacity Standard 250-Sheet Cassettes, 100-Sheet Bypass Optional 1 x 550-Sheet PFU (2nd Cassette) 1 x 550-Sheet PFP (3rd Cassette) 1 x 550-Sheet Cassette (4th Cassette) for PFP Optional 1 x 2,000-Sheet LCF
Duplex	Standard Automatic Duplex Unit (16lb Bond - 90lb Index)
Dimensions	Approx. 22.6" x 23.2" x 26.1" (W x D x H)
Weight	Approx. 125.7lb
CMYK Toner Yield	6% Coverage, CMY: 28K, BK: 32K
Power Supply	120 V, 12 Amps
Power Consumption	Maximum 1.5 kW

e-BRIDGE Print Specifications

PDL Support	PCL6, PostScript 3, XPS
Operating Systems	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, NetWare 6.5, Citrix, Macintosh 10.4-10.9, Solaris v10, 11, HP-UX V11.iv3, AIX 7.x, Linux, SCO
Protocol Support	Windows Printing (SMB1.0/2.0), LPR/LPD, IPP (Ver.1.1) w/Authentication, NetWare P-SERVER w/NDS, Binary, Novell NDPS Gateway, or LPD w/iPrint, Apple Talk PAP or EtherTalk, Port 9100 (bi-directional), WS Print, FTP
Drivers	Windows Server 2003, 2008, 2012, Vista SP2, 7, 8, Macintosh OS 10.4-10.9
Connectivity	10/100/1000BaseTX Ethernet, 802.11b/g/n, Wireless LAN, USB
Wireless Device	AirPrint, e-BRIDGE Print & Capture Application on iOS and Android (Available via Apple App Store or Google Play)
Device Management	Top Access, eFMS 6.0 (e-BRIDGE Fleet Management Software)
Certification	Windows 7, 8, 8.1, 2008R2, 2012, 2012 R2, WHQL, Novell, Citrix

Scan Specifications

Scan Resolution	100 dpi, 150 dpi, 200 dpi, 300 dpi, 400 dpi, 600 dpi
Scan Speed	50 SPM Color/50 SPM B&W (@ 300 dpi)
File Format	TIFF, PDF, Secure PDF, JPEG, (XPS with HDD)

Facsimile Specifications

Compatibility	Super G3
Data Compression	MH/MR/MMR/JBIG
Transmission Speed	Approx. 3 Seconds Per Page
Fax Modem Speed	33.6 Kbps
Memory Transmission	100 Jobs (with HDD), 2,000 Destinations Max. 400 Destinations/Job
Scan Speed	.7 Seconds Per Page, Maximum 50 SPM

e-Filing Specifications (with HDD)

Operation Method	Color Touch Screen Control Panel or Client PC
Number of Boxes	1 Public Box, 200 Private User Boxes
Capacity of Boxes	100 Folders Per Box, 400 Documents Per Folder, 200 Pages Per Document

Security

Data Encryption	256 Bit AES
Authentication	LDAP, SMTP, Windows Server Domain, Local

Accessories (Options)

Additional Paper Options

Platen Cover	KA1640PC
RADF: 100 Sheets	MR3024
Paper Feed Unit: 550-Sheet Pedestal, Statement-R to Ledger	MY1040
Paper Feed Pedestal: 550-Sheet Pedestal, Statement-R to Ledger	KD1032
Paper Drawer: 550-Sheet Pedestal, Statement-R to Ledger	MY1039
Large Capacity Feeder (LCF): 2,000-Sheet Drawer, Letter	KD1031
Paper Feed Controller	GH1080

Finishing Options

Saddle-Stitch Finisher:	MJ1037
Tray 1 Stack Capacity: 1,000 Sheets (LT)	
Staple Capacity: 50 Sheets	
60 Pages (15 Sheets) SS Booklets	
Multi-Position Hole Punch Unit for Inner Finisher	MJ6008
Inner Finisher	MJ1036
2 Tray: 600 Sheets (LT)	
Staple Capacity: 50 Sheets	
Multi-Position Hole Punch Unit for Inner Finisher	MJ6007

Connectivity/Security Options

Bridge Kit Required with MJ1037	KN2550
Fax Board	GD1320
2nd Line Fax	GD1260F
Wireless Module	GN1060
Wireless Antenna	GN3010
External Interface Enabler	GS1020
Meta Scan Enabler for e-CONNECT	GS1010
Data Overwrite Enabler	GP1070
IPsec Enabler	GP1080
Advanced Scanning (Re-Rite)	GB1280V8
SharePoint Connector	GB1440
Exchange Connector	GB1450
Google Docs Connector	GB1540

Miscellaneous Options

Accessible Arm Handle	KK2550
Harness Kit for Coin Controller	GQ1260



Corporate Office	9740 Irvine Blvd., Irvine, CA 92618-1631 Tel: 949-462-6000
East Coast	959 Route 46 East, 5th Floor, Parsippany, NJ 07054 Tel: 973-316-2700
Midwest	8770 W. Bryn Mawr Ave., Suite 700, Chicago, IL 60631 Tel: 773-380-6000
South	2037 Bakers Mill Rd., Dacula, GA 30019 Tel: 678-546-9385
West Coast	9740 Irvine Blvd., Irvine, CA 92618 Tel: 949-462-6000
Web Site	www.business.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.