

**e-STUDIO™ 351c/451c**



**The Economy of Black and White**  
– and Color on Demand.



**TOSHIBA**  
Leading Innovation >>>

**SPECIFICATIONS**

<b>Copying/Printing Process</b>	Indirect Electrostatic Photographic Method
<b>Copy System</b>	Color Laser, Toshiba Revolver B&W/Color Printing System
<b>Original Scanning Method</b>	CCD Line Sensor (4-Lines)
<b>Copy/Print Resolution</b>	600 x 600 dpi B&W: 2,400 x 600 dpi with Smoothing Color: 1,200 x 600 dpi with Optional Expansion Memory
<b>Copy/Print Speed</b>	35/45 PPM B&W / 11 PPM Color
<b>Warm Up Time</b>	Approximately 40 Seconds
<b>First Copy Out Time</b>	B&W: 6.8 Seconds Color: 16.2 Seconds
<b>Duty Cycle</b>	150,000 Copies
<b>Multiple Copying</b>	Up to 999 Copies
<b>Paper Supply</b>	Up to 3,700 Sheet Input Capacity Standard: 2 x 550 Sheet Cassettes (17-28 lbs.) Optional: 1 x 550 Sheet PFP, 1 x 550 Sheet Cassette, 1 x 2,500 Sheet LCF
<b>Bypass</b>	Stack Feed "Smart" Bypass (100 Sheets)
<b>Acceptable Paper Size</b>	Cassette: Statement-R to Ledger (17-28 lbs.) Bypass: Statement-R to 12" x 18" (17-110 lbs.) LCF: Letter (17-28 lbs.)
<b>Duplex</b>	Standard Trayless Automatic Duplex Unit
<b>Maximum Original Size</b>	Ledger
<b>Standard Memory</b>	384 MB, 80+ GB HDD
<b>Optional Memory</b>	Up to 768 MB
<b>Color Mode</b>	Automatic Color Selection, Full Color Mode, Black Mode, Twin Color
<b>Color Image Adjustments</b>	Color Balance, RGB, Sharpness, Background, One Touch
<b>Reduction Enlargement</b>	25% - 400%
<b>Dimensions</b>	30"H x 26"W x 29"D
<b>Weight</b>	247 lbs.
<b>PM Cycle</b>	120,000 / 150,000
<b>Toner Control Method</b>	Automatically Controlled, Toner Empty Detection
<b>Drum Type</b>	Organic Photoconductor
<b>Black Toner Yield</b>	27,000
<b>Color Toner Yield</b>	10,000 Per Color (C,M,Y)
<b>Power Supply</b>	115V, 15 Amps
<b>Power Consumption</b>	Maximum 1.5 kW

**PRINT**

<b>PDL Support</b>	PCL5c, PCL6, PostScript 3
<b>Operating Systems</b>	Netware 4.x, 5.x, 6.x, Windows Me/2000/XP, Windows NT4.0, Windows Server 2003, VISTA, Citrix MetaFrame, Macintosh, Linux, UNIX
<b>Protocol Support</b>	IPX/SPX, TCP/IP, EtherTalk, AppleTalk, NetBIOS Over TCP/IP LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
<b>Drivers</b>	Windows Me, 2000, Server 2003, XP, NT4.0, Macintosh OS 8.6, 9.x, 10.1/10.2/10.3 (with PPD), UNIX, AS400 via iData and Port 9100, SAP R/3
<b>Connectivity</b>	10BaseT/100BaseTX Ethernet, USB, IEEE 1284, IEEE 802.11b/g Wireless LAN, Bluetooth (HCRP)
<b>Device Management</b>	TopAccess
<b>Certification</b>	WHQL, Novell



**Corporate Office:** 2 Musick, Irvine, CA 92618-1631 • Tel: 949/462-6000  
**East Coast:** 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 • Tel: 973/316-2700 Fax: 973/263-2393  
**Midwest:** 8770 W. Bryn Mawr Ave., Suite 700, Chicago IL 60631 • Tel: 773/380-6000 Fax: 773/380-8077  
**South:** 4855 Peachtree Industrial Blvd., Suite 210, Norcross, GA 30092-3024 • Tel: 770/209-8540 Fax: 770/209-8556  
**West Coast:** 142 Technology, Suite 150, Irvine, CA 92618 • Tel: 949/462-6262 Fax: 949/462-2700  
**Web Site:** www.copiers.toshiba.com or www.fax.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.

© 2007 Toshiba America Business Solutions, Inc., Electronic Imaging Division  
 e-STUDIO351c/451c Spec Sheet/ Inv. Code ES351C451C2

**SCAN**

<b>Scan Resolution</b>	B&W: 600, 400, 300, 200, 150, 100 dpi Grayscale: 600*, 400*, 300, 200, 150, 100 dpi Color/ACS: 600*, 400*, 300, 200, 150, 100 dpi *Optional Expansion Memory Required
<b>Scan Speed</b>	B&W: Up to 50 SPM Grayscale: Up to 45 SPM Color: Up to 40 SPM
<b>File Format</b>	TIFF Single/Multipage, PDF, JPEG
<b>Authentication</b>	LDAP, SMTP

**e-FILING**

<b>Operation Method</b>	Touch Screen Control Panel or Client PC
<b>Number of Boxes</b>	1 Public Box, 200 Private User Boxes
<b>Capacity of Boxes</b>	100 Folders Per Box, 400 Documents Per Folder, 200 Pages Per Document
<b>File Format</b>	TIFF-MMR, TIFF-S, PDF, JPEG

**FACSIMILE**

<b>Compatibility</b>	Super G3
<b>Modem Speed</b>	33.6 Kbps
<b>Compression Method</b>	MH, MR, MMR, JBIG
<b>Transmission Speed</b>	Approximately 3 Seconds Per Page
<b>Fax Memory</b>	500 MB Transmission, 120 MB Reception, 80+ GB HDD Backup
<b>Memory Transmission</b>	100 Jobs, 1,000 Destinations Max, 400 Destinations/Job
<b>Scan Speed</b>	0.7 Seconds Per Page, 50 SPM

**OPTIONS**

<b>MR3018 Reversing Auto Document Feeder (RADF)</b>	Simplex Originals (13-55 lbs.) Duplex Original (13-42 lbs.)
<b>KD1011 Paper Feed Pedestal (PFP)</b>	550-Sheet Pedestal, Statement-R to Ledger (17-28 lbs.)
<b>MY1021 Cassette Module</b>	550-Sheet Drawer, Statement-R to Ledger (17-28 lbs.)
<b>KD1012 Large Capacity Feeder (LCF)</b>	2,500-Sheet Drawer, Letter (17-28 lbs.) Stacks Side-By-Side (2 x 1,250)
<b>MJ1022 Single-Position Hanging Finisher (e-STUDIO351c Only)</b>	2 Tray, Hanging Design Tray 1 Stack Capacity: 200 Sheets (Lt) Tray 2 Stack Capacity: 700 Sheets (Lt) Staple Capacity: 30 Sheets (Lt/Lt-R, 20 lbs.)
<b>MJ1101 Multi-Position Stapling Finisher</b>	2 Tray, Console Design Stationary Tray: 250 Sheets (Lt) Tray 1 Stack Capacity: 2,000 Sheets (Lt) Staple Capacity: 50 Sheets (Lt /Lt-R, 20 lbs.) Ad Hoc Stapling
<b>MJ1024 Multi-Position Stapling Finisher with Saddle-Stitch</b>	2 Tray + Saddle-Stitch Tray, Console Design Tray 1 Stack Capacity: 1,000 Sheets (Lt) Tray 2 Stack Capacity: 1,000 Sheets (Lt) Staple Capacity: 50 Sheets (Lt/Lt-R, 20 lbs.)
<b>MJ6004 Hole Punch Unit</b>	2- or 3-Hole Punch Capability (For MJ1024)
<b>MJ6101 Hole Punch Unit</b>	2- or 3-Hole Punch Capability (For MJ1101)
<b>KN3511 Bridge Kit</b>	Required with MJ1022, MJ1023, MJ1024
<b>KA3511 Platen Cover</b>	
<b>KK3511 Work Tray</b>	
<b>GD1200 Fax Board</b>	
<b>GD1160 2nd Line Fax Board</b>	
<b>GN1041 802.11b/g Wireless LAN Adapter</b>	
<b>GN2010 Bluetooth Module</b>	
<b>GN3010 Wireless Antenna</b>	
<b>G01060 PCI Slot</b>	
<b>GF1140 Parallel Interface Kit</b>	
<b>GP1040 Scrambler Board</b>	
<b>GP1060 Data Overwrite Kit</b>	
<b>GQ1020 Coin Controller Wiring Harness</b>	
<b>GC1181 128 MB Memory Upgrade</b>	
<b>GC1230 512 MB Memory Upgrade</b>	
<b>GB1280 Re-Rite - Integrated OCR Conversion Distribution Tool</b>	
<b>TB-04SXP01-03 e-Copy ScanStation OP</b>	
<b>TB-ACCSS02-00 e-Copy ScanStand Accessory Box</b>	