

**e**STUDIO5520c/6520c/6530c

Real life color.

Performance that's out of this world.



55/65/75 BW  
55/65/65 C



Workgroup



Color



Copy / Print / Scan / Fax

**TOSHIBA**  
Leading Innovation >>>



# e-STUDIO5520c/6520c/6530c

**Powerful performance, lightning speed,  
and the biggest, boldest color ever.**

Brilliant color images are delivered at up to 65 pages per minute, with black and white up to 75 pages per minute. It's high volume output and high quality, affordable color, all wrapped up into one. The e-STUDIO5520c/6520c/6530c Series. Only from Toshiba.



10.4" super VGA control panel



USB direct print from & scan to



Auto paper size detection from every drawer

## SPECIFICATIONS

<b>Copying Process</b>	4-Drum Electrostatic Photographic Transfer System with Internal Transfer Belt
<b>Copying Type</b>	4-Beam Color Laser (8 bit)
<b>Copy/Print Resolution</b>	600 x 600 dpi (10 bit)/1200 x 1200 dpi
<b>Copy/Print Speed</b>	e-STUDIO5520c - 55 PPM Color / 55 PPM B&W e-STUDIO6520c - 65 PPM Color / 65 PPM B&W e-STUDIO6530c - 65 PPM Color / 75 PPM B&W
<b>Warm-Up Time</b>	Approx. 180 Seconds
<b>First Copy Out Time</b>	e-STUDIO5520c - 6.5 Seconds Color / 5.3 Seconds B&W e-STUDIO6520c - 6.5 Seconds Color / 5.3 Seconds B&W e-STUDIO6530c - 6.5 Seconds Color / 4.6 Seconds B&W
<b>Duty Cycle</b>	225K / 250K / 275K Copies
<b>Multiple Copying</b>	Up to 9999 Copies
<b>Acceptable Paper Size and Weight</b>	Cassette: ST-R to 12" x 18" (17 lbs. Bond - 140 lbs. Index) Bypass: ST-R to 13" x 19" (17 lbs. Bond - 110 lbs. Cover) ST-R to 12" x 47" Banner (17 lbs. Bond - 110 lbs. Cover) LCF: LT (17 lbs. Bond - 140 lbs. Index)
<b>Memory (Min/Max)</b>	Page + Main Memory: 2 GB, PowerPC 1.2 GHz Processor HD: 80+ GB
<b>Reduction/Enlargement Bypass</b>	25% to 400% 100-Sheet Bypass (17 lbs. Bond - 110 lbs. Cover)
<b>Control Panel</b>	10.4 Color Super VGA Tilttable LCD Touch Panel
<b>Paper Supply</b>	Up to 6,000-Sheet Input Capacity (Tandem Version + LCF) 4 Drawer Version: 4 x 540-Sheet Cassettes (2,160 Sheets) Tandem Version: 2 x 540-Sheet Cassettes + 2,320-Sheet LCF 100-Sheet Bypass Optional 1 x 2,500-Sheet LCF
<b>Duplex</b>	Standard Trayless Automatic Duplex Unit (17 lbs. Bond - 140 lbs. Index)
<b>Dimensions</b>	Approx. 38.582" x 27.480" x 60.629" (W x D x H) Weight Approx. 573 lbs.
<b>PM Cycle</b>	225K / 250K / 275K
<b>CMYK Toner Yield</b>	CMY: 26.5K, K: 73K
<b>Power Supply</b>	120 V, 20 Amps
<b>Power Consumption</b>	Maximum 2.0 kW
<b>PRINT SPECIFICATIONS</b>	
<b>PDL Support</b>	PCL6 & PostScript 3
<b>Operating Systems</b>	Netware 6.x, Windows 2000/XP, Windows Server 2003, Vista, Citrix MetaFrame, Macintosh, Linux, UNIX
<b>Protocol Support</b>	IPX/SPX, TCP/IP, V4/IPv6 Dual Stack, Ethernalk, AppleTalk PAP, NetBIOS Over TCP/IP, LPR/LPD, IPP, SMB, SNMP, Netware, Port 9100, Bluetooth (HCRP)
<b>Drivers</b>	Windows 2000, Server 2003, Vista, XP Macintosh OS 10.1/10.2/10.3, 10.4, 10.5 (OS 10.4 PPD) UNIX, AS400 via iData & Port 9100, SAP R/3
<b>Connectivity</b>	10/100/1000BaseTX Ethernet, 802.11b/g Wireless LAN, USB, Bluetooth (HCRP)
<b>Device Management</b>	TopAccess
<b>Certification</b>	WHQL, Novell

## SCAN SPECIFICATIONS

<b>Scan Resolution</b>	Up to 600 dpi
<b>Scan Speed</b>	Up to 77 SPM Color / 77 SPM B&W
<b>File Format</b>	TIFF, PDF, JPEG, XPS
<b>Authentication</b>	LDAP, SMTP, Windows Domain

## FACSIMILE SPECIFICATIONS

<b>Compatibility</b>	Super G3
<b>Data Compression</b>	MH / MR / MMR / JBIG
<b>Transmission Speed</b>	Approx. 3 Seconds Per Page
<b>Fax Modem Speed</b>	33.6 Kbps
<b>Fax Memory</b>	500 MB Transmission, 200 MB Reception (HDD)
<b>Memory Transmission</b>	100 Jobs, 1,000 Destinations Max. 400 Destinations / Job
<b>Scan Speed</b>	.7 Seconds Per Page, Maximum 50 SPM

## E-FILING SPECIFICATIONS

<b>Operation Method</b>	Color Touch Screen Control Panel or Client PC
<b>Number of Boxes</b>	1 Public Box, 200 Private User Boxes
<b>Capacity of Boxes</b>	100 Folders Per Box, 400 Documents Per Folder 200 Pages Per Document

## OPTIONS

<b>MP2501 Large Capacity Feeder (LCF)</b>	2,500-Sheet Drawer, Letter
<b>MJ1103 Multi-Position Finisher</b>	Stationary Tray 250-Sheets Finishing Tray 3,000-Sheets Staple Capacity: 50 Sheets
<b>MJ1104 Saddle-Stitch Finisher</b>	Stationary Tray 250-Sheets Finishing Tray 3,000-Sheets Staple Capacity: 50 Sheets Saddle Tray Stitcher Up to 50 Sets
<b>MJ6102 Hole Punch Unit</b>	(for MJ1103/MJ1104) 2- or 3-Hole Punch Capability
<b>GA1310 EFI Controller</b>	(not available at launch)
<b>GD1270 Fax Board</b>	
<b>GD1260 2nd Line Fax</b>	
<b>GN1050 Wireless LAN Adapter</b>	
<b>GN2010 Bluetooth Adapter</b>	
<b>GN3010 Wireless Antenna</b>	
<b>GPI070 Data Overwrite Kit</b>	
<b>GPI080 IP SEC Enabler</b>	
<b>GS1010 Meta Scan Enabler for e-CONNECT</b>	
<b>GS1020 External Interface Enabler for Open Platform</b>	
<b>KP2004 HID SmartCard Authentication</b>	
<b>KP2005 MiFare SmartCard Authentication</b>	



**Corporate Office:** 2 Musick, Irvine, CA 92618-1631 / Tel: 949/462-6000  
**East Coast:** 959 Route 46 East, 5th Floor, Parsippany, NJ 07054 / Tel: 973/316-2700 Fax: 973/263-2393  
**Midwest:** 8770 W. Bryn Mawr Ave., Suite 700, Chicago IL 60631 / Tel: 773/380-6000 Fax: 773/380-8077  
**South:** 4855 Peachtree Industrial Blvd., Suite 210, Norcross, GA 30092 / Tel: 770/209-8540 Fax: 770/209-8556  
**West Coast:** 142 Technology, Suite 150, Irvine, CA 92618 / Tel: 949/462-6262 Fax: 949/462-2700  
**Web Site:** www.copiers.toshiba.com

Designs and specifications subject to change without notice. For best results and reliable performance, always use supplies manufactured or designated by Toshiba. Not all options and accessories may be available at the time of product launch. Please contact a local Authorized Toshiba Dealership for availability. Toner yields are estimates, based on 6% coverage, letter-size page. Driver and connectivity feature support varies by client/network operating system.